


SPECIFICATIONS



Model Number: TNE2A
Part Number: 020174

August 23, 2005

Mechanical Drawing:



Specifications subject to change without notice.

Motor:

Frequency	= 50 / 60 Hz
Nominal Voltage	= 115 VAC
Nominal Running Current	= 0.530 Amps
Max. Locked Rotor Current	= 1.35 Amps
Running Power	= 56 Watts
Average Speed	= 3480 RPM
Bearings	= Ball
Air Flow	= 280 / 340 CFM
Acoustic	= 61.6 / 65.4 dBA

Construction:

Venturi: Plastic, Black, UL 94V-0
Propeller & Cover: Plastic, Black, UL 94V-0

Life Expectancy:

This fan is designed for continuous duty life of 25,000 hours at 40°C.

Additional Features:

Permanent Split Capacitor
Automatic Reset Thermal Protector
Thermal Shutdown Protection
Class B Insulation
Operating Temperature: -10°C to 70°C
Storage Temperature: -40°C to 85°C

Termination:

0.125" Terminals

Agency Approvals:

UL, CSA, TUV, CE