

Main

Range of product	Zelio Relay
Series name	Universal
Product or component type	Plug-in relay
Device short name	RUM
Contacts type and composition	3 C/O
Control circuit voltage	120 V AC
[Ithe] conventional enclosed thermal current	10 A at -40...55 °C
Status LED	With
Control type	Without push-button
Utilisation coefficient	20 %

Complementary

Shape of pin	Cylindrical
[Ui] rated insulation voltage	300 V conforming to UL 300 V conforming to CSA 250 V conforming to IEC
[Uimp] rated impulse withstand voltage	4 kV
Contacts material	AgNi
[Ie] rated operational current	5 A AC-1/DC-1 (NC) conforming to IEC 16 A at 277 V AC-1 conforming to UL 12 A at 28 V DC-1 conforming to UL 10 A AC-1/DC-1 (NO) conforming to IEC
Minimum switching current	10 mA
Maximum switching voltage	250 V DC conforming to IEC 250 V AC conforming to IEC
Minimum switching voltage	17 V
Resistive rated load	10 A at 28 V DC 10 A at 250 V AC
Maximum switching capacity	280 W, DC circuit 2500 VA, AC circuit
Minimum switching capacity	170 mW
Operating rate	<= 1200 cycles/hour under load <= 18000 cycles/hour no-load
Mechanical durability	5000000 cycles
Electrical durability	100000 cycles for resistive load
Average coil consumption in VA	2...3 at 60 Hz
Drop-out voltage threshold	>= 0.15 U _c AC
Operate time	20 ms
Average coil resistance	1700 Ohm at 20 °C +/- 15 %
Rated operational voltage limits	96...132 V AC
Protection category	RT I
Operating position	Any position
Product weight	0.088 kg

Environment

Dielectric strength	1550 V AC between poles 1550 V AC between coil and contact 1500 V AC between contacts
Product certifications	CSA GOST UL
Standards	EN/IEC 61810-1 UL 508 CSA C22.2 No 14
Ambient air temperature for storage	-40...85 °C
Ambient air temperature for operation	-40...55 °C
Vibration resistance	4 gn (f = 10...150 Hz), amplitude +/- 1 mm (on 10 cycles not operating) conforming to EN/IEC 60068-2-27 3 gn (f = 10...150 Hz), amplitude +/- 1 mm (on 10 cycles in operation) conforming to EN/IEC 60068-2-27
IP degree of protection	IP40 conforming to EN/IEC 60529
Shock resistance	10 gn not operating 10 gn in operation
Pollution degree	3