## SIEMENS

## Product data sheet



## 3RT1025-1XB40-0LA2

CONTACTOR, AC-3, 7.5KW/400V DC 24V, 0.7...1.25\*US, 3-POLE SIZE S0, SCREW CONNECTION WITH SOLID-STATE CONTROL BLOCK VARISTOR INTEGRATED

General details:	
Size of the contactor	SO
Number of poles	3
Control circuit:	
Design of activation of the operating mechanism	contactor control unit
Type of voltage	DC
Control supply voltage	
<ul> <li>for DC / rated value / minimum</li> </ul>	24 V
<ul> <li>for DC / rated value / maximum</li> </ul>	24 V
Supply voltage frequency / for auxiliary and control current circuit / rated value	
• minimum	0 Hz
• maximum	0 Hz
Design of the surge suppressor	with varistor
Main circuit:	
Number of NC contacts / for main contacts	0
Number of NO contacts / for main contacts	3
Operating current	
• at AC-3 / at 400 V / rated value	17 A

• at AC-1 / at 400 V / rated value	40 A
Service power	
• at AC-3 / at 400 V / rated value	7.5 kW
<ul> <li>at AC-1 / at 400 V / rated value</li> </ul>	23 kW
Auxiliary circuit:	
Number of NO contacts / for auxiliary contact	0
Number of NC contacts / for auxiliary contact	0
Connection type:	
Design of the electrical connection / for main current	screw-type terminals
circuit	
-	screw-type terminals
circuit Design of the electrical connection / for auxiliary and	
circuit Design of the electrical connection / for auxiliary and control current circuit	

## last change:

Technical Assistance:	Telephone:	+49 (0) 911-895-5900 (8°° - 17°° CET)
	Fax:	+49 (0) 911-895-5907
	E-Mail:	technical-assistance@siemens.com
	Internet:	www.siemens.de/lowvoltage/technical-assistance