

# SIEMENS

## Product data sheet

## 3RU1116-1HC1



Abb. ähnlich / similar picture

OVERLOAD RELAY, 5.5...8 A, 1NO+1NC,  
SIZE S00, CLASS 10,  
CAGE CLAMP CONNECTION,  
FOR INSTALLAT. AS A SINGLE UNIT


### General technical details:

Operating current / of the fuse link / rated value	25 A
Adjustable response current / of the current-dependent overload release / initial value	5.5 A
Adjustable response current / of the current-dependent overload release / final value	8 A
Service power / for three-phase servomotors / rated value	3 kW
Number of NC contacts / for auxiliary contact	1
Number of NO contacts / for auxiliary contact	1
Number of change-over switches / for auxiliary contact	0
Type of assignment	2
Type of protection	DMT 98 ATEX G 001

### Mechanical design:

Design of the electrical connection / for main current circuit	Cage Clamp terminals
Design of the electrical connection / for auxiliary and control current circuit	Cage Clamp terminals
Size of the contactor / can be combined / company-specific	S00

Type of fixing/fixation	stand-alone installation
Size of overload relay	S00
Ambient conditions:	
Protection class IP	IP20



last change:

10/31/2006

**Technical Assistance:**

Telephone: +49 (0) 911-895-5900 (8°° - 17°° CET)

Fax: +49 (0) 911-895-5907

E-Mail: [technical-assistance@siemens.com](mailto:technical-assistance@siemens.com)

Internet: [www.siemens.de/lowvoltage/technical-assistance](http://www.siemens.de/lowvoltage/technical-assistance)