



DIGITAL MONITORING RELAY CURRENT MONITORING, 22.5MM FROM 0.05 TO 10A AC/DC OVERSHOOT AND UNDERSHOOT AC/DC 24 TO 240V DC AND AC 50 TO 60 HZ STARTUP AND INTERF. PEAK DELAY 0.1 TO 20S HYSTERESIS 0.01 TO 5A 1 CHANGEOVER CONTACT W. OR W/O ERROR LOG SPRING-LOADED TYPE

Figure similar

Product function		Current monitoring relay
<b>Measuring circuit:</b>		
Number of poles for main current circuit		1
Type of current for monitoring		AC/DC
Measurable current	A	0.05 ... 15
Measurable current at AC	mA	50 ... 15 000
Measurable line frequency	Hz	40 ... 500
Adjustable response value current		
• 1	A	0.5 ... 10
• 2	A	0.5 ... 10
Adjustable response delay time		
• when starting	s	0.1 ... 20
• with lower or upper limit violation	s	0.1 ... 20
Adjustable switching hysteresis for measured current value	mA	10 ... 5 000
Buffering time in the event of power failure minimum	ms	10
Operating voltage Rated value	V	24 ... 240
Response time maximum	ms	450
Relative metering precision	%	5

Accuracy of digital display		+/-1 digit
Relative temperature-related measurement deviation	%	5
Temperature drift per °C	%/°C	0.1
Relative repeat accuracy	%	1

#### General technical data:

<b>Design of the display</b>		LCD
<b>Product function</b>		
• Overcurrent detection 1 phase		Yes
• Overcurrent detection 3 phase		No
• undercurrent detection 1 phase		Yes
• undercurrent detection 3 phases		No
• Overcurrent detection DC		Yes
• undercurrent detection DC		Yes
• Current window recognition DC		Yes
• External reset		Yes
• Auto-reset		Yes
• Adjustable open/closed-circuit current principle		Yes
<b>Startup time after the control supply voltage has been applied</b>	ms	1 000
<b>Type of voltage of the supply voltage</b>		AC/DC
<b>Supply voltage</b>		
• 1 at AC		
— at 50 Hz	V	24 ... 240
— at 60 Hz	V	240 ... 24
• 1		
— at DC	V	24 ... 240
<b>Surge voltage resistance Rated value</b>	kV	4
<b>Active power consumption</b>	W	2
<b>Protection class IP</b>		IP20
<b>Electromagnetic compatibility</b>		IEC 60947-1 / IEC 61000-6-2 / IEC 61000-6-4
<b>Vibration resistance acc. to IEC 60068-2-6</b>		1 ... 6 Hz: 15 mm, 6 ... 500 Hz: 2g
<b>Shock resistance acc. to IEC 60068-2-27</b>		sinusoidal half-wave 15g / 11 ms
<b>Installation altitude at height above sea level maximum</b>	m	2 000
<b>Conducted interference due to burst acc. to IEC 61000-4-4</b>		2 kV
<b>Conducted interference due to conductor-earth surge acc. to IEC 61000-4-5</b>		2 kV
<b>Conducted interference due to conductor-conductor surge acc. to IEC 61000-4-5</b>		1 kV
<b>Electrostatic discharge acc. to IEC 61000-4-2</b>		6 kV contact discharge / 8 kV air discharge
<b>Field-bound parasitic coupling acc. to IEC 61000-4-3</b>		10 V/m

<b>Insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3</b> <b>Rated value</b>	V	690
<b>maximum permissible voltage for safe isolation</b>		
• between control and auxiliary circuit	V	300
• between auxiliary and auxiliary circuit	V	300
<b>Degree of pollution</b>		3
<b>Ambient temperature</b>		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +85
• during transport	°C	-40 ... +85
<b>Galvanic isolation</b>		
• between entrance and outlet		Yes
• between the outputs		Yes
• between the voltage supply and other circuits		Yes






Mechanical data:		
<b>Width</b>	mm	22.5
<b>Height</b>	mm	94
<b>Depth</b>	mm	91
<b>mounting position</b>		any
<b>Required spacing for grounded parts</b>		
• forwards	mm	0
• Backwards	mm	0
• at the side	mm	0
• upwards	mm	0
• downwards	mm	0
<b>Required spacing with side-by-side mounting</b>		
• forwards	mm	0
• Backwards	mm	0
• at the side	mm	0
• upwards	mm	0
• downwards	mm	0
<b>Required spacing for live parts</b>		
• forwards	mm	0
• Backwards	mm	0
• at the side	mm	0
• upwards	mm	0
• downwards	mm	0
<b>Mounting type</b>		snap-on mounting
<b>Type of electrical connection</b>		
• for auxiliary and control current circuit		spring-loaded terminals
• for main current circuit		spring-loaded terminals

<b>Product function</b>		
<ul style="list-style-type: none"> <li>removable terminal for auxiliary and control circuit</li> </ul>		Yes
<ul style="list-style-type: none"> <li>removable terminal for main circuit</li> </ul>		Yes
<b>Type of connectable conductor cross-section</b>		
<ul style="list-style-type: none"> <li>solid</li> </ul>		2x (0.25 ... 1.5 mm <sup>2</sup> )
<ul style="list-style-type: none"> <li>finely stranded <ul style="list-style-type: none"> <li>with core end processing</li> <li>without core end processing</li> </ul> </li> </ul>		2 x (0.25 ... 1.5 mm <sup>2</sup> ) 2x (0.25 ... 1.5 mm <sup>2</sup> )
<ul style="list-style-type: none"> <li>for AWG conductors <ul style="list-style-type: none"> <li>solid</li> <li>stranded</li> </ul> </li> </ul>		2x (24 ... 16) 2x (24 ... 16)

**Outputs:**

<b>Number of NO contacts delayed switching</b>		0
<b>Number of NC contacts delayed switching</b>		0
<b>Number of CO contacts delayed switching</b>		1
<b>Ampacity</b>		
<ul style="list-style-type: none"> <li>of the output relay <ul style="list-style-type: none"> <li>at AC-15 <ul style="list-style-type: none"> <li>at 250 V at 50/60 Hz</li> <li>at 400 V at 50/60 Hz</li> </ul> </li> <li>at DC-13 <ul style="list-style-type: none"> <li>at 24 V</li> <li>at 125 V</li> <li>at 250 V</li> </ul> </li> <li>for permanent overcurrent maximum permissible</li> <li>for overcurrent duration &lt; 1 s maximum permissible</li> </ul> </li> </ul>	A A A A A A A A	3 3 1 0.2 0.1 15 50
<b>Operating current at 17 V minimum</b>	A	0.005
<b>Continuous current of the DIAZED fuse link of the output relay</b>	A	4
<b>Thermal current of the switching element with contacts maximum</b>	A	5
<b>Mechanical service life (switching cycles) typical</b>		10 000 000
<b>Electrical endurance (switching cycles) at AC-15 at 230 V typical</b>		100 000
<b>Operating frequency with 3RT2 contactor maximum</b>	1/h	5 000

**Certificates/ approvals:**

General Product Approval		EMC	Declaration of Conformity	Test Certificates
 CCC		 UL	 C-TICK	 EG-Konf.

[Typprüfbescheinigung/Werkszeugnis](#)

Test Certificates	Shipping Approval	other		
<a href="#">spezielle Prüfbescheinigungen</a>	 DNV	 GL	 LRS	<a href="#">sonstig</a>

### Further information

#### Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

#### Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

#### Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mfb=3UG46222AW30>

#### Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<https://support.industry.siemens.com/cs/ww/en/ps/3UG46222AW30>

#### Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

[http://www.automation.siemens.com/bilddb/cax\\_de.aspx?mfb=3UG46222AW30&lang=en](http://www.automation.siemens.com/bilddb/cax_de.aspx?mfb=3UG46222AW30&lang=en)



last modified:

17.07.2015