

CIRCUIT BREAKER 230/400V 10KA, 1-POLE, D, 10A, D=70MM



Figure similar

| Model | | |
|---|---|--------------------------------|
| product brand name | | SENTRON |
| Product designation | | 5SY miniature circuit breaker |
| Design of the product | | 5SY miniature circuit breakers |
| General technical data | | |
| Number of poles | | 1 |
| Number of poles / Note | | 1P |
| Tripping characteristic class | | D |
| circuit-breaker / Design | | 5SY4 |
| Mechanical service life (switching cycles) / typical | | 20 000 |
| Overvoltage category | | 3 |
| Voltage | | |
| Type of voltage | | AC/DC |
| Insulation voltage | | |
| <ul style="list-style-type: none"> with single-phase operation / at AC / Rated value | V | 250 |
| <ul style="list-style-type: none"> with multi-phase operation / at AC / Rated value | V | 440 |

| Supply voltage | | |
|---|----|---------------------------------|
| Supply voltage / at AC / Rated value | V | 400 |
| Supply voltage frequency / Rated value | Hz | 50 |
| Protection class | | |
| Protection class IP | | IP20, with connected conductors |
| Energy limiting class | | 3 |
| Switching capacity | | |
| Switching capacity current | | |
| • at DC / acc. to IEC 60947-2 / Rated value | kA | 15 |
| • acc. to EN 60898 / Rated value | kA | 10 |
| • acc. to IEC 60947-2 / Rated value | kA | 20 |
| Dissipation | | |
| Active power loss | | |
| • for rated value of the current / at AC / in hot operating state / per pole | W | 0.9 |
| Electricity | | |
| rated current I _n / IEC, DIN/VDE / at 40 Cel | A | 9.4 |
| Current / at AC / Rated value | A | 10 |
| Product details | | |
| Product feature / Touch protection | | Yes |
| Product component | | |
| • combined terminal top | | Yes |
| • combined terminal bottom | | Yes |
| Product property | | |
| • Properties for main switches in accordance with EN 60204-1 | | Yes |
| • halogen-free | | Yes |
| • sealable | | Yes |
| • silicon-free | | Yes |
| Product expansion / can be installed / supplementary devices | | Yes |
| Product function | | |
| Product function / neutral conductor switching | | No |
| Short circuit | | |
| Breaking capacity short-circuit current (I_{cn}) | | |
| • at AC / acc. to UL 1077 and CSA C22.2 No.235 | kA | 5 |
| • at DC / acc. to EN 60898-2 | kA | 10 |
| Number | | |
| Number of test cycles / for environmental testing / acc. to IEC 60068-2-30 | | 6 |

| Connections | | |
|--|-----------------|---|
| Connectable conductor cross-section / stranded | | |
| • minimum | mm ² | 0.75 |
| • maximum | mm ² | 35 |
| Connectable conductor cross-section | | |
| • solid | | |
| — minimum | mm ² | 0.75 |
| — maximum | mm ² | 35 |
| • finely stranded / with core end processing | | |
| — minimum | mm ² | 0.75 |
| — maximum | mm ² | 25 |
| AWG number / as coded connectable conductor cross section | | |
| • minimum | | 14 |
| • maximum | | 4 |
| Tightening torque [lbf·in] / with screw-type terminals | | |
| • minimum | lbf·in | 22 |
| • maximum | lbf·in | 26 |
| Tightening torque / with screw-type terminals | | |
| • minimum | N·m | 2.5 |
| • maximum | N·m | 3 |
| Position / of power supply cord | | Any |
| Mechanical Design | | |
| Height | mm | 90 |
| Width | mm | 18 |
| Depth | mm | 76 |
| mounting position | | any |
| Installation depth | mm | 70 |
| Number of width units | | 1 |
| Mounting type | | Quick assembly system |
| Net weight | g | 155 |
| Environmental conditions | | |
| Influence of the surrounding temperature | | Max. 95% humidity |
| Shock resistance / acc. to IEC 60068-2-27 | | 150m/s ² at 11ms half-sine |
| Vibration resistance / acc. to IEC 60068-2-6 | | 50m/s ² at 25 to 150Hz and 60m/s ² at 35Hz (4sec) |
| Ambient temperature | | |
| • minimum | °C | -25 |
| • maximum | °C | 55 |
| • during storage / minimum | °C | -40 |
| • during storage / maximum | °C | 75 |
| Certificates | | |

General Product Approval

Declaration of
Conformity

CCC



IMQ



UL



VDE



EG-Konf.

Test Certificates

[sonstig](#)[spezielle
Prüfbescheinigung
n](#)

LRS




RINA

Shipping Approval

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)<http://www.siemens.com/lowvoltage/catalogs>**Industry Mall (Online ordering system)**<https://eb.automation.siemens.com/mall/en/WW/Catalog/Product/5SY41108>**Service&Support (Manuals, Certificates, Characteristics, FAQs,...)**<http://support.automation.siemens.com/WW/view/en/5SY41108/all>**Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)**http://www.automation.siemens.com/bilddb/cax_en.aspx?mfb=5SY41108**CAX-Online-Generator**<http://www.siemens.com/cax>**Tender specifications**<http://ausschreibungstexte.siemens.com/tiplv>



last modified:

07.08.2015