# **Anti-Surge Thick Film Chip Resistors** 0603, 0805, 1206, 1210

Type: ERJ P03, P06, P08, P14





#### ■ Features

- Anti-Surge characteristics superior to standard metal film resistors
- High reliability


Metal glaze thick film resistive element and three layers of electrodes

- Suitable for both reflow and flow soldering
- High power…0.2 W : 1608(0603) size

0.25 W : 2012(0805) size 0.33 W : 3216(1206) size 0.5 W : 3225(1210) size

● Reference Standards…IEC 60115-8, JIS C 5201-8

#### ■ Explanation of Part Numbers




Resistance Value


The first two or three digits are significant figures of resistance and the third one denotes number of zeros following.

Example:  $222\rightarrow2.2 \text{ k}\Omega$  $1002\rightarrow10 \text{ k}\Omega$ 

#### ■ Construction



#### ■ Dimensions in mm (not to scale)



Туре		Dimensions (mm)							
(inches)	L	W	а	b	t	[g/1000 pcs.]			
ERJP03 (0603)	1.60 <sup>±0.15</sup>	0.80+0.15	0.15+0.15	0.30 <sup>±0.15</sup>	0.45 <sup>±0.10</sup>	2			
ERJP06 (0805)	2.00 <sup>±0.20</sup>	1.25 <sup>±0.10</sup>	0.25 <sup>±0.20</sup>	0.40 <sup>±0.20</sup>	0.60 <sup>±0.10</sup>	4			
ERJP08 (1206)	3.20+0.05	1.60+0.05	0.40 <sup>±0.20</sup>	0.50 <sup>±0.20</sup>	0.60 <sup>±0.10</sup>	10			
ERJP14 (1210)	3.20 <sup>±0.20</sup>	2.50 <sup>±0.20</sup>	0.35 <sup>±0.20</sup>	0.50 <sup>±0.20</sup>	0.60 <sup>±0.10</sup>	16			

#### ■ Ratings


Type (inches)	Power Rating at 70 °C (W)	Limiting Element Voltage (Maximum RCWV) <sup>(1)</sup> (V)	Maximum Overload Voltage (2) (V)	Resistance Tolerance (%)	Resistance Range $(\Omega)$	T.C.R. [x10 <sup>-6</sup> /°C (ppm/°C)]	Category Temperature Range (Operating Temperature Range) (°C)
				±0.5	10 to 1 M (E24, E96)	±150	
ERJP03 (0603)		150	200	±1	10 to 1 M (E24, E96)	±200	−55 to +155
			±5	1 to 1 M (E24)	$\pm 200$ Less than 10 $\Omega$ : –150 to +400		
ERJP06	ERJP06 0.05 150		200	±0.5, ±1	10 to 3.3 M (E24, E96)	Less than 33 $\Omega$ : ±300 More than 33 $\Omega$ : ±100	
(0805)	0.25	(400) <sup>(3)</sup>	(600) <sup>(3)</sup>	±5	1 to 3.3 M (E24)	Less than 33 $\Omega$ : ±300 More than 33 $\Omega$ : ±200	
ERJP08	0.33	200	400	±0.5, ±1	10 to 1 M (E24, E96)	±100	-55 to +155
(1206)	(1206) U.33 (500) <sup>(3)</sup>	(1000) <sup>(3)</sup>	±5	1 to 10 M (E24)	Less than 10 $\Omega$ : –100 to +600 More than 10 $\Omega$ : ±200		
ERJP14	0.5	200	400	±0.5, ±1	10 to 1 M (E24, E96)	±100	-55 to +155
(1210)	0.5	200	400	±5	1 to 1 M (E24)	Less than 10 $\Omega$ : -100 to +600 More than 10 $\Omega$ : ±200	

<sup>(1)</sup> Rated Continuous Working Voltage (RCWV) shall be determined from RCWV=√Power Rating × Resistance Values, or Limiting Element Voltage (max. RCWV) listed above, whichever less.


#### Power Derating Curve

For resistors operated in ambient temperatures above 70 °C, power rating shall be derated in accordance with the figure on the right.


\* When the temperature of ERJP06/08/14 is 155 °C or less, the derating start temperature can be changed to 125 °C. (See the dotted line)



#### ■ ESD Characteristic



Anti-Surge Thick Film Chip Resistors(ERJP Type)Thick Film Chip Resistors(ERJ Type)



<sup>(2)</sup> Overload (Short-time Overload) Test Voltage (SOTV) shall be determined from SOTV=2.5 × Power Rating or max. Overload Voltage listed above whichever less.

<sup>(3)</sup> Please contact us when resistors with guaranteed high voltage are need.

## Panasonic

# Anti-Pulse Thick Film Chip Resistors 0805, 1206, 1210

Type: ERJ T06, T08, T14







#### ■ Features

Anti-Pulse characteristics

High pulse characteristics achieved by the optimized trimming specifications

High reliability

Metal glaze thick film resistive element and three layers of electrodes


Suitable for both reflow and flow soldering

● High power…0.25 W: 2012(0805) size


0.33 W : 3216(1206) size 0.5 W : 3225(1210) size

● Reference Standards…IEC 60115-8, JIS C 5201-8


#### ■ Explanation of Part Numbers



#### ■ Construction



#### ■ Dimensions in mm (not to scale)



Туре		Dimensions (mm)							
(inches)	L	W	а	b	t	[g/1000 pcs.]			
ERJT06 (0805)	2.00 <sup>±0.20</sup>	1.25 <sup>±0.10</sup>	0.25 <sup>±0.20</sup>	0.40 <sup>±0.20</sup>	0.60 <sup>±0.10</sup>	4			
ERJT08 (1206)	3.20+0.05	1.60+0.05	0.40 <sup>±0.20</sup>	0.50 <sup>±0.20</sup>	0.60 <sup>±0.10</sup>	10			
ERJT14 (1210)	3.20 <sup>±0.20</sup>	2.50 <sup>±0.20</sup>	0.35 <sup>±0.20</sup>	0.50 <sup>±0.20</sup>	0.60 <sup>±0.10</sup>	16			

#### ■ Ratings


Type (inches)	Power Rating at 70 °C (W)	Limiting Element Voltage (Maximum RCWV) <sup>(1)</sup> (V)	Maximum Overload Voltage <sup>(2)</sup> (V)	Resistance Tolerance (%)	Resistance Range (Ω)	T.C.R. [x10 <sup>-6</sup> /°C (ppm/°C)]	Category Temperature Range (Operating Temperature Range) (°C)
ERJT06 (0805)	0.25	150	200	±5	1 to 1 M (E24)	Less than 10 $\Omega$ : -100 to +600 Less than 33 $\Omega$ : ±300 More than 33 $\Omega$ : ±200	-55 to +155
ERJT08 (1206)	0.33	200	400	±5	1 to 1 M (E24)	Less than 10 $\Omega$ : -100 to +600 More than 10 $\Omega$ : ±200	-55 to +155
ERJT14 (1210)	0.5	200	400	±5	1 to 1 M (E24)	Less than 10 $\Omega$ : -100 to +600 More than 10 $\Omega$ : ±200	

<sup>(1)</sup> Rated Continuous Working Voltage (RCWV) shall be determined from RCWV= $\sqrt{\text{Power Rating} \times \text{Resistance Values}}$ , or Limiting Element Voltage (max. RCWV) listed above, whichever less.

Overload (Short-time Overload) Test Voltage (SOTV) shall be determined from SOTV=2.5 × Power Rating or max. Overload Voltage listed above


#### Power Derating Curve

For resistors operated in ambient temperatures above 70 °C, power rating shall be derated in accordance with the figure on the right.



#### ■ Limiting Power Curve

• In rush pulse Characteristic




Test cycle: 1000 cycles


: Resistance value = within ±5% Spec

> • : Anti-Pulse Thick Film Chip Resistors (ERJT Type) O: Thick Film Chip Resistors (ERJ Type)


#### • ERJT06 (2012 (0805) size)



#### • ERJT08 (3216 (1206) size)



#### • ERJT14 (3225 (1210) size)




whichever less.

### ■ Packaging Methods (Taping)

#### Standard Quantity


Туре	Kind of Taping	Pitch (P <sub>1</sub> )	Quantity	
ERJP03				
ERJP06	Punched Carrier Taping	4	5000	
ERJP08		4 mm	5000 pcs./reel	
ERJP14	Embossed Carrier Taping			

● Carrier Tape (Unit:mm)



Туре	А	В	W	F	E	P <sub>1</sub>	P <sub>2</sub>	P <sub>0</sub>	$\phi D_0$	Т	$\phi D_1$
ERJP03	1.10 <sup>±0.10</sup>	1.90 <sup>±0.10</sup>	8.00 <sup>±0.20</sup>	3.50 <sup>±0.05</sup> 1.75 <sup>±0.10</sup>					0.70 <sup>±0.05</sup>	_	
ERJP06	1.65 <sup>±0.15</sup>	2.50 <sup>±0.20</sup>			1.75 <sup>±0.10</sup>	4.00 <sup>±0.10</sup>	2.00 <sup>±0.05</sup> 4.00 <sup>±</sup>	4.00+0.10	4 FO+010	0.84 <sup>±0.05</sup>	-
ERJP08	2.00 <sup>±0.15</sup>	3.60 <sup>±0.20</sup>	8.00 <sup>±0.30</sup>					4.00	1.50+0.10		_
ERJP14	2.80 <sup>±0.20</sup>	3.50 <sup>±0.20</sup>	0.00							1.00 <sup>±0.10</sup>	1.0+0.10


#### Taping Reel



					(Unit : mm)
Type	φA	φB	φC	W	Т
ERJP03					
ERJP06	180.0+0	60 min.	13.0 <sup>±1.0</sup>	9.0 <sup>±1.0</sup>	11.4 <sup>±1.0</sup>
ERJP08					
ERJP14					

#### ■ Recommended Land Pattern

In case of flow soldering, the land width must be smaller than the Chip Resistor width to control the solder amount properly. Generally, the land width should be 0.7 to 0.8 times (W) of the width of chip resistor. In case of reflow soldering, solder amount can be adjusted, therefore the land width should be set to 1.0 to 1.3 times chip resistor width (W).



Type	Dimensions (mm)					
(inches)	а	b	С			
ERJP03 (0603)	0.7 to 0.9	2 to 2.2	0.8 to 1			
ERJP06 (0805)	1 to 1.4	3.2 to 3.8	0.9 to 1.4			
ERJP08 (1206)	2 to 2.4	4.4 to 5	1.2 to 1.8			
ERJP14 (1210)	2 to 2.4	4.4 to 5	1.8 to 2.8			


# **Panasonic**

### ■ Packaging Methods (Taping)

#### Standard Quantity


Type	Kind of Taping	Pitch (P <sub>1</sub> )	Quantity	
ERJT06	Dunahad Carrier Taning			
ERJT08	Punched Carrier Taping	4 mm	5000 pcs./reel	
ERJT14	Embossed Carrier Taping			

● Carrier Tape (Unit:mm)



Туре	А	В	W	F	E	P <sub>1</sub>	$P_2$	P <sub>0</sub>	$\phi D_0$	Т	$\phi D_1$
ERJT06	1.65 <sup>±0.15</sup>	2.50 <sup>±0.20</sup>	8.00 <sup>±0.20</sup>							0.04±0.05	-
ERJT08	2.00 <sup>±0.15</sup>	3.60 <sup>±0.20</sup>	8.00 <sup>±0.30</sup>	3.50 <sup>±0.05</sup>	1.75 <sup>±0.10</sup>	4.00 <sup>±0.10</sup>	2.00 <sup>±0.05</sup>	4.00 <sup>±0.10</sup>	1.50+0.10	0.84 <sup>±0.05</sup>	-
ERJT14	2.80 <sup>±0.20</sup>	3.50 <sup>±0.20</sup>	0.00							1.00 <sup>±0.10</sup>	1.0+0.10


#### Taping Reel



					(Unit : mm)
Туре	φA	φB	φC	W	Т
ERJT06					
ERJT08	180.0+0	60 min.	13.0±1.0	$9.0^{\pm 1.0}$	11.4 <sup>±1.0</sup>
ERJT14					

#### ■ Recommended Land Pattern

In case of flow soldering, the land width must be smaller than the Chip Resistor width to control the solder amount properly. Generally, the land width should be 0.7 to 0.8 times (W) of the width of chip resistor. In case of reflow soldering, solder amount can be adjusted, therefore the land width should be set to 1.0 to 1.3 times chip resistor width (W).




Туре	Dimensions (mm)					
(inches)	а	b	С			
ERJT06 (0805)	1 to 1.4	3.2 to 3.8	0.9 to 1.4			
ERJT08 (1206)	2 to 2.4	4.4 to 5	1.2 to 1.8			
ERJT14 (1210)	2 to 2.4	4.4 to 5	1.8 to 2.8			

#### ■ Recommended Soldering Conditions

Recommendations and precautions are described below.

- Recommended soldering conditions for reflow
- · Reflow soldering shall be performed a maximum of two times
- · Please contact us for additional information when used in conditions other than those specified.
- · Please measure the temperature of the terminals and study every kind of solder and printed circuit board for solderability before actual use.



#### For soldering (Example: Sn/Pb)

	Temperature	Time
Preheating	140 °C to 160 °C	60 s to 120 s
Main heating	Above 200 °C	30 s to 40 s
Peak	235 ± 5 °C	max. 10 s

#### For lead-free soldering (Example : Sn/Ag/Cu)

	Temperature	Time	
Preheating	150 °C to 180 °C	60 s to 120 s	
Main heating	Above 230 °C	30 s to 40 s	
Peak	max. 260 °C	max. 10 s	

#### Recommended soldering conditions for flow

	For soldering		For lead-free soldering	
	Temperature	Time	Temperature	Time
Preheating	140 °C to 180 °C	60 s to 120 s	150 °C to 180 °C	60 s to 120 s
Soldering	245 ± 5 °C	20 s to 30 s	max. 260 °C	max. 10 s

#### 

The following are precautions for individual products. Please also refer to the precautions common to Fixed Resistors shown on page ER2 of this catalog.

- 1. Take measures against mechanical stress during and after mounting of Anti-Pulse Thick Film Chip Resistors (hereafter called the resistors) so as not to damage their electrodes and protective coatings.
- 2. If a transient load (heavy load in a short time) like a pulse is expected to be applied, check and evaluate the operations of the resistors when installed in your products before use.
  - Never exceed the rated power. Otherwise, the performance and/or reliability of the resistors may be impaired.
- 3. Do not use halogen-based or other high-activity flux. Otherwise, the residue may impair the resistors' performance and/or reliability.
- 4. When soldering with a soldering iron, never touch the resistors' bodies with the tip of the soldering iron. When using a soldering iron with a high temperature tip, finish soldering as quickly as possible (within three seconds at 350 °C max.).
- 5. As the amount of applied solder becomes larger, the mechanical stress applied to the resistors increases, causing problems such as cracks and faulty characteristics. Avoid applying an excessive amount of solder.
- 6. Do not apply shock to the resistors or pinch them with a hard tool (e.g. pliers and tweezers). Otherwise, the resistors' protective coatings and bodies may be chipped, affecting their performance.
- 7. Avoid excessive bending of printed circuit boards in order to protect the resistors from abnormal stress.

## Panasonic

#### 

(Common precautions for Fixed Resistors)

- When using our products, no matter what sort of equipment they might be used for, be sure to make a written agreement on the specifications with us in advance. The design and specifications in this catalog are subject to change without prior notice.
- Do not use the products beyond the specifications described in this catalog.
- This catalog explains the quality and performance of the products as individual components. Before use, check and evaluate their operations when installed in your products.
- Install the following systems for a failsafe design to ensure safety if these products are to be used in equipment where a defect in these products may cause the loss of human life or other significant damage, such as damage to vehicles (automobile, train, vessel), traffic lights, medical equipment, aerospace equipment, electric heating appliances, combustion/gas equipment, rotating equipment, and disaster/crime prevention equipment.
- \* Systems equipped with a protection circuit and a protection device
- \* Systems equipped with a redundant circuit or other system to prevent an unsafe status in the event of a single fault

#### (1) Precautions for use

- These products are designed and manufactured for general and standard use in general electronic equipment (e.g. AV equipment, home electric appliances, office equipment, information and communication equipment)
- These products are not intended for use in the following special conditions. Before using the products, carefully check the effects on their quality and performance, and determine whether or not they can be used.
  - 1. In liquid, such as water, oil, chemicals, or organic solvent
  - 2. In direct sunlight, outdoors, or in dust
  - 3. In salty air or air with a high concentration of corrosive gas, such as Cl2, H2S, NH3, SO2, or NO2
  - 4. Electric Static Discharge (ESD) Environment

These components are sensitive to static electricity and can be damaged under static shock (ESD).

Please take measures to avoid any of these environments.

Smaller components are more sensitive to ESD environment.

5. Electromagnetic Environment

Avoid any environment where strong electromagnetic waves exist.

- 6. In an environment where these products cause dew condensation
- 7. Sealing or coating of these products or a printed circuit board on which these products are mounted, with resin or other materials
- These products generate Joule heat when energized. Carefully position these products so that their heat will not affect the other components.
- Carefully position these products so that their temperatures will not exceed the category temperature range due to the effects of neighboring heat-generating components. Do not mount or place heat-generating components or inflammables, such as vinyl-coated wires, near these products.
- Note that non-cleaning solder, halogen-based highly active flux, or water-soluble flux may deteriorate the performance or reliability of the products.
- Carefully select a flux cleaning agent for use after soldering. An unsuitable agent may deteriorate the performance or reliability. In particular, when using water or a water-soluble cleaning agent, be careful not to leave water residues. Otherwise, the insulation performance may be deteriorated.

#### (2) Precautions for storage

The performance of these products, including the solderability, is guaranteed for a year from the date of arrival at your company, provided that they remain packed as they were when delivered and stored at a temperature of 5 °C to 35 °C and a relative humidity of 45 % to 85 %.

Even within the above guarantee periods, do not store these products in the following conditions. Otherwise, their electrical performance and/or solderability may be deteriorated, and the packaging materials (e.g. taping materials) may be deformed or deteriorated, resulting in mounting failures.

- 1. In salty air or in air with a high concentration of corrosive gas, such as Cl<sub>2</sub>, H<sub>2</sub>S, NH<sub>3</sub>, SO<sub>2</sub>, or NO<sub>2</sub>
- 2. In direct sunlight

#### <Package markings>

Package markings include the product number, quantity, and country of origin. In principle, the country of origin should be indicated in English.