

PLUG-IN RELAY 2 CHANGEOVER CONT. DC 24V



General technical details:		
Type of voltage		DC
Control supply voltage		
<ul style="list-style-type: none"> • for DC / rated value 		
<ul style="list-style-type: none"> • minimum 	V	24
<ul style="list-style-type: none"> • maximum 	V	24
Number of NC contacts		
<ul style="list-style-type: none"> • for auxiliary contacts 		0
Number of NO contacts		
<ul style="list-style-type: none"> • for auxiliary contacts 		0
Number of changeover contacts		
<ul style="list-style-type: none"> • for auxiliary contacts 		2
Operating current / of the auxiliary contacts		
<ul style="list-style-type: none"> • at DC-13 		
<ul style="list-style-type: none"> <ul style="list-style-type: none"> • at 24 V 	A	8
<ul style="list-style-type: none"> • at AC-15 		
<ul style="list-style-type: none"> <ul style="list-style-type: none"> • at 230 V 	A	5
Design of the switching function		
<ul style="list-style-type: none"> • guided 		changeover switch
		No
Switching behaviour		monostable

Mechanical design:

Design of the electrical connection		screw-type terminals
Design of the relay operating mechanism		poled
Product component / jumper socket		No
Width	mm	22.5
Height	mm	28
Depth	mm	35

Certificates/approvals:

General Product Approval

other



[Declaration of Conformity](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

CAX-Online-Generator

<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/LZX:PT270024/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=LZX:PT270024

last change:

Jun 16, 2014