Power Choke Coil for Automotive application

PCC-M0630M (MC) **PCC-M0754M (MC)** PCC-M0854M (MC) PCC-M0850M (MC) PCC-M1054M (MC) PCC-M1050M (MC)

Series: PCC-M0530M (MC) PCC-M0540M (MC) **PCC-M0645M (MC)**

PCC-M1050ML (MC) PCC-M1060ML (MC)



Inc (A)

Realize high heat resistance and high reliability with metal composite core(MC)

Panasonic

Industrial Property : patents 21 (Registered 2/Pending 19)

Features Fig.1 Inductance v.s. DC current, Temp. High heat resistance : Operation up to 150 °C High-reliability : High vibration resistance due to newly developed ETQP5M470YFM(reference) integral construction and severe reliability condition 60.0 of automotive application is covered 50. High bias current : Excellent inductance stability by using ferrous alloy <u> </u> 40.0 magnetic material(Fig.1) 30.0 Temp. stability : Excellent inductance stability in wide temp. range (Fig.1) 25 °C Low buzz noise 100 °C : New metal composite core technology ਦੋ 20.0 125 °C • High efficiency : Low RDC of winding and low eddy-current loss of the core 150 °C 10.0 AEC-Q200 qualified 0.0L 0.0 RoHS compliant 2.0 2.5 3.0

Recommended Applications


- Noise filter for various drive circuitry requiring high temp. operation and peak current handling capability
- DC/DC converters

Standard Packing Quantity (Minimum Quantity/Packing Unit)

1,000 pcs./box (2 reel) : PCC-M0645M, M0754M, M0854M, M0850M, M1054M, M1050M,

M1050ML, M1060ML

2,000 pcs./box (2 reel) : PCC-M0530M, M0540M, M0630M



Operatin	g temperature range	Tc : -40 °C to +150 °C(Including self-temperature rise)
Storage condition	After PWB mounting	ic40 C to +150 C(including sen-temperature rise)
Storage condition	Before PWB mounting	Ta : -5 °C to +35 °C 85%RH max.

Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use Should a safety concern arise regarding this product, please be sure to contact us immediately

1. Series PCC-M0530M/PCC-M0540M (ETQP3M VFP/ETQP4M VFP)

Standard Parts								
	Inductance *1		DCR (at 20 °C) (mΩ)		Rated Current (Typ. : A)			
Series	Part No.	LO	Tolerance	Тур.	Tolerance	∆T=	40K	△L=-30%
		(µH)	(%)	(max.)	(%)	(*2)	(*3)	(*4)
PCC-M0530M	ETQP3M2R2YFP	2.2		22.6 (24.8)		4.8	5.8	10.9
[5.5×5.0×3.0(mm)]	ETQP3M3R3YFP	3.3	±20	31.3 (34.4)	. 10	4.1	5.0	8.6
PCC-M0540M	ETQP4M4R7YFP	4.7	1 ±20	36.0 (39.6)	±10	4.0	4.8	7.7
[5.5×5.0×4.0(mm)]	ETQP4M220YFP	22]	163 (179)		1.9	2.3	3.1

(*1) Measured at 100 kHz.

(*2) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on four-layer PWB (1.6 mm FR4) and measured at room temperature. See also (*5)


(*3) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on multilayer PWB with high heat dissipation performance. Note: Heat radiation constant are approx. 52 K/W measured on 5.5×5.0×3.0 mm case size and approx. 48 K/W measured on 5.5×5.0×4.0 mm case size. See also (*5)


(*4) Saturation rated current : DC current which causes L(0) drop -30 %.

(*5) Within a suitable application, the part's temperature depends on circuit design and certain heat dissipation conditions. This should be double checked in a worst case operation mode. In normal case, the max.standard operating temperature of +150 °C should not be exceeded.


For higher operating temperature conditions, please contact Panasonic representative in your area.

Performance Characteristics (Reference)











PWB condition A : Four-layer PWB (1.6 mm FR4), See also (*2) PWB condition B : Multilayer PWB with high heat dissipation performance. See also (*3)





Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.

2. Series PCC-M0630M/PCC-M0645M (ETQP3M VFN/ETQP4M VFN)

Standard Parts								
		Inductance *1		DCR (at 20 °C) (mΩ)		Rated Current (Typ. : A)		
Series	Part No.	LO	Tolerance	Тур.	Tolerance	∆T=	:40K	△L=-30%
		(µH)	(%)	(max.)	(%)	(*2)	(*3)	(*4)
PCC-M0630M	ETQP3MR68YFN	0.68		6.3 (6.9)		9.8	12.0	24.0
[6.5×6.0×3.0(mm)]	ETQP3M1R0YFN	1.0]	7.9 (8.7)] [8.8	10.7	20.0
	ETQP4M6R8YFN	6.8	±20	39.3 (43.2)	±10	4.1	5.2	10.0
PCC-M0645M [6.5×6.0×4.5(mm)]	ETQP4M100YFN	10		54.2 (59.6)] [3.3	4.5	8.3
	ETQP4M470YFN	47		210 (231)]	1.8	2.2	3.8

(*1) Measured at 100 kHz.

(*2) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on four-layer PWB (1.6 mm FR4) and measured at room temperature. See also (*5)

(*3) DC current which causes temperature rise of 40 K. Partsare soldered by reflow on multilayer PWB with high heat dissipation performance. Note: Heat radiation constant are approx. 44 K/W measured on 6.5×6.0×3.0 mm case size and approx. 37 K/W measured on 6.5×6.0×4.5 mm case size. See also (*5)

(*4) Saturation rated current : DC current which causes L(0) drop -30 %.


(*5) Within a suitable application, the part's temperature depends on circuit design and certain heat dissipation conditions. This should be double checked in a worst case operation mode.

In normal case, the max.standard operating temperature of +150 °C should not be exceeded.


For higher operating temperature conditions, please contact Panasonic representative in your area.


Performance Characteristics (Reference)


Inductance vs DC Current




• Case Temperature vs DC Current







PWB condition A : Four-layer PWB (1.6 mm FR4), See also (*2) PWB condition B : Multilayer PWB with high heat dissipation performance. See also (*3)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use Should a safety concern arise regarding this product, please be sure to contact us immediately.

3. Series PCC-M0754M (ETQP5M VFM)

Standard Parts								
		Inductance *1		DCR (at 20 °C) (mΩ)		Rated Current (Typ. : A)		
Series	Part No.	LO	Tolerance	Тур.	Tolerance	∆T=	40K	∆L=–30%
		(µH)	(%)	(max.)	(%)	(*2)	(*3)	(*4)
	ETQP5M4R7YFM	4.7		20(23)		6.3	8.0	13.1
	ETQP5M100YFM	10]	37.6(41.3)		4.7	5.7	10.6
PCC-M0754M [7.5×7.0×5.4(mm)]	ETQP5M220YFM	22	±20	92(102)	±10	3.0	3.7	5.8
	ETQP5M330YFM	33]	120(132)		2.6	3.3	4.8
	ETQP5M470YFM	48]	156(172)]	2.3	2.9	4.1

(*1) Measured at 100 kHz.

(*2) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on four-layer PWB (1.6 mm FR4) and measured at room temperature. See also (*5)

(*3) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on multilayer PWB with high heat dissipation performance. Note: Heat radiation constant is approx. 31 K/W measured on 7.5×7.0×5.4 mm case size. See also (*5) (*4) Saturation rated current : DC current which causes L(0) drop -30 %.

(*5) Within a suitable application, the part's temperature depends on circuit design and certain heat dissipation conditions. This should be double checked in a worst case operation mode.

In normal case, the max.standard operating temperature of +150 °C should not be exceeded.

10


0

0


For higher operating temperature conditions, please contact Panasonic representative in your area.


Performance Characteristics (Reference)


Inductance vs DC Current



Case Temperature vs DC Current










3


2 IDC (A)

PWB condition B : Multilayer PWB with high heat dissipation performance. See also (*3)



2 З 4 5 6

IDC (A)



Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use Should a safety concern arise regarding this product, please be sure to contact us immediately

30

20

10

0

4. Series PCC-M0854M/PCC-M0850M (ETQP5M VFK/ETQP5M VGK)

Standard Parts								
		Inductance *1		DCR (at 20 °C) (mΩ)		Rated Current (Typ. : A)		
Series	Part No.	LO	Tolerance (%)	Typ. Tolerance	∆T=40K		△L=-30%	
		(µH)		(max.)	(%)	(*2)	(*3)	(*4)
	ETQP5M2R5YFK	2.5	±20	7.6(8.4)	±10	11.9	14.0	20.1
PCC-M0854M	ETQP5M100YFK	10		33(37)		5.7	6.7	13.0
[8.5×8.0×5.4(mm)]	ETQP5M220YFK	22		63(70)		4.1	4.8	6.9
	ETQP5M470YFK	48		125(138)		2.9	3.4	5.4
PCC-M0850M [8.5×8.0×5.0(mm)]	ETQP5M101YGK	100		302(333)		1.7	2.1	3.0

(*1) Measured at 100 kHz.

(*2) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on four-layer PWB (1.6 mm FR4) and measured at room temperature. See also (*5)

(*3) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on multilayer PWB with high heat dissipation performance. Note: Heat radiation constant are approx. 27 K/W measured on 8.5×8.0×5.4 mm case size and approx. 29 K/W measured on 8.5×8.0×5.0 mm case size. See also (*5)
(*4) Saturation rated current : DC current which causes L(0) drop -30 %.


(*5) Within a suitable application, the part's temperature depends on circuit design and certain heat dissipation conditions. This should be double checked in a worst case operation mode.

In normal case, the max standard operating temperature of + 150 °C should not be exceeded.


For higher operating temperature conditions, please contact Panasonic representative in your area.


Performance Characteristics (Reference)


Inductance vs DC Current




• Case Temperature vs DC Current








PWB condition A : Four-layer PWB (1.6 mm FR4), See also (*2) PWB condition B : Multilayer PWB with high heat dissipation performance. See also (*3)





Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately. 08

5. Series PCC-M1054M/PCC-M1050M (ETQP5M VFC/ETQP5M VGC)

Standard Parts								
		Inducta	ance *1	DCR (at 20 °C) (mΩ)		Rated Current (Typ. : A)		
Series	Part No.	LO	Tolerance	Тур.	Tolerance	∆T=	40K	△L=-30%
		(µH)	(%)	(max.)	(%)	(*2)	(*3)	(*4)
	ETQP5M1R5YFC	1.45		3.8(4.2)		17.9	21.4	35.1
	ETQP5M2R5YFC	2.5		5.3(5.9)	±10	15.1	18.1	27.2
	ETQP5M3R3YFC	3.3		7.1(7.9)		13.1	15.7	22.7
PCC-M1054M [10.7×10.0×5.4(mm)]	ETQP5M4R7YFC	4.7		10.2(11.3)		10.9	13.1	20.0
	ETQP5M100YFC	10	±20	23.8(26.2)		7.1	8.5	10.7
	ETQP5M220YFC	22		45(50)		5.2	6.2	8.8
	ETQP5M330YFC	32.5		68.5(75.4)		4.2	5.0	7.6
PCC-M1050M [10.7×10.0×5.0(mm)]	ETQP5M101YGC	97		208(229)		2.2	2.7	3.0

(*1) Measured at 100 kHz.

(*2) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on four-layer PWB (1.6 mm FR4) and measured at room temperature. See also (*5)

(*3) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on multilayer PWB with high heat dissipation performance. Note: Heat radiation constant are approx. 23 K/W measured on 10.7×10.0×5.4 mm case size and approx. 26 K/W measured on 10.7×10.0×5.0 mm case size. See also (*5)

(*4) Saturation rated current : Dc current which causes L(0) drop -30 %.


(*5) Within a suitable application, the part's temperature depends on circuit design and certain heat dissipation conditions. This should be double checked in a worst case operation mode.

In normal case, the max standard operating temperature of +150 °C should not be exceeded.

For higher operating temperature conditions, please contact Panasonic representative in your area.

Performance Characteristics (Reference)

Inductance vs DC Current




6 8 10


IDC (A)


10


0 L 0


2 4












Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use Should a safety concern arise regarding this product, please be sure to contact us immediately


Power Inductors


Panasonic


• Case Temperature vs DC Current

PWB condition A : Four-layer PWB (1.6 mm FR4), See also (*2) PWB condition B : Multilayer PWB with high heat dissipation performance. See also (*3)









4 6 IDC (A) 8

10

10

0

0 2

6. Series PCC-M1050ML/PCC-M1060ML (ETQP5M VLC/ETQP6M VLC)

Standard Parts								
		Inductance *1		DCR (at 20 °C) (mΩ)		Rated Current (Typ. : A)		
Series	Part No.	LO	Tolerance	Тур.	Tolerance	∆T=	:40K	∆L=–30%
		(µH)	(%)	(max.)	(%)	(*2)	(*3)	(*4)
PCC-M1050ML	ETQP5MR68YLC	0.68		1.75(1.93)		26.3	31.5	42.0
[10.9×10.0×5.0(mm)]	ETQP5M1R0YLC	1.0	±20	2.3(2.53)	±10	23.0	27.5	38
PCC-M1060ML	ETQP6M2R5YLC	2.5		4.5(5.0)	± 10	16.3	19.6	27.0
[10.9×10.0×6.0(mm)]	ETQP6M3R3YLC	3.3]	6.0(6.6)		14.2	17.0	26.0

(*1) Measured at 100 kHz.

(*2) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on four-layer PWB (1.6 mm FR4) and measured at room temperature. See also (*5)

(*3) DC current which causes temperature rise of 40 K. Parts are soldered by reflow on multilayer PWB with high heat dissipation performance. Note: Heat radiation constant are approx. 23 KW measured on 10.9×10.0×5.0 mm case size and approx. 23 K/W measured on 10.9×10.0×6.0 mm case size. See also (*5)


(*4) Saturation rated current : Dc current which causes L(0) drop -30 %.


(*5) Within a suitable application, the part's temperature depends on circuit design and certain heat dissipation conditions. This should be double checked in a worst case operation mode. In normal case, the max standard operating temperature of +150 °C should not be exceeded.

For higher operating temperature conditions, please contact Panasonic representative in your area.

Performance Characteristics (Reference)

Inductance vs DC Current







IDC (A)

Case Temperature vs DC Current

PWB condition A : Four-layer PWB (1.6 mm FR4), See also (*2) PWB condition B : Multilayer PWB with high heat dissipation performance. See also (*3)







Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use Should a safety concern arise regarding this product, please be sure to contact us immediately

Dimensions in mm (not to scale)


Dimensional tolerance unless noted : ±0.5




Series PCC-M0630M Series PCC-M0645M (ETQP3MDDYFN/ETQP4MDDYFN)



Series PCC-M0754M (ETQP5MDDDYFM)




Series PCC-M0854M Series PCC-M0850M (ETQP5MDDDYFK/YGK)




Series PCC-M1054M Series PCC-M1050M (ETQP5MDDDYFC/YGC)

Inductance



Series PCC-M1050ML Series PCC-M1060ML (ETQP5MDDJLC/ETQP6MDDJLC)




Design and specifications are each subject to change without notice. Ask factory for the current technical specifications before purchase and/or use. Should a safety concern arise regarding this product, please be sure to contact us immediately.


Recommended Land Pattern in mm (not to scale)

Dimensional tolerance unless noted : ±0.5

Series PCC-M0530M Series PCC-M0540M (ETQP3MUUUYFP/ETQP4MUUUYFP)

6.1 3.6 6.0 K 2.2 7.2





Series PCC-M0630M

Series PCC-M0645M (ETQP3MUUUYFN/ETQP4MUUUYFN)


8.8 The same as the left

28




Series PCC-M0754M

(ETQP5MDDVFM)



The same as the left.

Series PCC-M0854M Series PCC-M0850M (ETQP5MDDYFK/YGK)



Don't wire on the pattern on shaded portion the PWB

Series PCC-M1054M Series PCC-M1050M (ETQP5MDDYFC/YGC)

11.7 4.0 6.1 13.7 The same as the left

Series PCC-M1050ML Series PCC-M1060ML $(ETQP5M \square \square YLC/ETQP6M \square \square YLC)$

> 11.9 0 ÷ // V 6.5 13.9

The same as the left.

■ As for Packaging Methods, Soldering Conditions and Safety Precautions (Power Choke Coils for Automotive application),

Please see Data Files