HellermannTyton

596-00326

Article Number: 596-00326

Pre-Printed Solar Label, 3.75" X 2", BIPOLAR SOLAR ARRAY, Red, 50/pkg







Base Data

Local Order Number 596-00326

Type BIPOLARPV

Color Red (RD)

- Features and Benefits Made with UV stable inks and materials for durability and weather resistance.
 - The labels are supplied with aggresive adhesive to ensure long life.
 - · Solar Installation labels meet NEC & IFC standards for printed text, character height, color and outdoor UV stability

to pass inspections.

Product Description HellermannTyton pre-printed Solar Installation labels are designed to meet the requirements of the 2014 National Electrical Code (NEC 2014) and the 2012 International Fire Code (IFC 2012) as well as being acceptable to the Authority Having Jurisdiction (AHJ). Labels are made with durable UV stable materials and adhesives that are designed to stick to both baked enamel and powder coat surfaces. Where applicable, labels are made using reflective materials for first responder safety. Some pre-printed labels are printable using a thermal transfer printer

when variable voltage or series data must be printed and displayed.

Technical Description 3.75" X2" White text on red background that reads as: "WARNING - BIPOLAR PHOTOVOLTAIC ARRAY. DISCONNECTION OF NEUTRAL OR GROUNDED CONDUCTORS MAY RESULT IN OVERVOLTAGE ON ARRAY

OR INVERTER." - 50 per roll.

Short Description Pre-Printed Solar Label, 3.75" X2", BIPOLAR SOLAR ARRAY, Red, 50/pkg

Product Dimensions

Width W (Imperial) 3.75 "

Width W (Metric) 92.25 mm

Height H (Imperial) 2.0 "

Height H (Metric) 50.8 mm

Logistics and Packaging

Quantity Per reel

Package Quantity (Metric) 50

Material and Specifications

Material Vinyl

Material Shortcut VL

Adhesive Acrylic

Adhesive Shortcut Acrylic

Adhesive Operating Temperature -40°F to +174°F (-40°C to +79°C)

Halogenfree

Operating Temperature -40°F to +174°F (-40°C to +79°C)

ROHS Compliant Yes

UL Recognized (US) Yes

© HellermannTyton 2015