

OT125F3

**ABB contact for United States
of America**

General Information

Extended Product Type:	OT125F3
Product ID:	1SCA105033R1001
EAN:	6417019391632
Catalog Description:	OT125F3 Switch-disconnector
Long Description:	Front operated switch-disconnector. Types OT 16...125 include protected terminal clamps, IP 20.



Categories

Products » Low Voltage Products and Systems » Switches » Switch
Disconnectors

Ordering

EAN:	6417019391632
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85365080

Dimensions

Product Net Width:	70 mm
Product Net Height:	100 mm
Product Net Depth:	74 mm
Product Net Weight:	0.4 kg

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	81 mm
Package Level 1 Height:	86 mm
Package Level 1 Length:	112 mm
Package Level 1 Gross Weight:	0.4 kg
Package Level 1 EAN:	6417019391632

Environmental

RoHS Status:	Planned to follow EU Directive 2002/95/EC August 18, 2005 and amendment after 2009 Q3
---------------------	---

Technical UL/CSA

Ampere Rating UL/CSA:	100 A
Horse Power Rating UL/CSA:	acc. to UL 200V 25 Hp acc. to UL 208V 25 Hp acc. to UL 240V 30 Hp acc. to UL 480V 50 Hp

acc. to UL 600V 50 Hp

Additional Information

Cable Cross-Section:	10...70 mm ²
Conventional Free-air Thermal Current (I_{th}):	q=40°C 125 A
Conventional Thermal Current (I_{the}):	Fully Enclosed 125 A
Earthing Switch Type:	No Additional Type
Handle Type:	None
IIT Publishing Status:	Level 0 - Information enabled
Includes:	None
Mounting Type:	Modular
Number of Poles:	3
Operating Mechanism:	Mechanism on top of the switch
Operating Mode:	Front Operated
Pollution Degree:	3
Position of Line Terminals:	Top in - bottom out
Power Loss:	Per Pole 0.36 W
Product Main Type:	OT
Product Name:	Switch-disconnectors
Rated Impulse Withstand Voltage (U_{imp}):	8 kV
Rated Insulation Voltage (U_i):	750 V
Rated Operational Current AC-21A (I_e):	(380 ... 415V) 125 A (500V) 125 A (690V) 125 A
Rated Operational Current AC-22A (I_e):	(380 ... 415 V) 125 A (500 V) 125 A (690 V) 125 A
Rated Operational Current AC-23A (I_e):	(690 V) 50 A (500 V) 70 A (380 ... 415 V) 90 A
Rated Operational Power AC-23A (P_e):	(220 ... 240V) 22 kW (400V) 45 kW (415V) 45 kW (500V) 45 kW (690V) 45 kW
Rated Operational Voltage:	750 V
Rated Short-time Withstand Current (I_{cw}):	for 1.0s 2.5 kiloampere rms
Special Functions:	No
Standards:	IEC
Terminal Type:	Screw Terminals

Certificates and Declarations (Document Number)

Declaration of Conformity - CE:	1SCC301168D0201
RoHS Information:	1SCC301183D0201

Classifications

E-nummer:	3170943
ETIM 5.0:	EC000216 - Switch disconnecter
Object Classification Code:	Q
