



Main

Range	TeSys
Product or component type	Contacteur coil
Device short name	LX1D2
Control circuit type	AC 50/60 Hz
[Uc] control circuit voltage	48 V AC 50/60 Hz
Average resistance	25 Ohm at 68 °F (20 °C)
Inductance of closed circuit	1 H
Product compatibility	LC1D09...D18

Complementary

Coil technology	Without built-in suppressor module
Control circuit voltage limits	0.8...1.1 Uc at <= 131 °F (55 °C) operational 50/60 Hz
Inrush power in VA	70 VA at 68 °F (20 °C) (cos φ 0.75) 50/60 Hz
Hold-in power consumption in VA	8 VA at 68 °F (20 °C) (cos φ 0.3) 50/60 Hz

Environment

product weight	1.54 lb(US) (0.7 kg)
----------------	----------------------

Contractual warranty

Warranty period	18 months
-----------------	-----------

The information provided in this documentation contains general descriptions and/or technical characteristics of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.