

# TiX1000, TiX660 and TiX640 Infrared Cameras

## The Fluke Expert Series

### Technical Data



#### PREMIUM IMAGE QUALITY

##### SPATIAL RESOLUTION

###### TiX1000

0.6 mRad

###### TiX660 and TiX640

0.8 mRad

##### RESOLUTION

###### TiX1000

1024 x 768 (786,432 pixels)

###### TiX660 and TiX640

640 x 480 (307,200 pixels)

##### SUPER RESOLUTION MODE

###### TiX1000

2048 x 1536 (3,145,728 pixels)

###### TiX660

1280 x 960 (1,228,800 pixels)

##### FIELD OF VIEW

###### TiX1000

32.4 ° x 24.7 ° (1.0/30 mm)

###### TiX660 and TiX640

30.9 ° x 23.1 ° (1.0/30 mm)

##### TEMPERATURE RANGE

-40 to 2000 °C (-40 to 3632 °F)


TiX1000 and TiX660

-40 to 1200 °C (-40 to 2192 °F) TiX640

#### Fluke Infrared Cameras Experience. Performance. Confidence.

Take the guesswork out of your inspection and analysis.

- **Up to 10 times the on-camera pixels than standard 320x240 cameras** (1024x768 resolution, 786,432 pixels)
- **Enhanced image quality and temperature measurement accuracy**—get 4 times the resolution and pixels than standard mode with SuperResolution (up to 3,145,728 pixels)
- **Work from greater distances.** See a 5 mm (0.2 in) target from 35 m (115 ft) away using the TiX1000 with the Super Telephoto lens
- **Get a premium in-field viewing experience** for quick issue identification with the large 5.6 inch high resolution LCD screen
- **Save time focusing** with the most advanced focus options available for consistently in focus image: LaserSharp® Auto Focus, auto focus, manual and EverSharp multifocal recording features—available in one camera
- **The Fluke Expert Series offers the best flexibility of the entire Fluke infrared camera portfolio** to capture spectacular images close up or from a distance. The TiX1000, TiX660 and TiX640 are compatible with 8 lens options (2x and 4x telephoto lenses, 2 wide angle lenses, 3 macro lenses and 1 standard lens) so great images can be captured despite certain obstacles.



Electrical utility distribution lines

	TiX1000		TiX660		TiX640
<b>Key features</b>					
IFOV (spatial resolution)	0.6 mRad		0.8 mRad		0.8 mRad
Image resolution (pixel)	1024 x 768 (786,432 pixels)	2048 x 1536 (3,145,728 pixels) (SuperResolution mode)	640 x 480 (307,200 pixels)	1280 x 960 (1,228,800 pixels) (SuperResolution mode)	640 x 480 (307,200 pixels)
Frame rate (@ max. image resolution)	30 Hz	–	60 Hz	–	60 Hz
SuperResolution & Dynamic SuperResolution (resolution enhancement)	Yes, MicroScan technology quadruples IR measurement pixels.				No
Subwindowing modes available: (add-on at time of order– subwindowing options are not available on 9 Hz models)	Option 1: 640 × 480 (60 fps) Option 2: 384 × 288 (120 fps) Option 3: 1024 × 96 (240 fps)		Option 1: 384 × 288 (120 fps) Option 2: 640 × 120 (240 fps)		
Field of View (FOV) w/standard 30mm lens	32.4° x 24.7°		30.9° x 23.1°		
Thermal sensitivity [NETD]	≤ 0.05 °C at 30 °C target temp (50 mK)		≤ 0.03 °C at 30 °C target temp (30 mK)		
Spectral range	7.5 μm to 14 μm				
<b>IR-Fusion® technology</b>					
AutoBlend™	Yes				
Viewing modes	Picture-in-picture, continuous blending, color alarms (above and below user defined temperatures)				
<b>Focus systems</b>					
LaserSharp® Auto Focus	Yes			No	
Auto focus	Yes				
Manual focus	Yes, with the touch of a finger for tighter views.				
EverSharp multifocal recording	Yes. Multifocal recording captures images from different focal distances and combines them into one image displaying each object sharply for the best image quality.				
<b>Temperature measurement</b>					
Temperature measurement range	-40 °C to +1200 °C (-40 °F to 2192 °F), High temperature option–request at time of order: up to 2000 °C (3632 °F)			-40 °C to +1200 °C (-40 °F to 2192 °F)	
Measurement accuracy	+/- 1.5 °C or +/- 1.5 %				
Correction functions	Laser rangefinder based distance correction, emissivity (manual or material table)			Emissivity (manual or material table)	
	Transmissivity, ambient temperature, humidity (option)				
<b>Data storage and image capture</b>					
Image / video storage	SDHC memory card				
Interfaces for image/data transfer	Camera data ports: Image transfer: SD card, USB 2.0, video output DVI-D (HDMI), GigE vision and RS232 available in 2015. SmartView® software: SD card, USB 2.0, GigE Vision and RS232 available in 2015.				
<b>General specifications</b>					
Laser pointer	Yes, laser class: 2				
Laser distance meter	Accuracy: ± 1.5 mm, range: 70 m (230 ft.), wavelength: 635 nm (red), laser class: 2			None	
Display	Extra-large 5.6" color TFT display, 1280 × 800 pixel resolution, suitable for daylight operation				
Geo-localization	Built-in GPS for geo-referencing				
Digital visible light camera	Up to 8 Megapixel resolution for image and video recording				
Digital zoom	Up to 32x digital zoom				
Text annotation	Yes				
Voice annotation	Yes				
Audio	Integrated microphone and loudspeaker for voice annotations				
A/D conversion	16 bit				
Power supply	External: 12 VDC ... 24 VDC, Battery: standard Li-Ion video camera battery				
Replaceable Smart Batteries with LED level indicator	Two			One	
Operating temperature	-25 °C to +55 °C (-13 °F to 131 °F)				
Storing temperature	-40 °C to +70 °C (-40 °F to 158 °F)				
Humidity	Relative humidity 10 % to 95 %, non-condensing				
Shock	Operational: 25G, IEC 68-2-29				
Vibration	Operational: 2G, IEC 68-2-6				
Protection class	IP54				
Ergonomics	Camcorder w/ handle			Camcorder	

	TiX1000	TiX660	TiX640
<b>General specifications (continued)</b>			
Viewfinder	Tilttable LCoS color viewfinder display, 800 × 600 pixel resolution		No
Dimensions (L x W x H, with standard 30 mm lens)	210 mm × 125 mm × 155 mm (8.25 in x 4.9 in x 6.1 in)		206mm x 125mm x 139mm (8.1 in x 4.9 in x 5.5 in)
Weight (with standard 30 mm lens)	1.95 kg (4.3 lb)		1.4 kg (3.1 lb)
Measurement functions (selection)	Multiple measurement spots & regions of interest (ROIs), hot/cold spot detection, isotherms, profiles, differences		
Automatic functions (selection)	Focus, image, level, range, NUC, lens recognition, image optimization, alarm sequence		
SmartView® software	Yes		
Supported languages	Czech, Dutch, English, Finnish, French, German, Hungarian, Italian, Japanese, Korean, Polish, Portuguese, Russian, Simplified Chinese, Spanish, Swedish, Traditional Chinese and Turkish		

### Available optional lenses\* with IP54-proof bayonet mount



Fluke Model	Lens description	Focal distance (mm)	Focus (m)	1024 x 768		640 x 480	
				iFOV (mRad)	FOV (°)	iFOV (mRad)	FOV (°)
<b>FLK-Xlens/Sup-Wide</b>	Super wide-angle lens	7.5	0.17	2.3	135.8 x 101.4	3.3	128.9 x 92.7
<b>FLK-Xlens/Wide</b>	Wide-angle lens	15	0.47	1.1	67.8 x 50.7	1.7	62.3 x 46.4
<b>FLK-Xlens/Stan</b>	Normal lens	30	0.72	0.6	32.4 x 24.7	0.8	30.9 x 23.1
<b>FLK-Xlens/Tele</b>	Telephoto lens	60	1.99	0.3	16.4 x 12.4	0.4	14.9 x 11.3
<b>FLK-Xlens/SupTele</b>	Super telephoto lens	120	6.58	0.1	8.1 x 6.2	0.2	7.5 x 5.7

Fluke Model	Lens description	Focal distance (mm)	Focus (mm)	1024 x 768		640 x 480	
				FOV (°) (mRad)	Resolution (µm)	FOV (°) (mRad)	Resolution (µm)
<b>FLK-Xlens/Macro1</b>	Close-up 0.2x	For 30	137.4	85.5 x 63.2	81	78.1 x 57.9	119
<b>FLK-Xlens/Macro2</b>	Close-up 0.5x	For 30	47.4	34.3 x 25.3	32	31.3 x 23.2	47
<b>FLK-Xlens/Macro3</b>	Close up 0.5x	For 60	100	35.1 x 26.5	35	32.3 x 24.4	50

\*Optional lenses must be calibrated to the individual camera. If lens purchase is post camera purchase, the camera will need to be returned for calibration with the lens.

## Ordering information

**FLK-TiX1000 30HzNFC** Thermal Imager; 1024x768;  
Non-FC 30 Hz

**FLK-TiX660 60HzNFC** Thermal Imager; 640x480;  
Non-FC 60 Hz

**FLK-TiX640 60HzNFC** Thermal Imager; 640x480;  
Non-FC 60 Hz


**FLK-TiX1000 9Hz NFC** Thermal Imager; 1024x768;  
Non-FC; 9 Hz

**FLK-TiX660 9Hz NFC** Thermal Imager; 640x480;  
Non-FC; 9 Hz

**FLK-TiX640 9Hz NFC** Thermal Imager; 640x480;  
Non-FC; 9 Hz

### Included with product


These infrared cameras are shipped with a rechargeable battery (2 for TiX1000 and TiX660; 1 for TiX640), battery charger and adapter, AC adapter, SD card, SD card reader, protective lens cap, hand strap, neck strap, carrying case, warranty card, safety instructions, calibration certificate, CD includes product manuals in English, Chinese, German, Portuguese, Spanish, French, Italian, Korean, Japanese, Russian and Turkish (printed in English and Chinese) and SmartView® software. (Software is also available via download at [www.fluke.com/smartviewdownload](http://www.fluke.com/smartviewdownload)).



**Steam vents under city street**



**Cement manufacturing facility**



**Printed circuit board assembly inspection**

**Fluke.** *Keeping your world up and running.*®

**Fluke Corporation**  
PO Box 9090, Everett, WA 98206 U.S.A.

**Fluke Europe B.V.**  
PO Box 1186, 5602 BD  
Eindhoven, The Netherlands

**Modification of this document is not permitted without written permission from Fluke Corporation.**

### For more information call:

In the U.S.A. (800) 443-5853 or  
Fax (425) 446-5116  
In Europe/M-East/Africa +31 (0)40 267 5100 or  
Fax +31 (0)40 267 5222  
In Canada (800)-36-FLUKE or  
Fax (905) 890-6866  
From other countries +1 (425) 446-5500 or  
Fax +1 (425) 446-5116  
Web access: <http://www.fluke.com>

©2014 Fluke Corporation.  
Specifications subject to change without notice.  
8/2014 6003154c-en