

UltraMax® Professional series

Introducing the UltraMax® Professional series, our highest-efficiency, longest-lasting, premium ballasts. These multi-volt control ballasts offer more than 90 percent efficiency.

Product Code	Old Description	New Description	Extended Description	Line Volts	# of Lamps	Lamp Type	Input Watts	Nominal Line Amps	Ballast Factor	Power Factor	Harmonic Total	Crest Factor	Minimum Starting Temp.
4 FT PREMIUM ULTRAMAX INSTANT START BALLAST													
72258	GE132MAX-L/ULTRA	GE132MAXP-L-ULTRA	1- F32T8 120 to 277V L .77BF	120-277	1	F32T8	25	0.21/0.09	0.77	0.99/0.96	<= 9%	<1.4%	-22° F
				120-277	1	F28T8	22/20	0.20/0.08	0.77	0.93/.094	<=11%	<1.4%	60° F
				120-277	1	F32T8/25W	21	0.18/0.08	0.77	0.99/0.97	<=10%	<1.4%	60° F
72259	GE132MAX-N/ULTRA	GE132MAXP-N-ULTRA	1- F32T8 120 to 277V N .87 BF	120-277	1	F32T8	28	0.23/0.10	0.87	0.99/0.96	<=6%	<1.4%	-22° F
				120-277	1	F28T8	25	0.21/0.09	0.88	0.99/0.95	<=9%	<1.4%	60° F
				120-277	1	F32T8/25W	23	0.19/0.09	0.88	0.99/0.97	<=10%	<1.4%	60° F
63885	GE132MAX-H/ULTRA	GE132MAXP-H-ULTRA	1- F32T8 120 to 277V H 1.18 BF	120-277	1	F32T8	37	0.31/0.14	1.18	0.99/.96	<=6%	<1.4%	-22° F
				120-277	1	F28T8	33	0.29/0.13	1.17	0.99/0.97	<=9%	<1.4%	60° F
				120-277	1	F32T8/25W	30	0.25/0.11	1.18	0.99/0.97	<=10%	<1.4%	60° F
72262	GE232MAX-L/ULTRA	GE232MAXP-L-ULTRA	2 or 1- F32T8 120 to 277V L .77 BF	120-277	2	F32T8	49/48	0.42/0.18	0.77	0.99/0.98	<=8%	<1.4%	-22° F
				120-277	2	F28T8	43	0.36/0.16	0.77	0.99/0.98	<=9%	<1.4%	60° F
				120-277	2	F32T8/25W	38	0.32/0.14	0.77	0.99/0.98	<=10%	<1.4%	60° F
74096	GE232MAX347-L	GE232MAXP-L-347	2 or 1- F32T8 347V L .77 BF	347	2	F32T8	48	0.14	0.77	0.99	<=5%	<1.4%	-22° F
				347	2	F28T8	42	0.12	0.74	0.98	<=7%	<1.4%	60° F
				347	2	F32T8/25W	37	0.11	0.74	0.98	<=7%	<1.4%	60° F
72266	GE232MAX-N/ULTRA	GE232MAXP-N-ULTRA	2 or 1- F32T8 120 to 277V N .88 BF	120-277	2	F32T8	54/53	0.47/0.20	0.87	0.99	<=8%	<1.4%	-22° F
				120-277	2	F28T8	49/48	0.41/0.18	0.87	0.99	<=8%	<1.4%	60° F
				120-277	2	F32T8/25W	44/43	0.37/0.16	0.87	0.99/0.98	<=10%	<1.4%	60° F
74093	GE232MAX347-N	GE232MAXP-N-347	2 or 1- F32T8 347V N .88 BF	347	2	F32T8	53	0.15	0.87	0.99	<=5%	<1.4%	-22° F
				347	2	F28T8	46	0.14	0.84	0.99	<=6%	<1.4%	60° F
				347	2	F32T8/25W	42	0.12	0.84	0.99	<=6%	<1.4%	-22° F
71421	GE232MAX-N+/ULTRA	GE232MAXP-N+ ULTRA	2 or 1- F32T8 120 to 277V N+ 1.0 BF	120-277	2	F32T8	62/61	0.51/0.23	1.0	0.99/0.96	<=10%	<1.4%	-22° F
				120-277	2	F28T8	55/54	0.46/0.20	1.0	0.99/0.96	<=10%	<1.4%	50° F
				120-277	2	F32T8/25W	46	0.38/0.17	1.01	0.99/0.98	<=10%	<1.4%	60° F
73190	GE232MAX-H/ULTRA	GE232MAXP-H-ULTRA	2 or 1- F32T8 120 to 277V H 1.18 BF	120-277	2	F32T8	74/73	0.62/0.27	1.18	0.99/0.97	<=10%	<1.4%	-22° F
				120-277	2	F28T8	64/63	0.52/0.24	1.18	0.99/0.97	<=10%	<1.4%	60° F
				120-277	2	F32T8/25W	60	0.51/0.22	1.18	0.99/0.98	<=10%	<1.4%	60° F
74109	GE232MAX347-H	GE232MAXP-H-347	2 or 1- F32T8 347V H 1.18 BF	347	2	F32T8	70	0.20	1.18	0.99	<=4%	<1.4%	-22° F
				347	2	F28T8	63	0.12	1.15	0.95	<=17%	<1.4%	60° F
				347	2	F32T8/25W	56	0.16	1.12	0.99	<=5%	<1.4%	60° F
62718	GE232MAX480-H	GE232MAXP-H-480	2 or 1- F32T8 480V H 1.18 BF	480	2	F32T8	73	0.16	1.18	0.95	<=10%	<1.4%	-22° F
				480	2	F28T8	64	0.14	1.13	0.92	<=10%	<1.4%	50° F
				480	2	F32T8/25W	59	0.13	1.11	0.92	<=10%	<1.4%	50° F
78621	GE332MAX-L/ULTRA	GE332MAXP-L-ULTRA	3 or 2- F32T8 120 to 277V L .77 BF	120-277	3	F32T8	72/71	0.60/0.26	0.77	0.99/0.97	<=10%	<1.4%	60° F
				120-277	3	F28T8	64/63	0.54/0.24	0.77	0.99/0.97	<=10%	<1.4%	50° F
				120-277	3	F32T8/25W	58/57	0.49/0.21	0.77	0.99/0.98	<=10%	<1.4%	60° F
74097	GE332MAX347-L	GE332MAXP-L-347	2 or 1- F32T8 347V L .77 BF	347	3	F32T8	71	0.21	0.77	0.99	<=4%	<1.4%	-22° F
				347	3	F28T8	63	0.18	0.74	0.99	<=5%	<1.4%	60° F
				347	3	F32T8/25W	55	0.16	0.73	0.99	<=5%	<1.4%	60° F
78623	GE332MAX-N/ULTRA	GE332MAXP-N-ULTRA	3 or 2- F32T8 120 to 277V N .87 BF	120-277	3	F32T8	82/80	.69/.30	0.87	.99/.98	<=10%	<1.4%	-22
				120-277	3	F28T8	71/70	.61/.28	0.87	.99/.98	<=10%	<1.4%	50F
				120-277	3	F32T8/25W	65/64	.55/.24	0.87	.99/.97	<=10%	<1.4%	50F
74094	GE332MAX347-N	GE332MAXP-N-347	2 or 1- F32T8 347V N.87 BF	347	3	F32T8	79	0.23	0.87	0.99	<=5%	<1.4%	-22
				347	3	F28T8	70	0.20	0.84	0.99	<=4%	<1.4%	60F
				347	3	F32T8/25W	63	0.18	0.84	0.99	<=4%	<1.4%	60F
71422	GE332MAX-N+/ULTRA	GE332MAXP-N+ ULTRA	3 or 2- F32T8 120 to 277V N 1.0 BF	120-277	3	F32T8	91/90	.77/.33	1.0	.99/.98	<=15%	<1.4%	0
				120-277	3	F28T8	83/82	.69/.30	1.0	.99/.98	<=15%	<1.4%	50F
				120-277	3	F32T8/25W	76/75	.64/.28	1.0	.99/.98	<=15%	<1.4%	60F
78619	GE332MAX-H/ULTRA	GE332MAXP-H-ULTRA	3 or 2- F32T8 120 to 277V H 1.18 BF	120-277	3	F32T8	106/104	.89/.38	1.18	.99/.98	<=10%	<1.4%	-22
				120-277	3	F28T8	95/94	.80/.35	1.18	.99/.98	<=10%	<1.4%	50F
				120-277	3	F32T8/25W	90/88	.76/.32	1.18	.99/.98	<=10%	<1.4%	50F
74111	GE332MAX347-H	GE332MAXP-H-347	3 or 2- F32T8 347 H 1.18 BF	347	3	F32T8	105	0.30	1.18	0.99	<=5%	<1.4%	-22
				347	3	F28T8	93	0.27	1.13	0.99	<=6%	<1.4%	60F
				347	3	F32T8/25W	85	0.25	1.13	0.99	<=6%	<1.4%	60F
4 FT PREMIUM ULTRAMAX INSTANT START BALLAST													

UltraMax® Professional series (cont'd.)

Product Code	Old Description	New Description	Extended Description	Line Volts	# of Lamps	Lamp Type	Input Watts	Nominal Line Amps	Ballast Factor	Power Factor	Harmonic Total	Crest Factor	Minimum Starting Temp.
62719	GE332MAX480-H	GE332MAXP-H-480	3 or 2- F32T8 480V H 1.18 BF	480	3	F32T8	108	0.23	1.18	0.95	<=10%	<1.4%	-22
				480	3	F28T8	94	0.20	1.13	0.95	<=10%	<1.4%	50F
				480	3	F32T8/25W	87	0.19	1.11	0.95	<=10%	<1.4%	50F
78625	GE432MAX-L/ULTRA	GE432MAXP-L-ULTRA	4 or 3- F32T8 120 to 277V L .77 BF	120-277	4	F32T8	97/95	.82/.35	.79/.81	.99/.98	<=10%	<1.4%	-22
				120-277	4	F28T8	86/84	.72/.31	0.77	.99/.98	<=10%	<1.4%	50F
				120-277	4	F32T8/25W	77/75	.65/.28	0.77	.99/.98	<=10%	<1.4%	50F
74098	GE432MAX347-L	GE432MAXP-L-347	4 or 3- F32T8 347V L .77 BF	347	4	F32T8	96	0.28	0.77	0.99	<=6%	<1.4%	-22
				347	4	F28T8	84	0.24	0.74	0.99	<=7%	<1.4%	60F
				347	4	F32T8/25W	74	0.22	0.74	0.99	<=7%	<1.4%	60F
78627	GE432MAX-N/ULTRA	GE432MAXP-N-ULTRA	4 or 3- F32T8 120 to 277V N .87 BF	120-277	4	F32T8	108/106	.90/.39	0.87	.99/.98	<=10%	<1.4%	-22
				120-277	4	F28T8	94/92	.79/.34	0.87	.99/.98	<=10%	<1.4%	50F
				120-277	4	F32T8/25W	87/88	.73/.32	0.87	.99/.98	<=10%	<1.4%	50F
74095	GE432MAX347-N	GE432MAXP-N-347	4 or 3- F32T8 347V N .87 BF	347	3	F32T8	106	0.30	0.88	0.99	<=5%	<1.4%	-22
				347	3	F28T8	97	0.27	0.84	0.99	<=5%	<1.4%	-22
				347	3	F32T8/25W	84	0.24	0.84	0.99	<=5%	<1.4%	-22
71423	GE432MAX-N+/ULTRA	GE432MAXP-N+ ULTRA	4 or 3- F32T8 120 to 277V N+ 1.0 BF	120-277	4	F32T8	124/123	1.03/.45	1.0	.99/.98	<=15%	<1.4%	0
				120-277	4	F28T8	114/112	.95/.36	1.0	.99/.97	<=18%	<1.4%	50F
				120-277	4	F32T8/25W	101/100	.85/.37	1.0	.99/.98	<=15%	<1.4%	60F
78619	GE432MAX-H/ULTRA	GE432MAXP-H-ULTRA	4 or 3- F32T8 120 to 277V H 1.18 BF	120-277	4	F32T8	148/145	1.3/.55	1.18	.99/.98	<=10%	<1.4%	-22
				120-277	4	F28T8	127/125	1.1/.48	1.18	.99/.98	<=10%	<1.4%	50F
				120-277	4	F32T8/25W	120/116	1.0/.43	1.18	.99/.98	<=10%	<1.4%	50F
74113	GE432MAX347-H	GE432MAXP-H-347	4 or 3- F32T8 347V H 1.18 BF	347	4	F32T8	137	0.39	1.18	0.99	<=7%	<1.4%	-22
				347	4	F28T8	126	0.36	1.13	0.99	<=7%	<1.4%	60F
				347	4	F32T8/25W	113	0.33	1.12	0.99	<=7%	<1.4%	60F
62720	GE432MAX480-N	GE432MAXP-H-480	4 or 3- F32T8 480V H 1.18 BF	480	4	F32T8	144	0.31	1.18	0.95	<=10%	<1.4%	-22
				480	4	F28T8	125	0.27	1.13	0.95	<=10%	<1.4%	50F
				480	4	F32T8/25W	115	0.26	1.11	0.95	<=10%	<1.4%	50F
8 FT PREMIUM ULTRAMAX INSTANT START BALLAST													
73199	GE259MAX-L/ULTRA	GE259MAXP-L-ULTRA	2 or 1 F96T8 120-277V L .77	120-277	2	F96T8	95/94	0.81/0.35	0.77	0.99	<=10%	<1.7%	0°F
				120-277	2	F96T8WWM	93/91	0.79/0.34	0.77	0.99	<=10%	<1.7%	60°F
				120-277	2	F96T8WMP	89/87	0.74/0.32	0.74	0.99/0.98	<=10%	<1.7%	60°F
49767	GE259MAX-N/ULTRA	GE259MAXPN-ULTRA	2 or 1 F96T8 120-277V N .87	120-277	2	F96T8	108/101	0.91/0.40	0.87	0.99	<=10%	<1.7%	0°F
				120-277	2	F96T8WWM	104/101	0.87/0.38	0.87	0.99	<=10%	<1.7%	60°F
				120-277	2	F96T8WMP	98/96	0.78/0.32	0.89	0.99	<=10%	<1.7%	60°F
63888	GE286MXA-HO-N	GE286MAXP-HO-ULTRA	2 or 1 F96T8HO 120-277V H 1.18	120-277	2	F96T8	142/140	1.24/0.52	1.15	0.99	<=10%	<1.7%	-22°F
				120-277	2	F96T8WWM	135/133	1.18/0.50	1.15	0.99/0.98	<=10%	<1.7%	-22°F
				120-277	2	F96T8WMP	124/122	1.10/0.46	1.37	0.99	<=10%	<1.7%	-22°F
				120-277	2	F96T849W	111/110	0.95/0.41	1.37	0.99	<=10%	<1.7%	-22°F

Get more information at www.gelighting.com/ultramax

Information provided is subject to change without notice. Please verify all details with GE. All values are design or typical values when measured under laboratory conditions, and GE makes no warranty or guarantee, expressed or implied that such performance will be obtained under end-use conditions.

*Rated life is given for programmed Rapid Start ballasts. Life ratings are based on engineering data with lamps cycled every 3 or 12 operating hours.

^T8 Starcoat® Ecolux® lamp initial and mean lumen ratings reflect light output at 95°F (35°C).

