



Product Catalog

for professionals

[Products](#) > 78623

78623 – GE332MAXP-N/ULTRA (replaces GE332MAX-N/ULTRA)

GE LFL UltraMax™ Professional Series Electronic High Efficiency Multivolt Instant Start Ballast

Print this Page

Convert to PDF

- Energy saving high efficiency instant start electronic ballast (> 90%)
- Multi-Voltage Technology handles voltage from 120 to 277V
- UL Type CC Rating provides protection against arcing in electrical devices.
- Anti-Striation Control for better light quality, with no striations.
- UL 55C Ambient Rating - HighTemperature Protection Circuit
- Cold temperature -20F Minimum Starting Temperature



ADDITIONAL RESOURCES

[Disposal Policies & Recycling Information](#)

GENERAL CHARACTERISTICS

Lamp type	Fluorescent - Electronic
Bulb	Electronic
Base	
Ballast Type	High Efficiency Multivolt Instant Start
Starting Method	Instant start
Lamp Wiring	Parallel
Line Voltage Regulation (+/-) (NOM)	10 %
Ambient Temperature (MIN)	-22 °F(-30 °C)
Ambient Temperature (MAX)	131 °F(55 °C)
Case Temperature (MAX)	70 °C(158 °F)
Ballast Factor	Normal
Power Factor Correction	Active
Sound Rating	A (20-24 decibels)
Additional Info	Anti-striation control, Auto-restart, Thermally protected

ELECTRICAL CHARACTERISTICS

Supply Current Frequency (MIN)	50.0 Hz
Supply Current Frequency (NOM)	60 Hz

DIMENSIONS

CaseLength	9.5 in (241.3 mm)
CaseWidth	1.3 in (33.0 mm)
CaseHeight	1.0 in (25.4 mm)
MountLength	8.9 in (225.8 mm)

MountSlots	0.3 in (7.9 mm)
MountWidth	0.9 in (22.3 mm)
Weight (NOM)	0.8 lb
Exit Type	Side
Remote Mounting Distance (NOM)	18.0 ft
Remote Mounting Wire Gauge (NOM)	18.0 AWG

PRODUCT INFORMATION

Product Code	78623
Description	GE332MAXP-N/ULTRA (replaces GE332MAX-N/ULTRA)
Standard Package	Case
Standard Package GTIN	10043168786239
Standard Package Quantity	10
Sales Unit	Standard Pack
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	10
UPC	043168786232

 CAUTIONS & WARNINGS

-

[See list of cautions & warnings.](#)

[Return To Top](#)