

LOGO! 24CE, LOGIC MODULE, DISPLAY PU/I/O: 24V/24V/24V TRANS., 8DI (4AI)/4DO; MEM 400 BLOCKS, EXPANDABLE, ETHERNET BUILT IN WEB-SERVER, DATALOG STANDARD MICRO SD CARD FOR LOGO! SOFT COMFORT V8 PREVIOUS PROJECT USABEL



Installation type/mounting	
Mounting	on 35 mm DIN rail, 4 spacing units wide
Supply voltage	
24 V DC	Yes
permissible range, lower limit (DC)	20.4 V
permissible range, upper limit (DC)	28.8 V
Time of day	
Time switching clocks	
• Number	190
• Power reserve	480 h
Digital inputs	
Number of digital inputs	8; Of which 4 can be used in analog mode (0 to 10 V)
Digital outputs	
Number of digital outputs	4; Transistor
short-circuit protection	Yes; electrical (1 A)
Output current	
• for signal "1" permissible range for 0 to 55 °C, max.	0.3 A

EMC

Emission of radio interference acc. to EN 55 011

- | | |
|---|---|
| • Limit class B, for use in residential areas | Yes; Radio interference suppression according to EN55011, Limit Value Class B |
|---|---|

Degree and class of protection

Degree of protection to EN 60529

- | | |
|--------|-----|
| • IP20 | Yes |
|--------|-----|

Standards, approvals, certificates

CSA approval	Yes
--------------	-----

UL approval	Yes
-------------	-----

FM approval	Yes
-------------	-----

Developed in accordance with IEC 61131	Yes
--	-----

according to VDE 0631	Yes
-----------------------	-----

Marine approval

- | | |
|-------------------|-----|
| • Marine approval | Yes |
|-------------------|-----|

Ambient conditions

Operating temperature

- | | |
|--------|-------|
| • Min. | 0 °C |
| • max. | 55 °C |

Dimensions

Width	71.5 mm
-------	---------

Height	90 mm
--------	-------

Depth	60 mm
-------	-------

last modified:	14.10.2014
-----------------------	------------