


# RV-8564-C2 Real Time Clock Module with I<sup>2</sup>C Bus





Automotive qualified, according to AEC-Q200 Rev. C
Xtal integrated solution
Miniature SMT ceramic package
Ultra low power consumption
Very tight frequency tolerance
I<sup>2</sup>C Bus Interface (400 kHz) \*
Programmable Clock-output
Low aging

Time keeping mode down to 1.2 V Programmable alarm, timer and interrupt functions

#### **DESCRIPTION:**

This very small SMD ceramic package has been specially designed to combine the 32.768 kHz crystal unit with the CMOS-based oscillator and real-time-clock circuit.


The calendar function tracks year, month, date, and day-of-the-week with built-in century and leap-year flags. The clock function tracks minute and second in 24-hour format. Programmable alarm setting and universal timer functions increase flexibility.

For pick-and-place equipment, the parts are available in 12 mm tape:

7" (178 mm) reel with 1'000 parts

13" (330 mm) reel with 5'000 parts

#### **BLOCK DIAGRAM:**



<sup>\*</sup> The I<sup>2</sup>C Bus is a trademark of Philips Electronics N.V.

## ELECTRICAL CHARACTERISTICS AT 25°C:

	Symbol	Condition	Min.	Тур.	Max	Unit
Supply voltage	$V_{DD}$	I <sup>2</sup> C Bus Active	1.8		5.5	V
Supply voltage	$V_{DD}$	Time keeping	1.2		5.5	V
Power current	I <sub>DD</sub>	fscl=400 kHz			800	μΑ
during access		fscl=100 kHz			200	μΑ
Current consumption Time keeping mode	I <sub>DDO</sub>	fscl=0 Hz, V <sub>DD</sub> 3 V		250	500	nA
		fscl=0 Hz, V <sub>DD</sub> 2 V		225	450	nA
CLKOUT frequency		Programmable	32768/1024/32/1		Hz	
Frequency tolerance	ΔF/F	@ 25°C	±10 / ±20 1)		ppm	
Aging first year max.	ΔF/F	@ 25°C	± 3		ppm	
Frequency vs. temp.	ΔF/F <sub>O</sub>	$20 \le T_0 \le 30$	-0.035 ppm/ <sub>°C²</sub> (T - T <sub>0</sub> )² ±10%		ppm	

<sup>1)</sup> Tighter and wider frequency tolerances on request.


# ENVIRONMENTAL CHARACTERISTICS:

		Conditions	Max. Dev.
Storage temp. range		–55 to +125°C	
TA Operating temperature range		–40 to +85°C	
Shock resistance	ΔF/F	5000 g, 0.3 ms, ½ sine	+/-5 ppm
Vibration resistance	ΔF/F	20 g / 10–2000 Hz	+/-5 ppm


## TERMINATIONS AND PROCESSING:

Package-Type	Termination	Processing		
SON 10-pin	For SMD mounting Au plated pads	Reflow soldering 260°C / 20 s max.		

# FREQUENCY TEMPERATURE CHARACTERISTICS:



## PIN CONNECTIONS TOP VIEW:



All specifications subject to change without notice.



Micro Crystal AG Mühlestrasse 14 CH-2540 Grenchen Switzerland Tel. +41 32 655 82 82 Fax +41 32 655 82 83 sales@microcrystal.com www.microcrystal.com