


## **RV-3029-C3**

Real Time Clock Module with I<sup>2</sup>C-Bus





Extremely Accurate RTC Module with embedded Xtal. I<sup>2</sup>C Interface Temperature Compensation

Temperature Compensation
Automotive qualified, according to
AEC-Q200 Rev. C

Option A:	Calibrated		
Temperature	<b>Time Deviation</b>		
@ +25°C	± 0.26 s/day	±	3ppm
0°C to +50°C	± 0.35 s/day	±	4ppm
-10°C to +60°C	± 0.44 s/day	±	5ppm
-40°C to +85°C	± 0.52 s/day	±	6ppm
-40°C to +125°C	± 0.70 s/day	±	8ppm

Option B:	Default	
Temperature	<b>Time Deviation</b>	1
@ +25°C	± 0.26 s/day	± 3ppm
0°C to +50°C	± 0.44 s/day	± 5ppm
-10°C to +60°C	± 0.87 s/day	±10ppm
-40°C to +85°C	± 2.17 s/day	±25ppm
-40°C to +125°C	± 2.60 s/day	±30ppm

## **BLOCKDIAGRAM:**

## **DESCRIPTION:**


The RV-3029-C3 is an ultra miniature Real-Time-Clock Module with embedded Crystal. This RTC has an I $^2$ C Bus (2-wire Serial-Interface) and offers temperature compensated time. The STC-Smart Temperature Compensation is calibrated in the factory and leads to a very high time-accuracy of  $\pm$  6ppm from -40 $^{\circ}$ C to +85 $^{\circ}$ C and  $\pm$  8ppm from -40 $^{\circ}$ C to +125 $^{\circ}$ C.

Beside standard RTC functions, it includes a Backup-Battery Input with internal switchover function, a programmable Trickle-charge circuitry, an integrated Temperature Sensor with digital-output and offers 8 Bytes RAM and 2 Bytes EEPROM for customer's application.

The calendar function tracks year and leap -year flags. The clock tracks second, minute and hour in 24-hour format. Programmable alarm setting and universal timer functions increase flexibility.

For pick-and-place equipment, the parts are available in 12 mm tape:

7" (178 mm) reel with 1'000 parts 7" (178 mm) reel with 3'000 parts



**ELECTRICAL CHARACTERISTICS** AT 25°C:

	Symbol	Condition	Min.	Тур.	Max	Unit
Supply voltage	$V_{DD}$	Time keeping	1.3		5.5	V
Supply voltage	$V_{DD}$	Temp. comp.	Temp. comp. 1.8		5.5	V
Current consumption	I <sub>DDO</sub>	$V_{DD} = 3V$	800		1000	nA
CLKOUT frequency		Progr.	32.768/1024/32/1		Hz	
Frequency Tolerance	ΔF/F	@ 25°C	±10		±20	ppm
Freq.vs.Temp.	$\Delta F/F_{TOPR}$	$20 \le T_0 \le 30$	-0.035 ppm/ <sub>°C²</sub> (T - T <sub>0</sub> )² ±10%		ppm	
Aging first year	ΔF/F	@ 25°C			± 3	ppm
Time accuracy Ont A	Δt/t	@ 25°C			±0.26	s/day
Time accuracy Opt. A		-40 to +85°C			±0.52	s/day
Time accuracy Opt. P	Δt/t	@ 25°C			±0.26	s/day
Time accuracy Opt. B		-40 to +85°C			±2.17	s/day


ENVIRONMENTAL CHARACTERISTICS:

		Conditions	Max. Dev.
Storage temp. range		–55 to +125°C	
TA Operating temperature range		–40 to +85°C	
TB Extended oper. temp. range		–40 to +125°C	
Shock resistance	ΔF/F	5000 g, 0.3 ms, ½ sine	± 5 ppm
Vibration resistance	ΔF/F	20 g / 10–2000 Hz	± 5 ppm


PACKAGE, TERMINATIONS AND PROCESSING:

Package-Type	Termination	Processing			
SON 10-pin	For SMD mounting Au plated pads	Reflow soldering 260°C/20 s max.			

FREQUENCY TEMPERATURE CHARACTERISTICS:



PIN CONNECTIONS TOP VIEW:



All specifications subject to change without notice.



Micro Crystal AG Mühlestrasse 14 CH-2540 Grenchen Switzerland Tel. +41 32 655 82 82 Fax +41 32 655 82 83 sales@microcrystal.com www.microcrystal.com