SIEMENS

AUXILIARY SWITCH BLOCK, 71E, 3NO+1NC, DIN EN50011, CAGE CLAMP CONNECTION FOR CONTACTOR RELAYS, 4-POLE

General technical data:						
product brand name		SIRIUS				
Acceptability for application		Contactor relay and power contactor				
Protection class IP / on the front		IP20				
Ambient temperature						
during storage	°C	-55 +80				
• during operating	°C	-25 +60				
Mechanical operating cycles as operating time						
• typical		10,000,000				
Electrical operating cycles as operating time / at AC-15 / at 230 V						
• typical		200,000				
Contact reliability		one incorrect switching operation of 100 million switching operations (17 V, 5 mA)				
Contact reliability / of the auxiliary contacts		1 faulty switching per 100 million (17 V, 1 mA)				
Insulation voltage / with degree of pollution 3						
rated value	V	690				
Impulse voltage resistance						
rated value	kV	6				
Auxiliary circuit:						
Number of NC contacts / for auxiliary contacts						

Number of NC contacts / for auxiliary contacts		
instantaneous switching		1
Number of NO contacts / for auxiliary contacts		
instantaneous switching		3
Operating current / of the auxiliary contacts / at AC-12		
• at 24 V	А	10
• at 230 V	А	10
• at 400 V	А	10
• at 690 V	А	10
• maximum	А	10
Operating current / of the auxiliary contacts / at AC-14		

• at 125 V	А	6
• at 250 V	A	6
Operating current / of the auxiliary contacts / at AC-15		
• at 24 V	A	6
• at 230 V	А	6
• at 690 V	А	1
• at 400 V	А	3
Operating current		
• with 2 current paths in series / at DC-12		
• at 24 V / rated value	А	10
• at 60 V / rated value	А	10
• at 110 V / rated value	А	4
• at 220 V / rated value	А	2
• at 440 V / rated value	А	1.3
• at 600 V / rated value	А	0.65
• with 3 current paths in series / at DC-12		
• at 24 V / rated value	А	10
• at 60 V / rated value	А	10
• at 110 V / rated value	А	10
• at 220 V / rated value	А	3.6
• at 440 V / rated value	А	2.5
• at 600 V / rated value	А	1.8
Operating current		
• of the auxiliary contacts / at DC-13		
• at 24 V	А	6
• at 60 V	А	2
• at 110 V	А	1
• at 220 V	А	0.3
• with 2 current paths in series / at DC-13		
• at 24 V / rated value	А	10
• at 60 V / rated value	А	3.5
• at 110 V / rated value	А	1.3
• at 220 V / rated value	А	0.9
• at 440 V / rated value	А	0.2
• at 600 V / rated value	А	0.1
• with 3 current paths in series / at DC-13		
• at 24 V / rated value	А	10
• at 60 V / rated value	А	4.7
• at 110 V / rated value	А	3
• at 220 V / rated value	А	1.2

• at 440 V / rated	d value		А	0.5			
• at 600 V / rated	d value		А	0.26			
			_	_			
Installation/mount	ing/dimensions:			_			
Type of mounting			-	snap-on mounting			
Width			mm	36.5			
Height			mm	37.5	37.5		
Depth			mm	46			
Connections:							
Design of the electric	cal connection						
 for auxiliary and c 	ontrol current circuit			spring-	loaded terminals		
Type of the connecta	able conductor cross-	section	_				
 for auxiliary conta 	cts						
• solid				2x (0.5	2x (0.5 2.5 mm²)		
 finely stranded 							
with conduct	tor end processing			2x (0.5 1.5 mm²)			
 without cond 	ductor final cutting			2x (0.5 2.5 mm²)			
 for AWG conductor 	ors / for auxiliary contac	cts		2x (20 14)			
Safety:related Para	ameter:						
Product function / mirror contact to IEC 60947-4-1			_	Yes			
Product function / positively driven operation to IEC 60947-5-1			_	Yes			
Certificates/approv	vals:		_		_	_	
General Product Ap			_	_	Functional Safety /	Declaration of	
General Froduct A	Sproval				Safety of Machinery	Conformity	
	(SA) CSA	GOST			Type Examination	EG-Konf.	
Test Certificates							
Special Test Certificate							
Shipping Approval							
ABS	BUREAU VERITAS	GL GL	Llovd's Register Lrs		RINA	RMRS	
other							
other	Environmental Confirmations						
Further informatio	n:						

Information- and Downloadcenter (Catalogs, Brochures,...) http://www.siemens.com/industrial-controls/catalogs

Industry Mall (Online ordering system)


http://www.siemens.com/industrial-controls/mall


Cax online generator:

http://www.siemens.com/cax

Service&Support (Manuals, Certificates, Characteristics, FAQs,...) http://support.automation.siemens.com/WW/view/en/3RH1911-2GA31/all

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...) http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RH1911-2GA31





last change:

Feb 25, 2013