

# SIEMENS

## Product data sheet

## 3RU1116-1EB0



Abb. ähnlich / similar picture

OVERLOAD RELAY, 2.8...4 A, 1NO+1NC,  
SIZE S00, CLASS 10,  
FOR CONTACTOR MOUNTING


### General technical details:

Operating current / of the fuse link / rated value	16 A
Adjustable response current / of the current-dependent overload release / initial value	2.8 A
Adjustable response current / of the current-dependent overload release / final value	4 A
Service power / for three-phase servomotors / rated value	1.5 kW
Number of NC contacts / for auxiliary contact	1
Number of NO contacts / for auxiliary contact	1
Number of change-over switches / for auxiliary contact	0
Type of assignment	2
Type of protection	DMT 98 ATEX G 001

### Mechanical design:

Design of the electrical connection / for main current circuit	screw-type terminals
Design of the electrical connection / for auxiliary and control current circuit	screw-type terminals
Size of the contactor / can be combined / company-specific	S00

Type of fixing/fixation	direct mounting
Size of overload relay	S00
Ambient conditions:	
Protection class IP	IP20



last change:

10/31/2006

<b>Technical Assistance:</b>	Telephone:	+49 (0) 911-895-5900 (8°° - 17°° CET)
	Fax:	+49 (0) 911-895-5907
	E-Mail:	technical-assistance@siemens.com
	Internet:	www.siemens.de/lowvoltage/technical-assistance