

4280	5280	0479	0379
<p>4280-0-XX-XX-16-XX-10-0 Solder mount in $\text{Ø}1,7\pm0,08$ PTH. #16 Contact for $\text{Ø}0,56-0,86$ pins. Also available on 8mm wide carrier tape: 6,000 parts per 330mm reel.</p>	<p>5280-0-XX-XX-16-XX-40-0 Solder mount in $\text{Ø}1,7\pm0,08$ PTH. #16 Contact for $\text{Ø}0,56-0,86$ pins. Also available on 16mm wide carrier tape: 2,200 parts per 330mm reel.</p>	<p>0479-0-XX-XX-34-XX-10-0 Solder mount in $\text{Ø}1,96\pm0,08$ PTH. #34 Contact for $\text{Ø}0,81-1,17$ pins. Also available on 16mm wide carrier tape: 2,000 parts per 330mm reel.</p>	<p>0379-0-43-XX-34-XX-10-0 Solder mount in $\text{Ø}1,96\pm0,08$ PTH. #34 Contact for $\text{Ø}0,81-1,17$ pins.</p>
9873	5364	5291	3966
<p>9873-0-XX-XX-02-XX-10-0 Solder mount in $\text{Ø}2,11\pm0,08$ PTH. #02 Contact for $\text{Ø}1,02-1,27$ pins. Also available on 12mm wide carrier tape: 4,500 parts per 330mm reel.</p>	<p>5364-0-XX-XX-23-XX-10-0 Solder mount in $\text{Ø}2,62\pm0,08$ PTH. #23 Contact for $\text{Ø}1,14-1,65$ pins. Also available on 12mm wide carrier tape: 2,000 parts per 330mm reel.</p>	<p>5291-0-XX-XX-08-XX-40-0 Solder mount in $\text{Ø}3,53\pm0,08$ PTH. #08 Contact for $\text{Ø}2,13-2,59$ pins. Also available on 16mm wide carrier tape: 1,700 parts per 330mm reel.</p>	<p>3966-0-XX-XX-07-XX-10-0 Solder mount in $\text{Ø}3,43\pm0,08$ PTH. #07 Contact for $\text{Ø}1,65-2,08$ pins. Also available on 24mm wide carrier tape: 650 parts per 330mm reel.</p>

<p>SPECIFICATIONS SHELL MATERIAL: Brass Alloy 360, 1/2 Hard CONTACT MATERIAL: Beryllium Copper Alloy 172, HT SOLDER BARRIER: Organic Fibre Plug® DIMENSION IN INCHES TOLERANCES ON: LENGTHS: $\pm 0,13$ DIAMETERS: $\pm 0,05$ ANGLES: $\pm 2^\circ$</p>	<p>ORDER CODE: XXXX - 0 - XX - XX - XX - XX -X0 - 0</p> <p>BASIC PART # →</p> <p>SPECIFY PACKAGING: →</p> <p>43 Discrete Receptacles 67 Supplied on 330mm Reels</p> <p>SPECIFY SHELL FINISH: →</p> <p>01 5,08µm TIN/LEAD OVER NICKEL 80 5,08µm TIN OVER NICKEL ◇</p> <p>CONTACT # →</p> <p>#02, #07, #08, #16, #23 or #34 CONTACT (DATA ON PAGES 221 - 226)</p>	<p>SPECIFY CONTACT FINISH:</p> <p>27 0,76µm GOLD OVER NICKEL ◇ 01 5,08µm TIN/LEAD OVER NICKEL 80 5,08µm TIN OVER NICKEL ◇</p>	
--	--	--	--