



3-PHASE LINE-SIDE TERMINAL 3-PHASE LINE-SIDE
 TERMINAL,
 FOR 3-PHASE BUSBARS,
 FOR SIZE S0 AND S00,
 CONNECTION FROM ABOVE,
 PIN-TYPE CONNECTIONS

General technical data:

product brand name		SIRIUS
product designation		3-phase infeed terminal
Size of the circuit-breaker		S00, S0
Protection class IP / on the front		IP20
Insulation voltage / with degree of pollution 3		
• rated value	V	690
Ambient temperature		
• during storage	°C	-50 ... +80
• during operating	°C	-20 ... +60
Current-carrying capacity / maximum	A	63

Installation/mounting/dimensions:

Width	mm	44
Height	mm	24
Depth	mm	25
Acceptability for application / makes the assembly of self-protected combination motor controllers (type E) according to UL 508 possible		No

Connections:

Design of the electrical connection		
--	--	--

• for main current circuit		screw-type terminals
Type of the connectable conductor cross-section		
• for main contacts		
• solid		1x (2.5 ... 25 mm ²)
• stranded		1x (2.5 ... 25 mm ²)
• finely stranded		
• with conductor end processing		1x (4 ... 16 mm ²)
• for AWG conductors / for main contacts		1x (12 ... 4)

Certificates/approvals:

Verification of suitability

CE / UL / CSA / CCC

General Product Approval

Declaration of Conformity

Test Certificates



CSA



UL



EG-Konf.

[Special Test Certificate](#)

Shipping Approval



other

[Confirmation](#)

[Declaration of Conformity](#)

[other](#)

[Environmental Confirmations](#)

Further information:

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrial-controls/mall>

Cax online generator:



<http://www.siemens.com/cax>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)

<http://support.automation.siemens.com/WW/view/en/3RV1915-5A/all>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, ...)

http://www.automation.siemens.com/bilddb/cax_en.aspx?mlfb=3RV1915-5A



last change:

Jan 21, 2013