








Product Specifications LCP2B250F60

 May not be exact product-for reference only	Catalog Number	Function*	Input Voltage	Output	Wiring / Sockets
	LCP2B250F60	SINGLE PROBE PUMP DOWN, Sensitivity Range: 1K - 250K Ohms, Fixed at 60 Sec.	120V AC	10A SPDT	 Use Socket 70169-D

*DESCRIPTION OF FUNCTION	CHART
<p>Pump Down (Drain): When the liquid level rises & touches the probe, a fixed time delay begins & the LED flashes Red. This time delay prevents rapid cycling of the output relay & its load. At the end of the time delay, the output relay energizes & the LED is Red ON. The pump is ON to drain the tank. The relay remains energized until the liquid level falls below the probe level. The output relay de-energizes, turning off the pump, and remains de-energized & the LED is Green ON until the liquid level rises & touches the probe.</p>	

APPLICATION INFORMATION	DIMENSIONS
<p>Voltage Tolerance: AC Operation: +10/-15% of nominal at 50/60 Hz.</p> <p>Load (Burden): 2 VA</p> <p>Indicator LEDs: Green ON with Input Voltage applied; Red Flashing during timing; Red ON when relay energized.</p> <p>Probe Voltage: 5V DC Pulsed</p> <p>Response Time: Pick-up: Fixed per value shown under "Function" in table above; Drop-out: 500ms</p> <p>Output Contacts: 10A @ 240V AC/7A @ 28V DC, 1/4HP @ 120V AC (N.O.)</p> <p>Life: Mechanical: 10,000,000 operations; Full Load: 100,000 operations</p> <p>Temperature: (Storage) -40° to 85° C (-40° to 185° F); (Operating) -28° to 65° C (-18° to 149° F)</p> <p>Approvals:</p>  <p>with Appropriate Macromatic Socket</p>	 <p>Inches (Millimeters)</p>

Macromatic Industrial Controls Inc.

W134N5345 Campbell Drive, Menomonee Falls, WI 53051 (USA)
Telephone: 800-238-7474 (262-781-3366) © 1997-2015 Macromatic Industrial Controls Inc.