



DIGITAL MONITORING RELAY VOLTAGE MONITORING, 22.5MM FROM 17 TO 275V AC/DC OVERSHOOT AND UNDERSHOOT INTERNAL POWER SUPPLY DC AND AC 50 TO 60 HZ SPIKE DELAY 0.1 TO 20S HYSTERESIS 0.1 TO 150V 1 CHANGEOVER CONTACT W. OR W/O ERROR LOG SCREW TERMINAL REPLACEMENT PRODUCT F. 3UG3534, 3UG3535

Figure similar

Product function		Voltage monitoring relay
Measuring circuit:		
Type of voltage for monitoring		AC/DC
Number of poles for main current circuit		1
Measurable line frequency	Hz	500 ... 40
Measurable voltage at AC	V	17 ... 275
Adjustable voltage range	V	17 ... 275
Adjustable response delay time		
• when starting	s	0.1 ... 20
• with lower or upper limit violation	s	0.1 ... 20
Response time maximum	ms	450
Relative metering precision	%	5
Accuracy of digital display		+/-1 digit
Relative temperature-related measurement deviation	%	0.1
Relative repeat accuracy	%	1
General technical data:		
Design of the display		LCD
Product function		
• Voltage window recognition 1 phase		Yes

• Voltage window recognition 3 phase		No
• Voltage window recognition DC		Yes
• Overvoltage detection 1 phase		Yes
• Overvoltage detection 3 phase		No
• Overvoltage detection DC		Yes
• undervoltage detection 1 phase		Yes
• undervoltage detection 3 phases		No
• undervoltage detection DC		Yes
• External reset		Yes
• Auto-reset		Yes
• Adjustable open/closed-circuit current principle		Yes
Startup time after the control supply voltage has been applied	ms	1 000
Type of voltage of the control supply voltage		AC/DC
Control supply voltage		
• at AC		
— at 50 Hz Rated value	V	17 ... 275
— at 60 Hz Rated value	V	17 ... 275
• at DC Rated value	V	17 ... 275
Operating range factor control supply voltage rated value		
• at AC		
— at 50 Hz		1 ... 1
— at 60 Hz		1 ... 1
• at DC		1 ... 1
Surge voltage resistance Rated value	kV	4
Active power consumption	W	2
Protection class IP		IP20
Electromagnetic compatibility		IEC 60947-1 / IEC 61000-6-2 / IEC 61000-6-4
Vibration resistance acc. to IEC 60068-2-6		1 ... 6 Hz: 15 mm, 6 ... 500 Hz: 2g
Shock resistance acc. to IEC 60068-2-27		sinusoidal half-wave 15g / 11 ms
Installation altitude at height above sea level maximum	m	2 000
maximum permissible voltage for safe isolation		
• between control and auxiliary circuit	V	300
• between auxiliary and auxiliary circuit	V	300
Conducted interference due to burst acc. to IEC 61000-4-4		2 kV
Conducted interference due to conductor-earth surge acc. to IEC 61000-4-5		2 kV
Conducted interference due to conductor-conductor surge acc. to IEC 61000-4-5		1 kV
Electrostatic discharge acc. to IEC 61000-4-2		6 kV contact discharge / 8 kV air discharge

Field-bound parasitic coupling acc. to IEC 61000-4-3		10 V/m
Insulation voltage for overvoltage category III according to IEC 60664 with degree of pollution 3 Rated value	V	690
Ambient temperature		
• during operation	°C	-25 ... +60
• during storage	°C	-40 ... +85
• during transport	°C	-40 ... +85
Design of the electrical isolation		Safe isolation
Galvanic isolation		
• between entrance and outlet		Yes
• between the outputs		Yes
• between the voltage supply and other circuits		No
Mechanical service life (switching cycles) typical		10 000 000
Electrical endurance (switching cycles) at AC-15 at 230 V typical		100 000
Operating frequency with 3RT2 contactor maximum	1/h	5 000






Mechanical data:		
Width	mm	22.5
Height	mm	92
Depth	mm	91
mounting position		any
Required spacing for grounded parts		
• forwards	mm	0
• Backwards	mm	0
• at the side	mm	0
• upwards	mm	0
• downwards	mm	0
Required spacing with side-by-side mounting		
• forwards	mm	0
• Backwards	mm	0
• at the side	mm	0
• upwards	mm	0
• downwards	mm	0
Required spacing for live parts		
• forwards	mm	0
• Backwards	mm	0
• at the side	mm	0
• upwards	mm	0
Mounting type		snap-on mounting
Product function removable terminal for auxiliary and control circuit		Yes

Type of electrical connection		screw-type terminals
Type of connectable conductor cross-section		1x (0.5 ... 4 mm ²), 2x (0.5 ... 2.5 mm ²)
<ul style="list-style-type: none"> • solid • finely stranded <ul style="list-style-type: none"> — with core end processing • for AWG conductors <ul style="list-style-type: none"> — solid — stranded 		1x (0.5 ... 2.5 mm ²), 2x (0.5 ... 1.5 mm ²)
		2x (20 ... 14)
		2x (20 ... 14)
Tightening torque with screw-type terminals	N·m	1.2 ... 0.8

Outputs:

Number of NO contacts delayed switching		0
Number of NC contacts delayed switching		0
Number of CO contacts delayed switching		1
Operating current at 17 V minimum	mA	5
Continuous current of the DIAZED fuse link of the output relay	A	4
Thermal current of the switching element with contacts maximum	A	5

Certificates/ approvals:

General Product Approval	EMC	Declaration of Conformity	Test Certificates
 CCC		 UL	 C-TICK
		 EG-Konf.	spezielle Prüfbescheinigung n

Test Certificates	Shipping Approval	other
Typprüfbescheinigung/Werkzeugnis	 DNV	sonstig
	 GL	
	 LRS	

Further information

Information- and Downloadcenter (Catalogs, Brochures,...)

<http://www.siemens.com/industrial-controls/catalogs>

Industry Mall (Online ordering system)

<http://www.siemens.com/industrymall>

Cax online generator


<http://support.automation.siemens.com/WW/CAXorder/default.aspx?lang=en&mlfb=3UG46331AL30>

Service&Support (Manuals, Certificates, Characteristics, FAQs,...)


<https://support.industry.siemens.com/cs/ww/en/ps/3UG46331AL30>

Image database (product images, 2D dimension drawings, 3D models, device circuit diagrams, EPLAN macros, ...)

http://www.automation.siemens.com/bilddb/cax_de.aspx?mlfb=3UG46331AL30&lang=en



last modified:



17.07.2015