

Product type designation

Product description

IE FC RJ45 Plug 145 (2x2)

RJ45 data connector

IE FC RJ45 PLUG 145 2X2, RJ45 PLUG CONNECTOR

(10/100MBIT/S) WITH RUGGED METAL HOUSING AND FC

CONNECTING METHOD FOR IE FC CABLE 2X2 145 DGR CABLE

OUTLET 1 PACK = 1 PCS



Suitability for use

For connection to IE FC TP cables 2x2, suitable for fast assembly with the FastConnect system

Transmission rate

Transfer rate / for Industrial Ethernet

10 Mbit/s, 100 Mbit/s

Interfaces

Number of electrical connections

- for Industrial Ethernet FC TP cables
- for network components or terminal equipment

4

1

Type of electrical connection

- for Industrial Ethernet FC TP cables
- for network components or terminal equipment

integrated cut-and-clamp contacts for 4-wire TP FC installation cable

RJ45 connector

Type of electrical connection / FastConnect

Yes

Mechanical data

Material / of the enclosure

metal

Number of reuses

10

Design, dimensions and weight	
Type of cable outlet	145° cable outlet
Width	13.9 mm
Height	16 mm
Depth	55.6 mm
Net weight	35 g

Permitted ambient conditions	
Ambient temperature	
<ul style="list-style-type: none"> during operation 	-40 ... +85 °C
<ul style="list-style-type: none"> during storage 	-40 ... +85 °C
<ul style="list-style-type: none"> during transport 	-40 ... +85 °C
Relative humidity / at 25 °C / without condensation / during operation / maximum	95 %
Protection class IP	IP20

Product properties, functions, components / general	
Product property	
<ul style="list-style-type: none"> PoE capability 	Yes
<ul style="list-style-type: none"> PoE+capability 	Yes
<ul style="list-style-type: none"> silicon-free 	Yes
Product component	
<ul style="list-style-type: none"> strain relief 	Yes

Standards, specifications, approvals	
Certificate of suitability	
<ul style="list-style-type: none"> RoHS conformity 	Yes
<ul style="list-style-type: none"> UL approval 	Yes
<ul style="list-style-type: none"> cULus approval 	Yes
<ul style="list-style-type: none"> Railway application in accordance with EN 50155 	No
Standard for structured cabling	Cat5

Further Information / Internet Links	
Internet-Link	
<ul style="list-style-type: none"> to website: Selector SIMATIC NET SELECTION TOOL 	http://www.siemens.com/snst
<ul style="list-style-type: none"> to website: Industrial communication 	http://www.siemens.com/simatic-net
<ul style="list-style-type: none"> to website: Industry Mall 	https://mall.industry.siemens.com
<ul style="list-style-type: none"> to website: Information and Download Center 	http://www.siemens.com/automation/net/catalog
<ul style="list-style-type: none"> to website: Image database 	http://automation.siemens.com/bilddb
<ul style="list-style-type: none"> to website: CAx Download Manager 	http://www.siemens.com/cax
<ul style="list-style-type: none"> to website: Industry Online Support 	https://support.industry.siemens.com
last modified:	08.08.2015