


Arteor™ hotel equipment



5 727 30



5 721 53



Hotel equipment

p. 422

Support frame and plate selection charts **p. 414-421**

Mechanisms supplied with rocker plates, to be equipped with support frames (p. 411) and plates (p. 414 to 421)

Pack	Cat.Nos	Mechanical key card switches
1	5 722 30	For energizing a circuit by inserting a key fob Cat.No 5 722 59 or a smart card (access card for a hotel room) Example of use: hotel room power supply only when guest is present Time-delay of approx. 30 sec. after card removal To be equipped with single pole latching relay Cat.Nos 5 722 27 or 5 727 27 (p. 391) 2 modules Key card switches 230 V <input type="radio"/> White <input checked="" type="radio"/> Magnesium
1	5 727 30	
1	5 722 31	Key card switches 12-24 V <input type="radio"/> White <input checked="" type="radio"/> Magnesium
1	5 734 93	

Pack	Cat.Nos	Key card switches RFID
1	5 722 53	For energizing a circuit for example meeting room, office, hotel room... Works only with ISO type contactless key card Cat.Nos 0 767 11/12/13 or other ISO type 13.56 MHz key card Time-delay of approx. 30 sec. after card removal Low capacity contact 230 V - 30 VA Lighting of the slot by LED 2 modules <input type="radio"/> White <input checked="" type="radio"/> Magnesium
1	5 727 53	

Pack	Cat.Nos	Key card
10	5 722 59	For mechanical key card switches Enables use of key fob switches in hotels with key locks Supplied complete with a label holder for individual hotel identification <input type="radio"/> White <input checked="" type="radio"/> Magnesium
10	5 727 59	
10	0 767 11	For RFID key card switches MIFARE contactless badge card ISO format (50 x 80 mm) Chip: 13.56 MHz Standard 1 KB memory

Pack	Cat.Nos	Shaver sockets
1	5 721 55	Conform to BS EN 61558-2-5 IP 24 For use with European, British, American, Australian 2-pin plugs Screwless live and neutral terminals Double wound isolating transformer Automatic self-resetting overload feature Plug insertion operates micro-switch which energises transformer To be equipped with BS 2 gang - 3-module plates (p. 414, 415) For flush-mounting boxes, use BS 2 gang box depth 48 mm, US type, Italian type boxes depth 48 mm or Cat.No 0 801 55 (p. 610) Power supply: 230 V - 50/60 Hz 3 modules 230 V / 120-230 V <input type="radio"/> White <input checked="" type="radio"/> Magnesium
1	5 726 55	
1	5 721 53	230 V / 120-230 V with earth connector <input type="radio"/> White <input checked="" type="radio"/> Magnesium
1	5 726 53	

Pack	Cat.Nos	Chimes
1	5 722 06	230 V - 50 Hz Consumption: 65 mA 1 melody Tone level: 73 dB at 1 m Compatible with push-button Cat.No 0 416 45 <input type="radio"/> White <input checked="" type="radio"/> Magnesium
1	5 722 46	