




Basic Character LCD Drawing

Part Number: FDS20x4(66x36)XBC



Features:

1. 5x8 Dots with cursor
2. Built-in controller (ST7066U or Equivalent)
3. +5V power supply
4. 1/16 duty cycle
5. No Backlight

Mechanical Data

ITEM	STANDARD	UNIT
MODULE DIMENSION	66.0 X 36.0	mm
VIEWING AREA	60.0 X 28.0	mm
DOT SIZE	0.43 X 0.60	mm
CHARACTER SIZE	2.35 X 5.15	mm



Interface Pin Connections

NO	SYMBOL	LEVEL	FUNCTION
1	V _{SS}	Power Supply	Signal Ground for LCM (GND)
2	V _{DD}		Power supply for logic (+5V) for LCM
3	V ₀		Contrast Adjust
4	RS	MPU	Register Select signal
5	R/W	MPU	Read/Write Select signal
6	E	MPU	Operation (data read/write) enable signal
7~10	DB ₀ ~DB ₃	MPU	Four High Order bi-directional three-state data bus lines. Used for data transfer between the MPU and the LCM. These four are not used during 4-bit operation.
11~14	DB ₄ ~DB ₇	MPU	Four High Order bi-directional three-state data bus lines. Used for data transfer between the MPU.
15	LED+	LED BKL power supply	NC
16	LED-		NC

Absolute Maximum Rating

ITEM	SYMBOL	MIN	TYP	MAX	UNIT
Power Voltage for Logic	V _{DD} -V _{SS}	-0.3	--	7.0	V
Input Voltage	V _{IN}	-0.3	--	10	
Operating Temperature Range	V _{OP}	-20	--	+70	
Storage Temperature Range	V _{ST}	-30	--	+80	°C

Electrical Characteristics

ITEM	SYM	CONDITION	MIN	TYP	MAX	UNIT
Supply Voltage for LCD	V _{DD} -V ₀	T _a =25°C	--	4.5	--	V
Input Voltage	V _{DD}		4.7	5.0	--	
Backlight Supply Voltage	V _F		--	3.3	--	
Supply Current	I _{DD}	T _a =25°C, V _{DD} =3.3V	--	1.5	3	mA
Backlight Supply Current	I _F		--	--	--	
Input Leakage Current	I _{LKG}		--	--	1.0	uA
"H" Level Input Voltage	V _{IH}		2.7	--	V _{DD}	V
"L" Level Input Voltage	V _{IL}	Twice Initial Value or Less	0	--	0.6	
"H" Level Output Voltage	V _{OH}	LOH= -0.25mA	2.7	--	--	
"L" Level Output Voltage	V _{OL}	LOH= 1.6mA	--	--	0.4	

