

## UNMANAGED INDUSTRIAL ETHERNET SWITCHES

The SL/SLX-5ES and SL/SLX-8/9ES are 5 and 8/9 port industrial Ethernet switches that provide advanced performance that enables you to achieve real-time deterministic operation. These ruggedized switches are hardened to provide superior reliability. They require no user setup and immediately start operating as soon as you power them up. Sixnet switches are designed to make your job easier, ensuring your system will keep running for many years to come.

### PRODUCT HIGHLIGHTS

- Slim packaging fits on your Din-rail
- High performance and value
- Truly industrial hardened design
- Plug & play saves you time and money

### REAL-TIME ETHERNET PERFORMANCE

- Fast wire-speed switching
- Intelligent message routing - No collisions!
- Ideal for any system

### PLUG & PLAY SIMPLICITY

- Auto-sensing for speed and duplex
- Auto-mdi/mdix-crossover works with straight or crossed cables
- Auto-polarity corrects for crossed signals

### TROUBLE FREE OPERATION

- Ultra-reliable 1,000,000+ hours MTBF
- Dual power inputs with industrial spike protection
- DIN-rail or direct panel mounting
- UL/CSA (CUL), CE, hazardous locations (Zone 2) and maritime rated



SLX Models

### Sixnet Knows Industrial

We have been designing industrial hardware such as Remote Terminal Units for over 30 years and have used this expertise to design the toughest Ethernet switches on the market. Don't trust your critical communications to so-called industrial hardware from commercial switch manufacturers. Sixnet switches give you proven assurance that your system will keep running for years to come.



SL Models

**ETHERNET PERFORMANCE**

- Unmanaged with 5, 8 or 9 Ethernet ports
- Store & forward wire-speed switching
- Automatic address learning, aging and migration
- Full duplex operation with flow control (no collisions)
- All IEEE 802.3 Ethernet protocols supported
- 1024 MAC addresses supported
- Memory bandwidth 3.2 Gbps
- Typical latency (varies on load)
  - @ 100 Mbps: 5  $\mu$ s + frame time
  - @ 10 Mbps: 16  $\mu$ s + frame time
- Ethernet isolation 1500 VRMS 1 minute

**ETHERNET PORTS**

- Shielded RJ45 ports for 10/100BaseTX
  - Auto-negotiation for 10 or 100 Mbps
  - Auto-MDI/MDIX-crossover for either cable type
  - Auto-polarity corrects for crossed +/- signals
- Fiber optic port speed 100BaseFX (100 Mbps)
- Fiber duplex operation: Full duplex
- Fiber wavelength: 1300 nm center (typical)
- Fiber max. distance (full duplex) (see web for details)
  - 4 km for multimode 50 or 62.5/125  $\mu$ m (SC or ST)
  - 20 km for singlemode 9 or 10/125  $\mu$ m (SC or ST)
  - 40 km (long haul) or more (contact Sixnet)

**ETHERNET COMPLIANCE**

- IEEE 802.3 (10Mbps Ethernet supports legacy devices)
- IEEE 802.3u (Fast Ethernet 100Mbps for newer devices)
- IEEE 802.3x (Full-Duplex with Flow Control)

**POWER INPUT**

- Power input voltage: 10-30 VDC
- Redundant input terminals
- Input power (typical - all ports active at 100 Mbps)
  - 2.0 W (5-port without fiber)
  - 3.0 W (5-port including 1 fiber)
  - 4.0 W (8-port without fiber)
  - 5.0 W (9-port including 1 fiber)
- Transient protection: 15,000 watts peak
- Spike protection: 5,000 watts (10 times for 10  $\mu$ s)

**ENVIRONMENTAL**

- Operating temperature
  - SLX models: -40 to +85°C (cold startup at -40)
  - SL models: -40 to +60°C
- Storage temperature: -40 to +85 °C
- Humidity (non-condensing) 5 to 95% RH
- Vibration and shock: IEC60068-2-6


**STANDARDS COMPLIANCE**

- Electrical safety - UL508/CSA C22.2/14, EN61010-1, CE
- EMC - FCC part 15, ICES-003, EN55022, EN61000-6, CE
- Hazardous locations: ISA 12.12.01 / CSA C22.2/213 (Class I, Div. 2); EN60079-15 (Zone 2, Category 3), CE (ATEX)
- Maritime rated for marine & offshore per ABS
- Eye safety (fiber models) - IEC60825-1, Class 1; FDA 21 CFR 1040.10 and 1040.11

**PHYSICAL**

- Din-rail or direct panel mounting
- Ingress protection: SLX models - IP40, SL models - IP40
- Case: UL94V0 Lexan (SL) or Aluminum (SLX)
- Weight:
  - 4 oz (0.11 kg) – SL-5ES
  - 6 oz (0.17 kg) – SLX-5ES, SL-8/9ES
  - 8 oz (0.23 kg) – SLX-8/9ES
- Dimensions – see mechanical diagram below

All specifications are subject to change. Contact Sixnet to learn more.

**MECHANICAL DRAWINGS****ORDERING GUIDE**

<b>SLX-5ES-1</b>	5 RJ45 10/100 ports
<b>SLX-5ES-2SC</b>	4 RJ45 ports and 1 mm fiber SC, 4 Km
<b>SLX-5ES-2ST</b>	4 RJ45 ports and 1 mm fiber ST, 4 Km
<b>SLX-5ES-3SC</b>	4 RJ45 ports and 1 sm fiber SC, 20 Km
<b>SLX-5ES-3ST</b>	4 RJ45 ports and 1 sm fiber ST, 20 Km
<b>SLX-6ES-4/5</b>	Dual fiber - see separate datasheet
<b>SLX-8ES-1</b>	8 RJ45 10/100 ports
<b>SLX-8ES-6/7</b>	Three fiber - see separate datasheet
<b>SLX-9ES-2SC</b>	8 RJ45 ports and 1 mm fiber SC, 4 Km
<b>SLX-9ES-2ST</b>	8 RJ45 ports and 1 mm fiber ST, 4 Km
<b>SLX-9ES-3SC</b>	8 RJ45 ports and 1 sm fiber SC, 20 Km
<b>SLX-9ES-3ST</b>	8 RJ45 ports and 1 sm fiber ST, 20 Km
<b>SL-</b>	w/Lexan case and limited temperature
<b>ET-PS-024-02</b>	2 Amp, AC to 24 VDC Power Supply
<b>SP-ETH-2</b>	Dual Ethernet port surge & lightning protector

Contact Sixnet for special or long haul fiber transceivers up to 120 Km.



[www.redlion.net/sixnet](http://www.redlion.net/sixnet)  
+1 (518) 877-5173 | [info@redlion.net](mailto:info@redlion.net)

© 2013 Red Lion Controls. All Rights Reserved. FEB 2013

ADLD0203-SL.SLX-589ES-123  
Rev FEB 2013