Applicable Auto Switch Model

Refer to p.5.3-2 to 5.3-75 for the detailed specifications of auto switches.

Applicable Auto Switch Model

					_	_	F	Ree	ed	Sw	itc	h,								,	,	_				_		,	,		S	olio	ı s	tat	e s	Sw	vitc	h,					_		_	_	_			,	_
	Cylinder	D-C7/C8	D-C73C/C80C	D-B5/B6	D-B59W	D-A3/A4	-030444		D-A7/A8	D-A7 □ H/A80H	D-A73C/A80C	D-A79W	D-A5/A6	D-A59W	D-A9/A9	D-9/90A	D-E7 A/E80A	0-Z7/Z8	D-H7	D-H7C	D-H7BAL	0-H7 F	D-H7 UV	D-G5/K5	D-G5BAL	D-G59F	D-G5NTL	0-00 M/N39 W	D-G39/N39	D-57/17	-179C	D-F7	D-F7BAL	D-F7 \\	D-F7NTL	D-F7 UV(V)	D-F5/J5	D-F5BAL	D-F5 0V/J59W	0-F5 F	D-F5NTL	D-G39C/K39C	D-F9/F9 V	D-F9_W/F9_WV	D-F9BAL	D-Y5/Y6/Y7/JY7/JV					
CDJ	J2/RSD																																								-										Ť
CDJ	JP	Γ		t		T	T											T	T				T					T		Γ	T													1		1					t
CDL	J																																																		t
CDC	22															T																												1							t
CDC	QS			T		T	T																1					T		Γ	T													1		T				1	t
MDI	U/CDE1														T																													T							T
CDN	M2																													Γ	Т																				t
CDC	G1					T			1						1													t	T		t																	+			t
CDA	A1/CDNA/CE2	Γ		T		t	t									1		T	Ţ				T	T	T			t	ľ		T													1		T				1	1
MD	B/MDBB					Γ	T																T	Т					T																						1
CDS	61					ſ	T								1	1							1						t		T															+				1	†
CDL	_					t	t								+	+												t	T															1		+				+	
CDE	3			t		t	t								1	+							1	1				+	t															1		+				+	-
CD	/			T		T	ľ															1	1					1	T		T																				-
CD	⊐X			Γ		Γ	T									1			T			T	T	T	T	T	T	T	T		+							T		T											1
CD	Y1			T		T									1	T	T						1								t													1						+	-
MY1	1														1																T																				-
ML1	I/ML2			t		t									T	T	1						1					1	1															T	T	T					ľ
MX/	MTS														1														+		1																			T	1
cxs	6			T		t									T	T	1						1					1	1		T													T						+	1
MG	G/MGC/MLGC					t																						ſ	+		1															T					-
MGC	Q/MGF/MGP/MVGQ			Γ		t	+								╡	+			T				T	T	T		T	T	+		T														1					+	1
MK/	/MK2					1										+	T						1					1	+																ľ	T				+	1
RSF	4																1						1						+		T													T	1						-
RHC	C/REC					t	+								+	+	T											t	t		T													1	T	T				+	-
B	Band					t	t								+							+	+	+			+	+	t		1														1	+					+
Mounting method	Rail			F		ſ	t								+	+	+	+					T	T	T			T															+	+	+	+			+	+	t
oting	Tie-rod	-		\vdash											┥				╡					+	+		+		T														+	-		+			+	+	┦
Mour	Direct	\vdash		\vdash	+	+	T				+	+							╡		+	+	+	+	╡	+	+	+	+		+																				ł
	Function				2 color							2 colour		2 colour							Water resistance	Diagnosis output	2 colour		Water resistance	Diagnosis output	With timer					Diagnosis output	Water resistance		With timer	2 colour		Water resistance	2 colour	Diagnosis output	With timer			2 colour	Water resistance	Mitter and the second	Water resistance		2 colour	Z COIOUI	
	Page	5.3-9	5.3-11	5.3-10			5.2.12	5.3-18	5.3-14	5.3-15		5.3-26			5.3-19/5.3-20	5.3-21/5.3-22	5.3-24	5.3-23	5.3-29	5.3-31	5.3-55	5.3-49/5.3-50		5.3-30			5.3-59		2.3.32	00-0-0	5.3-36	5.3-52/5.3-53	5.3-57		5.3-60	5.3-44/5.3-45 2 colour	5.3-37		5.3-46	ង្ក		5.3-38	5.3-39			5.3-40			5.2-41		

Note 1) D-B7/B8, D-B73C/B80C, D-G7/K7 and D-K79C are applicable for series MGG, MGC and MLGC. Note 2) Series MXS, MXF, MXP, MXQ, MXW and MXU are included in Series MX.





Auto Switch Guide Reed Switch Solid State Switch

Road Switch	
Reed Switch	P 5.3-8
	Contraction of the second seco
General Purpose Style	Р 5.3-9
Band, Rail, Tie-rod, Direct mounting	
•2 Colour Indication Style	Р 5.3-25
Band, Rail, Tie-rod Mounting	
Solid State Switch	P 5.3-28
General Purpose Style	P 5.3-29
Band, Rail, Tie-rod, Direct mounting	
-	Р 5.3-42
Band, Rail, Tie-rod, Direct mounting	
-	Diagnostic Output ·····P 5.3-49
Band, Rail, Tie-rod Mounting	
	n StyleP 5.3-55
Band, Rail, Tie-rod, Direct mounting	Р 5.3-59
Band, Rail, Tie-rod, Direct mounting	
	2 Colour Indication StyleP 5.3-64
	2 Oolour muldulon Otyle

Rail Mounting

1

RB

J


D

-X

20-

Technical Data

SMC Auto Switch Variations



General purpose auto switch



Band mounting


Rail mounting

Tie-rod mounting

Direct mounting

SMC

SMC Auto Switch Variations



5.3-4

▲ Precautions

1	Refer to "Auto Switch Precautions" in p.0-44 to 0-	

Auto Switch Common Specifications

Auto switch style	Reed switch	Solid state switch						
Current leakage	None	3 wire: 100 μA or less, 2 wire: 1mA or less						
Operating time	1.2ms	1ms or less ⁽³⁾						
Shock resistance	300m/s ²	1000m/s ²						
Insulation resistance	50 M Ω or more at 500MV DC (between lead wire and the case)							
Withstand voltage	1500V AC/min. (between lead wire and the case) ⁽¹⁾ (between lead wire and the case							
Ambient temperature	-10 to 60°C							
Protective construction	IEC529 Standard IP67, Waterproof construction (JISC0920) ⁽²⁾							

Note 1) Connector style (D-A73C/A80C/C73C/C80C) and D-9/9□A/A9/A9□V style: 1000V AC/min. (between lead wire and the case)


Note 2) IEC529 Standard IP63, Rainproof construction (JISC0920) for Terminal conduit style (D-A3/A3 C/G39/G39A/G39C/K39/K39A/K39C) and DIN teminal style (D-A44/A44A/A44C).

Note 3) Except solid state switch with timer (D-M5DTL, G5NTL, F7NTL, F5NTL) and Auto switch for strong magnetic field resistance (D-P5DWL). D-J51: 5ms or less

Lead Wire Length

How to Order

Ex.)



 \ast Applicable for the connector style (D- $\ast\ast$ C) only

Note 1) Applicable auto switch with 5 meter lead wire ("Z")

Reed switch: D-B53/B54, D-C73 (C)/C80C,D-A73(C)(H)/A80C D-A53/A54, D-Z73, D-90/97/90A/93A

Solid state switch: Manufactured upon receipt of order as standard (Except D-F9/F9 \Box V)

Note 2) The standard lead wire length of solid state switch with timer or with water resistant 2 colour indication is 3 meters. (Not available 0.5m)

Note 3) The standard lead wire length of strong magnetic field resistant solid state switch is 3 or 5 meters. (Not available 0.5m.)

Part No. of lead wire with connector

(Available for conr	nector style only.)
Part No.	Lead wire length
D-LC05	0.5m
D-LC30	3m
D-LC50	5m

Change of Lead Wire Colour

Lead wire colours of SMC auto switches have been changed in order to meet Nippon Electric Control Equipment Industries Association Standard No. 402.

2 wire au	to swi	tch				
	Old	New				
Output (+)	Red	Brown				
Output (-) Black Blue						

Solid state auto switch with diagnostic output

Old	New
Red	Brown
Black	Blue
White	Black
Yellow	Orange
	Red Black White

3 wire au	to swi	tch						
	Old	New						
Power supply	Red	Brown						
GND	Black	Blue						
Output	White	Black						
Solid state auto switch with latching style diagnostic output								
	yle dia	gnostic output						
	yle dia Old	gnostic output New						
	<u> </u>	<u> </u>						
latching st	Old	New						
latching st Power supply	Old Red	New Brown						

Prior to Use Auto Switch Hysteresis/Contact Protection Box

Contact Protection Box/CD-P11, CD-P12

1

The following auto switches are not incorporated with the contact protection box.

D-A7/A8, D-A7□H/A80H, D-A73C, A80C, D-C7/C8, D-C73C/C80C, D-E7□A, E80A, D-Z7/Z8, D-9/9□A, D-A9/A9□V, and D-A79W type

Use an auto switch with a contact protection box in any case listed below. Unless using a contact protection box, the contact life may be shortened.

(Due to permanent energizing conditions.)

D-A72(H) must be used with the contact protection box

regardless of load styles and lead wire length.

Operating load is an inductive load.

②The wiring length to load is more than 5m.③The load voltage is 100 or 200 V AC.

2

Contact SMC when using built-in contact protection circuit style (D-A34[A] [C], D-A44[A] [C], D-A54/A64, D-B54/B64,

D-A59W, D-B59W) in the following conditions:

(1) The wiring length to load is more than 30m.

2 When using PLC with large flow current

Contact Protection Box/Specifications


Part No.	CD-	P11	CD-P12		
Load voltage	100V AC max.	200V AC	24V DC		
Max. load current	25mA	12.5mA	50mA		

Lead wire length - Switch connecting side 0.5m




Contact Protection Box/Internal Circuit

(): If applicable for IEC Standard




Contact Protection Box/Dimensions



Auto Switch Hysteresis

The distance between the turn-on point (ON) of the switch by moving of the piston to the turn-off point (OFF) is called "Hysteresis". This hysteresis is included as part of the operating range (one side).



Contact Protection Box/Connection Method

For connection of the switch body and the contact protection box, connect the lead wire in the side indicated as "SWITCH" on the contact protection box to the lead wire from the switch body. The length of lead wire between the switch body and the contact protection box should be within 1m and they should be set as close together as possible.




Technical Data


Prior to Use


Auto Switch Connection Method/Connection Example

Basic Wiring



Typical PLC (Programmable Logic Controller) Connection Circuits






Connect according to the input specification of PLC because the connection method varies with the input specification of PLC.

AND (Serial), OR (Parallel) Connection Examples

- •3 wire
- NPN/AND connection (with relay)



NPN/AND connection (with switch) Brown

Blue

Brown

Black

Blue

Switch 1


Switch 2

OR connection


Switch 1

Switch 2

Black Load



NPN/OR connection



Indication lights up when both switches are ON.

Brown

Blue

Brown

Blue

[Solid state switch]

When 2 switches are connected by OR, load voltage will increase at OFF and these connections may cause malfunction

[Reed switch]

There is no current leakage so that load voltage does not increase at OFF.

The flowing current is broken up into the ON-state switches, so indicator light becomes dark or may not turn ON due to the

lack of the current. Load voltage at OFF=Leakage current X 2 pcs. X Load impedance


=1mA X 2 pcs. X 3kΩ

Load

=6V

Example) Supply voltage 24V DC, switch internal drop voltage 4V Example) Load impedance 3kΩ, switch leakage current 1mA

•2 wire (2 pcs.) **AND** connection




Load voltage at ON=Supply voltage-Internal drop voltage X 2 pcs. =24V-4V X 2 pcs. =16V

SMC

Reed Switch

General Purpose Auto Switch 2 colour Indication Style

Reed Switch Variations





Technical Data

Reed Switch/Band Mounting D-C73/D-C76/D-C80

Grommet



Applicable Actuator Series

Series	Bore size (mm)
CDJ2	ø6, ø10, ø16
CDVJ	ø10, ø16
CDLJ2	ø16
CDM2/CDBM2/CDVM3, 5 CDLM2	ø20, ø25, ø32, ø40
CDG1/MGG	ø20, ø25, ø32, ø40, ø50, ø63
CDLG1	ø20, ø25, ø32, ø40
RSDG	ø40, ø50
MGC	ø20, ø25, ø32, ø40, ø50
MLGC/RHC/REC	ø20, ø25, ø32, ø40
Specifications	

Specifications

PLC: Programmable Logic Controller

20mA

40mA


None

1Ω or less (Including 3m lead wire)

D-C7 (With indicator light)						
Auto switch model number	D-	C73	D-C76			
Application	Rela	y/PLC	IC circuit			
Load voltage	24V DC	100V AC	4 to 8V DC			
Max. load current and range	5 to 40mA	5 to 20mA	20mA			
Contact protection circuit						
Internal voltage drop	≤ 2	≤ 2.4V				
Indicator light	ON: \	When red light emitting	diode			
D-C8 (Without indicator lig	iht)					
Auto switch model number		D-C80				
Application	Relay/PLC/IC circuit					
Load voltage	24V $_{\text{DC}}^{\text{AC}}$ or less	48V AC DC	100V AC			

Internal Circuit

(): If not applicable for IEC Standard



② In the case the wiring length to load is more than 5m.
 ③ In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the details of contact protection box. Lead wire - Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.


50mA

Dimensions

Max. load current

Internal resistance

Contact protection circuit



Actuator series				B	ore siz	e					
Actuator series	6	10	16	20	25	32	40	50 10 10 10 10 	63		
CDJ2	6	7	7	—	—	—	-	—	-		
CDVJ	-	7	7	-	-	-	-	-	-		
CDLJ2	-	—	7	-	_	-	-	-	-		
CDM2/CDBM2/CDVM3, 5/CDLM2	-	-	-	7	8	8	8	-	-		
CDG1/MGG	-	—	—	8	10	9	10	10	11		
CDLG1	-	—	—	8	10	9	10	—	-		
RSDG	-	—	—	_	_	_	10	10	-		
MGC	-	_	_	8	10	9	10	10	-		
MLGC/RHC/REC	-	—	—	8	10	9	10	—	-		

Note) Average value at normal temperature including hysteresis. (Tolerance \pm 30%)



Reed Switch/Band Mounting D-B53/D-B54/D-B64

Grommet



Internal Circuit

Reed switch

Reed switch

D-B53

OUT(-) o

Blue(Black)

D-B54

OUT(-) ~ •---Blue(Black)

D-B64

OUT(∓) ~ ^o Blue(Black)

(): If not applicable for IEC Standard

LED

Zener diode

-bì

Resistance

N Surge absorber

Reed switch

Surge absober

LED

Choke coil

-ww

Choke coil

Resistance

Zener diode

0UT(+)

Brown (Red)

OUT(+)~

Brown

(Red)

OUT(±)~

Brown (Red)

Applicable Actuator Series

Series	Bore size (mm)
CDM2, CDBM2, CDVM3/5, CDLM2	ø20, ø25, ø32, ø40
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
CDLG1	ø20, ø25, ø32, ø40
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CE2, CNA	ø40, ø50, ø63, ø80, ø100
MGC	ø20, ø25, ø32, ø40, ø50
MLGC, RHC, REC	ø20, ø25, ø32, ø40

PLC: Programmable Logic Controller


Specifications

		. =•	. egianni		and a second second second	
D-B5 (With indicator light)						
Auto switch model number	D-B53	D-B54				
Application	PLC	Relay/PLC				
Load voltage	24V DC	24V DC	100V	AC	200V AC	
Load current range	5 to 50mA	5 to 50mA	5 to 25	δmA	5 to 12.5mA	
Contact protection circuit	None	Built-in				
Internal voltage drop	≤ 2.4V	≤ 2.4V				
Indicator light	0	ON: When red light emitting diode				
D-B6 (Without indication	ator light)					
Auto switch model number		D-B	64			
Application		Relay/	PLC			
Load voltage	24V AC 200V AC 200V AC					
Max. load current	Max.50mA Max.25mA Max.12.5mA				ax.12.5mA	
Contact protection circuit	Built-in					
Internal resistance	10Ω or less					

Lead wire ——— Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 0.5m

Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions



Operation Range (*t* **Dimension)**

Bore size							
20	25	32	40	50	63	80	100
8	8	9	9	_	_	_	_
8	10	9	10	10	11	11	11
8	10	9	10	-	_	-	_
			0	10			
_	_	_	9	10	11	11	11
8	10	9	10	10	-	-	_
8	10	9	10	-	-	-	_
	8 8 8 8	8 8 8 10 8 10 - - 8 10	8 8 9 8 10 9 8 10 9 - - - 8 10 9	20 25 32 40 8 8 9 9 8 10 9 10 8 10 9 10 8 10 9 10 8 10 9 10 8 10 9 10 9 10 9 10	20 25 32 40 50 8 8 9 9 - 8 10 9 10 10 8 10 9 10 - 9 10 - 8 10 9 10 - 8 10 9 10 - - 9 10 8 10 9 10 10	20 25 32 40 50 63 8 8 9 9 - - 8 10 9 10 10 11 8 10 9 10 - - - - - 9 10 11 8 10 9 10 - - - - - 9 10 11 8 10 9 10 10 -	20 25 32 40 50 63 80 8 8 9 9 - - - 8 10 9 10 10 11 11 8 10 9 10 - - - - - 9 10 11 11 8 10 9 10 - - - - 9 10 11 11 8 10 9 10 10 - - 8 10 9 10 10 - -

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm\,30\%$)

Technical Data



(mm)

Reed Switch/Band Mounting D-C73C/D-C80C

Connector




▲ Caution

Precautions

①Confirm that the connector is appropriately tightened. If tightened insufficiently, the water resistant performance will deteriorate.

2 Refer to p.5.3-68 for the details.

Internal Circuit (): If not applicable for IEC Standard



Note) 1 In the case operation load is an inductive load. 2 In the case the wiring length to load is > 5m. Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the

details of contact protection box.

Applicable Actuator Series

Series	Bore size (mm)			
CDJ2	ø6, ø10, ø16			
CDVJ	ø10, ø16			
CDLJ2	ø16			
CDM2, CDBM2, CDVM3, CDVM5, CDLM2	ø20, ø25, ø32, ø40			
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63			
CDLG1	ø20, ø25, ø32, ø40			
RSDG	ø40, ø50			
MGC	ø20, ø25, ø32, ø40, ø50			
MLGC, RHC, REC	ø20, ø25, ø32, ø40			

PLC: Programmable Logic Controller

(mm)

Specifications


<u> </u>						
D-C73C (With indicator light)						
D-C73C						
Relay/PLC						
24V DC						
5 to 40mA						
None						
≤ 2.4V						
ON: When red light emitting diode						
ator light)						
D-C80C						
Relay/PLC						
\leq 24V $_{DC}^{AC}$						
50mA						
None						
\leq 1 Ω (Including 3m lead wire)						

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length.

Note 3) Lead wire with connector may be shipped with switch.

Dimensions



Operation Range (*l* Dimension)

Actuator series		Bore size							
Actuator series	6	10	16	20	25	32	40	50	63
CDJ2	6	7	7				_	-	—
CDVJ	_	7	7	_	_		—	_	_
CDLJ2	—	—	7	_	_	_	—	_	—
CDM2, CDBM2, CDVM3, CDVM5, CDLM2	—	—	—	7	8	8	8	—	—
CDG1, MGG	—	—	_	8	10	9	10	10	11
CDLG1	—	—	—	8	10	9	10	—	—
RSDG	—	_	-			_	10	10	—
MGC	_	_	_	8	10	9	10	10	_
MLGC, RHC, REC	—	—	_	8	10	9	10	—	—

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



Reed Switch/Band Mounting D-A33/D-A34/D-A44

Terminal conduit: D-A3 DIN terminal: D-A4




▲ Caution

Precautions

- ①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.
- 2 After wiring, confirm that tightening gland and all screws are tightened.

Internal Circuit



Applicable Actuator Series

Series	Bore size (mm)		
CDA1, CDBA1, CDV3, CDVS, CDLA, CE2, CNA	ø40, ø50, ø63, ø80, ø100		
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160		
CDS1	ø125, ø140, ø160, ø180, ø200		
RHC	ø20, ø25, ø32, ø40		


Specifications

Specifications	PLC: Programmable Logic Controlle					
D-A3 (With indicator light) Terminal conduit						
Auto switch model number	D-A33		D-A34			
Application	PLC		Relay/PLC			
Load voltage	24V DC	24V DC	100V AC	200V AC		
Load current range	5 to 50mA	5 to 50mA	5 to 25mA	5 to12.5mA		
Contact protection circuit	None	Built-in				
Internal voltage drop			2.4V			
Indicator light		ON: When red light emitting diode				
D-A44 (With indicator light) DIN terminal						
Auto switch model number	D-A44					
Application	Relav/PLC					

Application	Relay/PLC					
Load voltage	24V DC	100V AC	200V AC			
Load current range	5 to 50mA	5 to 25mA	5 to 12.5mA			
Contact protection circuit	Built-in					
Internal voltage drop	≤ 2.4V					
Indicator light	ON: When red light emitting diode					

Note) Refer to common specifications on p.5.3-5.

Dimensions



Note) Average value at normal temperature including hysteresis. (Tolerance \pm 30%)




Reed Switch/Band Mounting D-A33A/D-A34A/D-A44A

Terminal conduit: D-A3□A **DIN terminal: D-A44A**



Internal Circuit



Applicable Actuator Series

Series CDM2, CDBM2, CDLM2

Bore size (mm) ø20, ø25, ø32, ø40

D-A3□A (With indica	tor light) Te	erminal cond	duit				
Auto switch model number		D-A34A D-A					
Application		Relay/PLC		PLC			
Load voltage	24V DC	100V AC	200V AC	24V DC			
Load current range	5 to 50mA	5 to 25mA	5 to12.5mA	5 to 50m			
Contact protection circuit		Built-in		None			
Internal voltage drop		≤	2.4V	•			
Indicator light	ON: When red light emitting diode						
D-A44A (With indicat	tor light) DI	V terminal					
Auto switch model number		D-4	\44A				
Application		Rela	y/PLC				
Load voltage	24V DC	100	IV AC	200V AC			
Load current range	5 to 50m/	A 5 to	25mA	5 to12.5mA			
Contact protection circuit	Built-in						
Internal voltage drop	≤2.4V						
Indicator light	ON: When red light emitting diode						

▲ Caution


Precautions

①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.


2 After wiring, confirm that tightening gland and all screws are tightened.

Dimensions





D-A44A



Note) Average value at normal temperature including hysteresis. (Tolerance ± 30%)

CDLM2

8

8

9

Reed Switch/Rail Mounting **D-A72/D-A73/D-A80**





Applicable Actuator Series

Series	Bore size (mm)
CDJ2, CDVJ	ø10, ø16
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CDXW	Plate mounted ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40
RSDQ	ø16, ø20, ø32, ø40, ø50
MDU	ø25, ø32, ø40, ø50, ø63
CE1	ø12, ø20, ø32, ø40, ø50, ø63
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63
СХТ	ø32, ø40

Specifications

Internal resistance

Dimensions

PLC: Programmable Logic Controller

D-A7 (With indicator light)						
Auto switch model number	D-A72 D-A73					
Application	Relay/PLC	Relay/PLC Relay/PLC				
Load voltage	200V AC	200V AC 24V DC 100V /				
Load current range	5 to 10mA	5 to 40mA	5 to 20mA			
Contact protection circuit	None					
Internal voltage drop	≤ 2.4V					
Indicator light	ON: V	Vhen red light emitting	g diode			
D-A8 (Without indicate	or light)					
Auto switch model number		D-A80				
Application	Relay/IC circuit/PLC					
Load voltage	24V ^{AC} _{DC} or less 48V ^{AC} _{DC} 100V ^{AC} _{DC}					
Max. load current	50mA	40mA	20mA			
Contact protection circuit	None					


1Ω or less (Including 3m lead wire)

(11.7)

1.5

Internal Circuit

(): If not applicable for IEC Standard



Note) ①In the case operation load is an inductive load. ②In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100 or 200V AC.

(3) In the case the load voltage is 100 of 200V AC. Be sure to use the auto switch with the contact protection box in any case mentioned above.

D-A72 must be used with contact protection box. Refer to p.5.3-6 for the details of contact protection box.

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on the p.5.3-5. Note 2) Refer to the p.5.3-5 for lead wire length.

Operation Range (*l* Dimension)

																	()
Actuator se	arion								Bore	size							
Actuator se	enes	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CD	/J	-	8	—		9	—	—	-	—		—	—	-	—	-	—
CDQ2		-	-	10	-	12	12	12	12	11	10	12	12	13	13	13	13
CDXW	В		-			6	6	6	6								
CDAW	Ρ		6		_	6	6	6	6								
CDY1S		6	6	-	6	-	6	6	6	6	—	—	—	-	—	-	—
CY1L		6	6	—	6	-	6	6	6	6	—	—	—	_	—	—	_
RSDQ		-	-	-	-	-	12	12	12	11	10	—	—	-	—	-	—
MDU		-	_	—	—	—	—	13	13	13	13	13	—	-	—	—	_
CE1		-	—	10	-	-	12	-	12	11	10	12	—	-	—	—	-
MK, MK2		-	—	-	-	-	12	12	12	11	10	12	—	-	—	-	-
СХТ		-	—	_	—	-	—	_	12	11	—	_	—	—	—	—	_

Note) Average value at normal temperature including hysteresis. (Tolerance \pm 30%)

SMC

(mm)

5.3-14

Reed Switch/Rail Mounting

Grommet Electrical entry : In-line



Applicable Actuator Series

Series Bore size (mm) CDJ2, CDVJ Ø10, Ø16 CDQ2 Ø12, Ø16, Ø20, Ø25, Ø32, Ø40, Ø50, Ø63, Ø80, Ø100, Ø125, Ø140, Ø160 CDXW Plate mounted Ø10, Ø16, Ø20, Ø25, Ø32, Housing mounted Ø16, Ø20, Ø25, Ø32 CDY1S, CY1L Ø6, Ø10, Ø15, Ø20, Ø25, Ø32, Ø40 RSDQ Ø16, Ø20, Ø32, Ø40, Ø50 MDU Ø25, Ø32, Ø40, Ø50, Ø63 CE1 Ø12, Ø20, Ø32, Ø40, Ø50, Ø63 MK, MK2 Ø20, Ø25, Ø32, Ø40, Ø50, Ø63 CXT Ø32, Ø40		
CDQ2 ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160 CDXW Plate mounted ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32 CDY1S, CY1L ø6, ø10, ø15, ø20, ø25, ø32, ø40 RSDQ ø16, ø20, ø32, ø40, ø50 MDU ø25, ø32, ø40, ø50, ø63 CE1 ø12, ø20, ø32, ø40, ø50, ø63 MK, MK2 ø20, ø25, ø32, ø40, ø50, ø63	Series	Bore size (mm)
CDXW Plate mounted ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32 CDY1S, CY1L ø6, ø10, ø15, ø20, ø25, ø32, ø40 RSDQ ø16, ø20, ø32, ø40, ø50 MDU ø25, ø32, ø40, ø50, ø63 CE1 ø12, ø20, ø32, ø40, ø50, ø63 MK, MK2 ø20, ø25, ø32, ø40, ø50, ø63	CDJ2, CDVJ	ø10, ø16
CDY1S, CY1L ø6, ø10, ø15, ø20, ø25, ø32, ø40 RSDQ ø16, ø20, ø32, ø40, ø50 MDU ø25, ø32, ø40, ø50, ø63 CE1 ø12, ø20, ø32, ø40, ø50, ø63 MK, MK2 ø20, ø25, ø32, ø40, ø50, ø63	CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
RSDQ Ø16, Ø20, Ø32, Ø40, Ø50 MDU Ø25, Ø32, Ø40, Ø50, Ø63 CE1 Ø12, Ø20, Ø32, Ø40, Ø50, Ø63 MK, MK2 Ø20, Ø25, Ø32, Ø40, Ø50, Ø63	CDXW	Plate mounted ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32
MDU ø25, ø32, ø40, ø50, ø63 CE1 ø12, ø20, ø32, ø40, ø50, ø63 MK, MK2 ø20, ø25, ø32, ø40, ø50, ø63	CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40
CE1 ø12, ø20, ø32, ø40, ø50, ø63 MK, MK2 ø20, ø25, ø32, ø40, ø50, ø63	RSDQ	ø16, ø20, ø32, ø40, ø50
MK, MK2 Ø20, Ø25, Ø32, Ø40, Ø50, Ø63	MDU	ø25, ø32, ø40, ø50, ø63
· · · · · · · · · · · · · · · · · · ·	CE1	ø12, ø20, ø32, ø40, ø50, ø63
CXT Ø32, Ø40	MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63
	СХТ	ø32, ø40

Specifications

PLC: Programmable Logic Controller

(mm)

D-A7 H (With indicator light)										
Auto switch model number	D-A72H	D-A	73H	D-A76H						
Application	Relay/PLC	Relay/PLC Relay/PLC IC c								
Load voltage	200V AC	24V DC	C 4 to 8V DC							
Max. load current and range	5 to 10mA	5 to 40mA	5 to 20m	A 20mA						
Contact protection circuit		No	one							
Internal voltage drop	≤ 2.4V 0.8V 0									
Indicator light	ON: Whe	en red light emitt	ing diode							
D-A80H (Without indic	ator light)									
Auto switch model number	D-A80H									
Applications	Relay/IC circuit/PLC									
Load voltage	24V ^{AC} or le	ss 48	V AC DC	100V ^{AC} _{DC}						
Max. load current	50mA	40	mA	20mA						

 Internal resistance
 1Ω or less (Including 3m lead wire)

 • Lead wire — Oilproof vinyl heavy insulation cable, 0.2mm², 2 cores (Brown, Blue), 3 cores (Brown, Black, Blue), 0.5m


 Note 1) Refer to common specifications on p.5.3-5.

 Note 2) Refer to p.5.3-5 for lead wire length.

None

Dimensions

Contact protection circuit




Operation Range (*t* Dimension)

Actuator se	rico								Bore	size							
Actuator se	nes	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDV	J,	-	8	-	—	9	-	_	—	—	_	—	—	-	—	—	—
CDQ2		-	-	10	—	12	12	12	12	11	10	12	12	13	13	13	13
CDXW	В		-			6	6	6	6								
CDXW	Ρ] —	6		_	6	6	6	6	_	_	-	_	-	_	_	_
CDY1S		6	6	-	6	—	6	6	6	6	—	—	—	—	—	—	—
CY1L		6	6	-	6	-	6	6	6	6	—	-	—	-	—	—	—
RSDQ		—	—	—	—	—	12	12	12	11	10	—	—	—	—	—	—
MDU		-	-	-	—	—	-	13	13	13	13	13	—	-	—	—	—
CE1		-	_	10	—	_	12	—	12	11	10	12	—	-	_	—	_
MK, MK2		-	—	-	—	—	12	12	12	11	10	12	—	-	—	—	—
СХТ		—	—	—	—	—	—	—	12	11	—	—	—	—	—	—	—
	arage value at permit to including bysteresis. (Telerapee + 30%)																

Internal Circuit

(): If not applicable for IEC Standard



Heed switch	Contact OUT(±) protection Brown(Red) box to CD-P11 to CD-P12 OUT(∓) Blue(Black)

Note) ①In the case operation load is an inductive load. ②In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100 or 200V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above.

D-A72H must be used with contact protection box. Refer to p.5.3-6 for the details of contact protection box.

Reed Switch/Rail Mounting **D-A73C/D-A80C**

Connector




▲ Caution Precautions

 Confirm that the connector is appropriately tightened. If tightened insufficiently, the water resistant performance will deteriorate.
 Refer to p.5.3-68 for the details.

Internal Circuit

(): If not applicable for IEC Standard




Note) (1)In the case operation load is an inductive load. (2)In the case the wiring length to load is ">" 5m.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the details of contact protection box.

Applicable Actuator Series

Series		Bore size (mm)						
CDJ2, CDVJ		ø10, ø16						
CDQ2	ø12, ø16,	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160						
CDXW	Plate mounted	d ø10, ø16, ø20, ø25, ø32, Housing mounted ø16, ø20, ø25, ø32						
CDY1S, CY1L		ø6, ø10, ø15, ø20, ø25, ø32, ø40						
RSDQ		ø16, ø20, ø32, ø40, ø50						
MDU		ø25, ø32, ø40, ø50, ø63						
CE1		ø12, ø20, ø32, ø40, ø50, ø63						
MK, MK2		ø20, ø25, ø32, ø40, ø50, ø63						
СХТ		ø32, ø40						
Specificatior	PLC: Programmable Logic Controll							
-A73C (With indicator light)								
Auto switch mo	del number	D-A73C						
Application		Relay/PLC						
Load voltage	24V DC							
Load current ra	nge	5 to 40mA						
Contact protect	ion circuit	None						
Internal voltage	drop	≤ 2.4V						
Indicator light		ON: When red light emitting diode						
D-A80C (Wit	hout indic	ator light)						
Auto switch mo	Auto switch model number D-A80C							
Application Relay/IC circuit/PLC								
Load voltage		24V _{DC}						
Max. load current 50mA								
Contact protection circuit None								
Internal resistar	nce	1Ω or less (Including 3m lead wire)						
●Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm ² , 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length. Note 3) Lead wire with connector may be shipped with switch.								

Dimensions



Indicator light D-A80C:

Operation Range (*ℓ* Dimension)

SMC

Actuator se	rios								Bore	size							
Actual01 Set	103	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDV	J	—	- 8 -		_	9	_	_	—	—	_	—	—	—	—	—	_
CDQ2		—	—	10	_	12	12	12	12	11	10	12	12	13	13	13	13
ODYW	в		—			6	6	6	6								
CDXW	Ρ	_	6		_	6	6	6	6	-	_	-	_	-	_	_	_
CDY1S		6	6	_	6	_	6	6	6	6	_	—	—	-	—	—	_
CY1L		6	6	—	6	—	6	6	6	6	—	—	—	-	—	—	_
RSDQ		—	—	_	_	—	12	12	12	11	10	—	—	—	—	—	—
MDU		—	—	—	—	—	—	13	13	13	13	13	—	—	—	—	_
CE1		—	—	10	_	—	12	—	12	11	10	12	—	—	—	—	_
MK, MK2		—	—	—	—	—	12	12	12	11	10	12	—	—	—	—	—
CXT		—	—	—	_	—	_	_	12	11	_	—	—	—	_	—	-
Note) Average va	Note) Average value at normal temperature including hysteresis. (Tolerance ± 30%) 5 3-16																

5.3-16

RB

J

D

-X

20-

Technical

Data

(mm)

Reed Switch/Tie-rod Mounting

Grommet



Applicable Actuator Series

Series	Bore size (mm)
CDA1, CDBA1, CDV3, CDVS, CDLA, CE2, CNA	ø40, ø50, ø63, ø80, ø100
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CDS1	ø125, ø140, ø160, ø180, ø200
MDB, MDBB	ø32, ø40, ø50, ø63, ø80, ø100

PLC: Programmable Logic Controllar

(mm)

Specifications

D-A5 (With indicator light)										
Auto switch model number	D-A53	D-A54 D-A56								
Application	PLC	Relay/PLC IC circuit								
Load voltage	24V DC	24V DC 100V AC 200V AC 4 to 8V DC								
Max. load current	E . E . A	5 · 5 · 4	5 · 05 · 4							
and range	5 to 50mA	5 to 50mA	5 to 25mA	5 to 12.5mA	20mA					
Contact protection circuit	None Built-in None									
Internal voltage drop	2.4V 0.8V or less									
Indicator light	ON: When red light emitting diode									

D-A6 (Without indicator light)


(
Auto switch model number		D-A64							
Application		Relay/PLC							
Load voltage	\leq 24V $\frac{\text{AC}}{\text{DC}}$	MAX. 24V DC							
Max. load current	50mA	30mA							
Contact protection circuit		None							
Internal resistance		$\leq 1\Omega$ (Including 3m lead wire)							

Lead wire ——Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 0.5m or ø4, 0.2mm², 3 cores (Brown, Black, Blue), 0.5m

Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length

Dimensions



D-A64/A67: without indicator light


Operation Range (*l* **Dimension)**

Actuator series	Bore size												
Actuator series	32	40	50	63	80	100	125	140	160	180	200		
CDA1, CDBA1, CDV3, CNA, CDVS, CDLA, CE2	_	9	10	11	11	11	_	_	-	_	_		
CDL1	—	9	10	11	11	11	10	10	10	—	—		
CDS1	_	—	_	—	_	—	10	10	10	10	10		
MDB, MDBB	9	9	10	11	11	11	—	_	_	_	—		

Note) Average value at normal temperature including hysteresis. (Tolerance \pm 30%)

Internal Circuit

(): If not applicable for IEC Standard



5.3-17




Reed Switch/Tie-rod Mounting D-A33C/D-A34C/D-A44C

Terminal conduit: D-A3□C **DIN terminal: D-A44C**



Internal Circuit



Applicable Actuator Series

Series	Bore size (mm)
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CE2, CNA	ø40, ø50, ø63, ø80, ø100

Specifications		PL	.C: Programmabl	e Logic Controller					
D-A3 C (With indicator light) Terminal conduit									
Auto switch model number	D-A33C	D-A33C D-A34C							
Application	PLC	PLC Relay/PLC							
Load voltage	24V AC	24V DC	100V AC	200V AC					
Load current range	5 to 50mA	5 to 50mA	5 to 25mA	5 to 12.5mA					
Contact protection circuit	None		Built-in						
Internal voltage drop	≤2.4V								
Indicator light	ON: When red light emitting diode								
D-A44C (With indica	tor light) DI	V terminal							
Auto switch model number		D-A	44C						
Application		Relay	/PLC						
Load voltage	24V DC	100	/ AC	200V AC					
Load current range	5 to 50m/	A 5 to 2	25mA	5 to 12.5mA					
Contact protection circuit	Built-in								
Internal voltage drop		≤ 2	.4V						
Indicator light	ON: When red light emitting diode								

Note) Refer to common specifications on p.5.3-5.

▲ Caution

①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.

Precautions


2 After wiring, confirm that tightening gland and all screws are tightened.

J D -X 20-

RB

Technical

Dimensions




∂SMC


Reed Switch/Direct Mounting D-A90/D-A93/D-A96

Grommet **Electrical entry: In-line**



Internal Circuit (): If not applicable for IEC Standard






Note) 1 In the case operation load is an inductive load. 2 In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the details of contact protection box

Dimensions



Operation Range (ℓ Dimension)

Actuator						В	ore si	ze					
series	6	8	10	12	16	20	25	32	40	50	63	80	100
CDU	5	Ι	6	—	9	11	12.5	14	-	-	-	_	-
CDQS	-	—	—	6	7.5	10	10	—	-	-	-	_	—
CDQ2	—	-	-	—	-	-	-	9.5	9.5	9.5	11.5	9	11.5
MY1	-	—	—	—	5	5	-	—	-	-	-	_	—
MXU	5	-	6	_	9	-	-	-	-	-	-	_	—
MXW	-	6	—	6	8.5	10	10	—	-	-	-	—	—
MXF	-	4.5	-	5	6	7	-	—	-	-	-	_	—
MXS	4.5	5	—	6	7	8	8	—	-	—	-	—	—
F 0 10													

Applicable Actuator Series

Series	Bore size (mm)
CDU	ø6, ø10, ø16, ø20, ø25, ø32
CDQS	ø12, ø16, ø20, ø25
CDQ2*	ø32, ø40, ø50, ø63, ø80, ø100
MY1	ø16, ø20
MXU	ø6, ø10, ø16
MXW	ø8, ø12, ø16, ø20, ø25
MXF	ø8, ø12, ø16, ø20
MXS/MXQ	ø6, ø8, ø12, ø16, ø20, ø25
*Not applicable	for CDQP2

Series	Bore size (mm)
MXP	ø10, ø12, ø16
MTS	ø20, ø25, ø32, ø40
СХТ	ø12, ø16, ø20, ø25, ø32, ø40
МК	ø12, ø16
MK2	ø32, ø40, ø50, ø63
RSQ	ø12, ø32, ø40, ø50
CEP	ø12, ø20
CY1R	ø6, ø10, ø15, ø20
	•

Specifications

PLC: Programmable Logic Controller

D-A90 (Withou	ut indicator light)								
Auto swich modle number	D-A90								
Application	IC circuit/Relay/PLC								
Load voltage	$24V \frac{AC}{DC}$ or less $48V \frac{AC}{DC}$ or less $100V \frac{AC}{DC}$ or								
Max. load current	50mA	40mA	20mA						
Contact protection circuit		None							
Internal resistance	1Ω or less (Including 3m lead wire)								
D-A93/D-A96 (With indicator lig	ght)							
Auto switch model number	D-A93 D-A96								
Application	Relay	//PLC	IC circuit						
Load voltage	24V DC	100V AC	4 to 8V DC						
Max. load current and load current range	5 to 40mA	5 to 20mA	20mA						
Contact protection circuit		None							
Internal voltage drop	\leq 2.4V (up to 20mA)/≤ 3V (up to 40mA)	≤ 0.8V						
Indicator light	ON: When red light emitting diode								
 Lead wire 									

D-A90/D-A93 Oilproof vinyl heavy insulation cable, ø2.7, 0.18mm² X 2cores (Brown, Blue), 0.5m Oilproof vinyl heavy insulation cable, ø2.7, 0.15mm² X 3cores (Brown, Black, Blue), 0.5m D-A96-Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length

▲ Caution

Precautions

①Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

Operation Range (*l* **Dimension)**

Actuator						Bore	e size					
series	6	8	10	12	15	16	20	25	32	40	50	63
MXQ	4.5	5	—	6	—	7	8	9	—	—	—	
MXP	Ι	_	5	5	—	5	—	—	—	_	—	_
MTS	—	—	—	—	—	—	7.5	8	7	8	—	-
СХТ	Ι	_	_	6	_	7.5	10	10	9.5	9.5	—	—
MK	—	—	—	6	—	7.5	—	—	—	—	—	-
MK2	Ι	_	_	—	—	—	—	—	9.5	9.5	9.5	11.5
RSQ	—	_	—	—	—	—	—	—	9.5	9.5	9.5	-
CEP	—	—	—	5	—	—	6.5	—	—	—	—	-
CY1R	9	—	13	—	8	—	6	—	—	—	-	-
Note) Avera	Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)											

(mm)

5.3-19



(mm)


Reed Switch/Direct Mounting D-A90V/D-A93V/D-A96V





Internal Circuit

(): If not applicable for IEC Standard



Note) 1 In the case operation load is an inductive load. 2 In the case the wiring length to load is ">" 5m.


Blue(Black)

DC(-

 $\textcircled{3}\ensuremath{\mathsf{In}}$ the case the load voltage is 100V AC. Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the details of contact protection box

(-)

Dimensions



Operation Range (*l* Dimension)

Actuator						В	ore siz	ze	_				
series	6	8	10	12	16	20	25	32	40	50	63	80	100
CDU	5	—	6	—	9	11	12.5	14	—	—	-		-
CDQS		_	_	6	7.5	10	10	_	_	_	-	-	
CDQ2	_	—	-	—	-	—	—	9.5	9.5	9.5	11.5	9	11.5
MY1	Ι	_	_	—	5	5	-	_	-	_	-		_
MXU	5	—	6	—	9	—	-	—	—	—	-	—	-
MXW		6	_	6	8.5	10	10	-	_	—	-	_	-
MXF	_	4.5	_	5	6	7	-	-	_	_	-	_	-
MXS	4.5	5	_	6	7	8	8	—	—	—	-		-

Applicable Actuator Series

Series	Bore size (mm)
CDU	ø6, ø10, ø16, ø20, ø25, ø32
CDQS	ø12, ø16, ø20, ø25
CDQ2*	ø32, ø40, ø50, ø63, ø80, ø100
MY1	ø16, ø20
MXU	ø6, ø10, ø16
MXW	ø8, ø12, ø16, ø20, ø25
MXF	ø8, ø12, ø16, ø20
MXS/MXQ	ø6, ø8, ø12, ø16, ø20, ø25
*Not applicable	for CDQP2

Series Bore size (mm) MXP ø10, ø12, ø16 MTS ø20, ø25, ø32, ø40 СХТ ø12, ø16, ø20, ø25, ø32, ø40 MK ø12, ø16 MK2 ø32, ø40, ø50, ø63 RSQ ø12, ø32, ø40, ø50 CEP ø12. ø20 CY1R ø6, ø10, ø15, ø20

PLC: Programmable Logic Controller

Specifications

D-A90V (Without indicator light)

D-A90V (With	out maleator light	9							
Auto swich model number	D-A90V								
Application		IC circuit/Relay/PLC							
Load voltage	24V ^{AC} _{DC} or less 48V ^{AC} _{DC} or less 100V ^{AC} _{DC} or les								
Max. load current	50mA	40mA	20mA						
Contact protection circuit		None							

Internal resistance 1Ω or less (Including 3m lead wire)

D-A93V/D-A96	6V (With indicator	[·] light)						
Auto switch model number	D-A93V D-A96V							
Application	Relay	IC circuit						
Load voltag	24V DC	4 to 8V DC						
Max. load current and load current range	5 to 40mA	20mA						
Contact protection circuit		None						
Internal voltage drop	2.7V or less 0.8V or less							
Indicator light	ON: When red light emitting diode							
Lead wire								

D-A90V/D-A93V -

- Oilproof vinyl heavy insulation cable, ø2.7, 0.18mm² X 2cores (Brown, Blue), 0.5m Oilproof vinyl heavy insulation cable, ø2.7, 0.15mm² X 3cores (Brown, Black, Blue), 0.5m D-A96V-Note 1) Refer to common specifications on p.5.3-5 Note 2) Refer to p.5.3-5 for lead wire length.

Caution

Precautions

①Fix the switch with appropriate screw installed on the switch body. If using other screws, switch may be damaged.

RB

J

D

-X

20-

Operation Range (*t* **Dimension)**

Actuator						Bore	size					
series	6	8	10	12	15	16	20	25	32	40	50	63
MXQ	4.5	5	_	6	—	7	8	9	—	-	—	-
MXP	—	—	5	5	—	5	-	—	-	-	—	-
MTS	—	-	-	-	-	-	7.5	8	7	8	—	-
СХТ	—	—	—	6	—	7.5	10	10	9.5	9.5	—	-
MK	—	-	—	6	—	7.5	-	—	-	-	—	-
MK2	—	—	—	—	—	—	-	—	9.5	9.5	9.5	11.5
RSQ	-	-	—	-	—	-	-	—	9.5	9.5	9.5	-
CEP	—	_	_	5	_	_	6.5	_	_	-	_	_
CY1R	9	—	13	-	8	—	6	—	—	-	—	-
Note) Avera	de valu	ue at n	ormal	tempe	rature	includi	na hvs	teresis	. (Tole	rance	±30%)

⁄////

(mm)

(mm)

Reed Switch/Direct Mounting D-90/D-97

Grommet
Lead wire: Parallel cord



Applicable Actuator Series

Series	Bore size (mm)
CDJP-□D	ø6, ø10, ø15
CDU	ø6, ø10, ø16, ø20, ø25, ø32

Specifications

Specifications	PLC: Programmable Logic Controller						
D-90 (Without indicator lig	jht)						
Auto switch model number	D-90						
Application	Relay/IC circuit/PLC						
Load voltage	5V AC 12V AC 24V						
Max. load current	50mA						
Internal resistance	1Ω or less (Including 3m lead wire)						
D-97 (With indicator light)							
Auto switch model number		D-97					
Application		Relay/PLC					
Load voltage		24V DC					
Load current range	5 to 40mA						
Internal voltage drop	≤ 2.4V						
Indicator light	ON: When red light emitting diode						
Load wire — Vinul parallel cable 0.2mm	2 2 00r00 0 Em						


• Lead wire — Vinyl parallel cable, 0.2mm², 2 cores, 0.5m


Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions

D-90





Operation Range (*l* **Dimension)**


Actuator series			Bore size							
Actuator	6	10	15	16	20	25	32			
CDJP	-□D	5.5 8 9			-					
0011	Without shield plate		7	—	9	11	12	14		
CDU	With shield plate	-	-	-	7	8	8	9		

(mm)

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

Internal Circuit

(): If not applicable for IEC Standard



Note) (1)In the case operation load is an inductive load. (2)In the case the wiring length to load is ">" 5m.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the details of contact protection box

SMC

Reed Switch/Direct Mounting D-90A/D-93A

Gror	nmet
Lead wire: Heavy	insulation cable



Applicable Actuator Series

Series	Bore size (mm)
CDJP-□D	ø6, ø10, ø15
CDU	ø6, ø10, ø16, ø20, ø25, ø32

Specifications

Load current range

Indicator light

Dimensions

D-90A

D-93A

Internal voltage drop

Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

21

l Ś

23

Specifications	PLC: Programmable Logic Controller						
D-90A (Without indicator	light)						
Auto switch model number		D-	90A				
Application	Relay/IC circuit/PLC						
Load voltage	5V AC DC	5V AC 12V AC 24V AC					
Max. load current		50mA		20mA			
Internal resistance	1Ω	2 or less (Inclu	ding 3m lead v	wire)			
D-93A (With indicator ligh	t)						
Auto switch model number	D-93A						
Application	Relay/PLC						
Load voltage	24V DC 100V AC						

5 to 40mA

ő3.

Operation range (Refer to the table below.)

Most sensitive position

• Lead wire — Oilproof vinyl heavy insulation cable, 0.2mm², 2 cores (Brown, Blue), 0.5m

5 to 20mA

RB

J

D

-X

20-


Technical

Data

 $\leq 2.4V$

ON: When red light emitting diode

Internal Circuit



Note) (1)In the case operation load is an inductive load. ②In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the details of contact protection box.

(): If not applicable for IEC Standard

2 Operation range (Refer to the table below.) Most sensitive position 29 Indicator light

 \square

Operation Range (/ Dimension)									
Actuato		Bore size							
Actuato	6	10	15	16	20	25	32		
CDJF	P-□D	5.5 8 9					—		
Without shield plate		5.5	7	-	9	11	12	14	
CDU	With shield plate	—	—	—	7	8	8	9	

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



Reed Switch/Direct Mounting D-Z73/D-Z76/D-Z80

Grommet



Applicable Actuator Series

D-77 (With indicator light)

Series	Bore size (mm)
MGQ, MVGQ, MGP	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
CXS	ø6, ø10, ø15, ø20, ø25, ø32
RSH	ø20, ø32, ø50, ø63, ø80
MY1B	ø25, ø32, ø40, ø50, ø63, ø80, ø100
MY1M, MY1C, CY1R	ø25, ø32, ø40, ø50, ø63
MY1H, ML2B	ø25, ø32, ø40
MGF	ø40, ø63, ø100
CY1H	ø10, ø15, ø20, ø25, ø32

Specifications

PLC: Programmable Logic Controller

100V $\frac{AC}{DC}$ or less

20mA

(mm)

Auto swich model number	D-2	D-Z76						
Application	Relay	IC circuit						
Load voltage	24V DC	4 to 8V DC						
Max. load current and load current range	5 to 40mA 5 to 20mA		20mA					
Contact protection circuit	None							
Internal voltage drop	\leq 2.4V (up to 20mA)/≤ 3V (up to 30mA)	≤ 0.8V					
Indicator light	ON: V	Vhen red light emitting	diode					
D-Z8 (Without indicator light)								
Auto switch model number	D-Z80							

Relay/PLC/IC circuit

48V $\frac{AC}{DC}$ or less


40mA

None

1Ω or less (Including 3m lead wire)

Internal Circuit

(): If not applicable for IEC Standard



Note) ①In the case operation load is an inductive load. ②In the case the wiring length to ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to the p.5.3-6 for the details of contact protection box. • Lead wire – Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

24V $\frac{AC}{DC}$ or less

50mA

Dimensions


Application

Load voltage

Max. load current

Internal resistance

Contact protection circuit



Operation Range (*t* **Dimension)**

Actuator series		Bore size											
Actuator series	6	10	12	15	16	20	25	32	40	50	63	80	100
MGQ, MVGQ	-	—	7.5	—	8.5	9.5	9.5	11	11	11	13	13	14
CXS	9	7	_	9	-	9	9	11	—	_	—	_	—
MGP		—	7.5	—	10	10	10	10.5	10.5	10.5	11.5	11.5	12
RSH	_	—	_	—	-	8.5	_	7	—	9.5	10.5	11.5	—
MY1B		—		—	—	—	12	12	12	12	12	12	12
MY1M, MY1C	_	—	_	—	-	—	12	12	12	12	12	_	—
MY1H, ML2B		-	-	—	-	—	12	12	12		-	-	—
MGF		—		—	-	—		-	13.5		12		13
CY1H	—	8	—	6	-	6	6	9	—	—	-	—	_
CY1R		-	-	—	-	-	9	9	11	11	11	-	—

Reed Switch/Direct Mounting D-E73A/D-E76A/D-E80A

Grommet





Applicable Actuator Series

Series	Bore size (mm)
CDBX	ø10
ML1	ø25, ø32, ø40

PLC: Programmable Logic Controller

Specifications

D-E7 A (With indicator light)								
Auto swich model number	D-E	D-E76A						
Application	Relay	IC circuit						
Load voltage	24V DC	4 to 8V DC						
Max. load current and load current range	5 to 40mA	5 to 40mA 5 to 20mA						
Contact protection circuit		None						
Internal voltage drop	≤2	≤ 0.8V						
Indicator light	ON: When red light emitting diode							


D-E80A (Without indicator light)

Auto switch model number		D-E80A					
Application		Relay/PLC/IC circuit					
Load voltage	24V $\frac{AC}{DC}$ or less	48V AC DC	100V AC				
Max. load current	50mA	40mA	20mA				
Contact protection circuit		None					
Internal resistance	1Ω or less (Including 3m lead wire)						

- Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Lead wire Note 1) Refer to common specifications on p.5.3-5

Note 2) Refer to p.5.3-5 for lead wire length


Internal Circuit (): If not applicable for IEC Standard



Note) 1 In the case operation load is an inductive load. 0 In the case the wiring length to load is ">" 5m. ③In the case the load voltage is 100V AC.

Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to p.5.3-6 for the details of contact protection box.

Dimensions



25 CDBX 6 ML1 6

10

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

32

6

40

6

2 Colour Indication Style Reed Switch/Band Mounting **D-B59W**

Grommet

The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)



Applicable Actuator Series

Series	Bore size (mm)					
CDM2, CDBM2, CDVM3, CDVM5, CDLM2	ø20, ø25, ø32, ø40					
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100					
CDLG1	ø20, ø25, ø32, ø40					
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CE2, CNA	ø40, ø50, ø63, ø80, ø100					
MGC	ø20, ø25, ø32, ø40, ø50					
MLGC, RHC, REC	ø20, ø25, ø32, ø40					

Specifications

PLC: Programmable Logic Controller


(mm)

D-B59W (With indicator light)						
Auto switch model number	D-B59W					
Application	Relay/PLC					
Load voltage	24V DC					
Load current range	5 to 40mA					
Contact protection circuit	Built-in					
Internal voltage drop	≤ 4V					
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode					


Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5.
 Note 2) Refer to the p.5.3-5 for lead wire length.

Internal Circuit

(): If not applicable for IEC Standard



Dimensions



Operation Range (ℓ Dimension)

Actuator series	Bore size								
Actuator series	20	25	32	40	50	63	80	100	
CDM2, CDBM2, CDVM3, CDVM5, CDLM2	12	12	13	13	_	_	_	_	
CDG1	13	13	14	14	14	17	16	18	
CDLG1	13	13	14	14	—	—	—	—	
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CNA, CE2	-	_	_	14	14	17	16	18	
MGG, MGC	13	13	14	14	14	—	—	—	
MLGC, RHC, REC	13	13	14	14	_	_	_	_	

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

2 Colour Indication Style Reed Switch/Rail Mounting **D-A79W**

Grommet

The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)



Applicable Actuator Series

Series	Bore size (mm)				
CDJ2, CDVJ	ø10, ø16				
CDLJ2	ø16				
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160				
RSDQ	ø20, ø25, ø32, ø40, ø50				
MDU	ø25, ø32, ø40, ø50, ø63				
CE1	ø12, ø20, ø32, ø40, ø50, ø63				
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63				
CXT	ø32, ø40				


Specifications

PLC: Programmable Logic Controller

D-A79W (With indicator light)							
Auto switch model number	D-A79W						
Application	Relay/PLC						
Load voltage	24V DC						
Load current range	5 to 40mA						
Contact protection circuit	None						
Internal voltage drop	≤ 4V						
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode						

Internal Circuit


(): If not applicable for IEC Standard



Note) ①In the case operation load is an inductive load. ②In the case the wiring length to load is more than 5m. Be sure to use the auto switch with the contact protection box in any case mentioned above. Refer to the p.5.3-6 for the details of contact protection box. Generation of the second second

Note 1) Refer to common specifications on the p.5.3-5. Note 2) Refer to the p.5.3-5 for lead wire length.


Dimensions



Operation Range (*t* **Dimension)**

Actuator series	Bore size															
Actuator series	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDVJ	-	11	—	—	13	—	—	-	—	—	—	—	-	—	—	_
CDLJ2	-	—	—	—	13	—	—	_	—	—	-	—	—	—	—	-
CDQ2	—	—	13	—	13	13	13	13	14	14	16	15	17	17	17	17
RSDQ	-	—	—	—	—	13	13	13	14	14	-	—	—	—	—	-
MDU	—	—	—	—	—	—	13	13	14	14	14	—	—	—	—	—
CE1	_	—	13	—	—	13	—	13	14	14	16	—	-	-	—	_
MK, MK2	—	—	—	—	—	13	13	13	14	14	16	—	—	—	—	—
CXT	—	—	—	—	—	—	—	13	14	—	—	—	—	—	—	—

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)



(mm)

2 Colour Indication Style Reed Switch/Tie-rod Mounting **D-A59W**

Grommet

The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)



Applicable Actuator Series

	-					
Series	Bore size (mm)					
CDA1, CDBA1, CDV3, CDVS, CDLA, CE2, CNA	ø40, ø50, ø63, ø80, ø100					
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160					
CDS1	ø125, ø140, ø160, ø180, ø200					
MDB, MDBB	ø32, ø40, ø50, ø63, ø80, ø100					
Specifications	PLC: Programmable Logic Controller					
D-A59W (With indicator light	ght)					
Auto switch model number	D-A59W					
Application	Relay/PLC					
Load voltage	24V DC					
Load current range	5 to 40mA					
Contact protection circuit	Built-in					
Internal voltage drop	≤ 4V					
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode					

0.5


9

•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5.


Note 2) Refer to p.5.3-5 for lead wire length

Internal Circuit

(): If not applicable for IEC Standard



Dimensions



Operation Range (*t* **Dimension)**

(mm) Bore size Actuator series 32 40 50 63 80 100 125 140 160 180 200 CDA1, CDBA1, CDV3, CDVS, 13 13 14 14 15 _ CDLA, CE2, CNA CDL1 13 14 17 17 17 _ _ 13 14 15 CDS1 17 17 17 17 17 MDB, MDBB 15 13 13 13 14 14 _

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

Solid State Switch

General Purpose Auto Switch, 2 Colour Indication Style, 2 Colour Indication Style with Diagnostic Output, Water Resistant 2 Colour Indication Style, With Timer, Strong Magnetic Field Resistant Style

			- •			
Style	Function	Mounting method	Electrical entry	Auto switch model No.	Page	
			Г	D-H7A1/H7A2/H7B	5.3-29	
			Grommet	D-G59/G5P/K59	5.3-30	
		Band	Connector	D-H7C	5.3-31	
	itch		- · · · · · ·	D-G39/K39	5.3-32	
	SW		Terminal conduit	D-G39A/K39A	5.3-33	
	auto switch			D-F79/F7P/J79	5.3-34	
		Rail	Grommet	D-F7NV/F7PV/F7BV	5.3-35	
	o		Connector	D-J79C	5.3-36	
	General purpose	Tie week	Grommet	D-F59/F5P/J51/J59	5.3-37	
	d la	Tie-rod	Terminal conduit	D-G39C/K39C	5.3-38	
	lera		Г	D-M9N/M9P/M9B	5.3-39	
	Gen			D-M9NV/M9PV/M9BV		
		Direct	Grommet	D-Y59A/Y59B/Y7P	5.3-40	
				D-Y69A/Y69B/Y7PV		
				D-M5N/M5P/M5B	5.3-41	
	yle		Г	D-H7NW/H7PW/H7BW	5.3-42	
	l stj	Band	Grommet	D-G59W/G5PW/K59W	5.3-43	
	tion			D-F79W/F7PW/J79W	5.3-44	
<u> </u>	icat	Rail	Grommet	D-F7NWV/F7BWV	5.3-45	
itc	ind	Tie-rod	Grommet	D-F59W/F5PW/J59W	5.3-46	
Ms	ar		Г	D-M5NW/M5PW/M5BW	5.3-47	
Solid state switch	Colour indication style	Direct	Grommet	D-Y7NW/Y7PW/Y7BW	5.3-48	RB
tal	2 (D-Y7NWV/Y7PWV/Y7BWV		1
s S				D-F9NW/F9PW/F9BW	5.3-66	J
olic			L	D-F9NWV/F9PWV/F9BWV		D
ы С	vle		Г	D-H7LF(Latching style)	5.3-49	-X
	utpi	Band	Grommet	D-H7NF	5.3-50	· ^
	lication style			D-G59F	5.3-51	20-
	nost	Dell	Grommet	D-F7LF(Latching style)	5.3-52	
	2 Colour india with diagnos	Rail	Gioniniet	D-F79F	5.3-53	
	ith c	Tip rod	Grommet	D-F59F		Technical Data
	2 × 0	Tie-rod		D-F5LF(Latching style)	5.3-65	Jala
	/le		Г	D-H7BAL	5.3-55	
	Water resistant 2 colour indication style	Band	Grommet	D-G5BAL	5.3-56	
	er rec	Rail	Grommet	D-F7BAL	5.3-57	
	Wate 2 ndio	Tie-rod	Grommet	D-F5BAL	5.3-58	
		Direct	Grommet	D-Y7BAL	5.3-63	
			L	D-F9BAL	5.3-67	
	<u>ب</u>	Band	Grommet	D-G5NTL	5.3-59	
		Rail	Grommet	D-F7NTL	5.3-60	
	With timer	Tie-rod	Grommet	D-F5NTL	5.3-61	
	Š	Direct	Grommet	D-M5NTL/M5PTL	5.3-62	
	netic I re- ince	Rail	Grommet	D-P5DWL	5.3-64	
	Magnetic field re- sistance	nali	Gioniniet	D-FJDWL		
					5 3-28	

Solid State Switch/Band Mounting D-H7A1/D-H7A2/D-H7B

Grommet



Applicable Actuator Series

Series	Bore size (mm)
CDJ2	ø6, ø10, ø16
CDVJ3, CDVJ5	ø10, ø16
CDLJ2	ø16
CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, REC	ø20, ø25, ø32, ø40
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63
RSDG	ø40, ø50
MGC	ø20, ø25, ø32, ø40, ø50
RHC, MLGC	ø20, ø25, ø32, ø40

Specifications


PLC: Programmable Logic Controller

(mm)

D-H7 (With indicator light)							
Auto switch model number	D-H7A1	D-H7A2	D-H7B				
Wiring	3 w	/ire	2 wire				
Output	NPN	PNP	_				
Application	IC circuit/F	24V DC Relay/PLC					
Power voltage	5/12/24V DC (4	_					
Current consumption	10mA	-					
Load voltage	28V DC or less	28V DC or less –					
Load current	40mA or less	80mA or less	5 to 40mA				
Internal voltage drop		4V or less					
Current leakage	≤ 100μA a	at 24V DC	≤ 0.8mA at 24V DC				
Indicator light	ON: When red light emitting diode						


Internal Circuit

(): If not applicable for IEC Standard



• Lead wire— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5 Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions



Operation Range (*l* **Dimension)**

Bore size Actuator series 6 10 15 16 20 25 32 40 50 63 CDJ2 3 4 4 CDVJ3, CDVJ5 4 4 _ _ _ _ CDLJ2 4 CDM2, CDBM2, CDVM3, 5 4 4 4.5 _ _ _ CDVM5, CDLM2, CDLG1, REC CDG1, MGG 4 4 4.5 5 6 6.5 RSDG 5 6 MGG, MGC 4 4 4.5 6 5 RHC, MLGC 4 4 4.5 5

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

SMC

Solid State Switch/Band Mounting D-G59/D-G5P/D-K59

Grommet



Applicable Actuator Series

Series	Bore size (mm)			
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100			
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CNA	ø40, ø50, ø63, ø80, ø100			
MGC	ø20, ø25, ø32, ø40, ø50			
RHC, MLGC, REC	ø20, ø25, ø32, ø40			
CE2	ø40, ø50, ø63, ø80, ø100			

Specifications


PLC: Programmable Logic Controller

D-G5□/D-K59 (With indicator light)						
Auto switch model number	D-G59	D-G5P	D-K59			
Wiring	3 w	2 wire				
Output	NPN	PNP	—			
Application	IC circuit/F	IC circuit/Relay/PLC				
Power voltage	5/12/24V DC (4	—				
Current consumption	10mA	—				
Load voltage	28V DC or less	—	24V DC (10 to 28V DC)			
Load current	40mA or less	80mA or less	5 to 40mA			
Internal voltage drop	1.5V or less (0.8V or less at 10mA) of load current	0.8V or less	4V or less			
Current leakage	≤ 100μA a	\leq 0.8mA at 24V DC				
Indicator light	ON: When red light emitting diode					

•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Internal Circuit


(): If not applicable for IEC Standard



D-K59

0 DC(--)

Dimensions



Operation Range (*t* **Dimension)**

Actuator series		Bore size							
Actuator series	20	25	32	40	50	63	80	100	
CDG1, MGG	4	4	4.5	5	6	6.5	6.5	7	
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CNA	_	_	_	5	6	6.5	6.5	7	
MGC	4	4	4.5	5	6	-	—	—	
RHC, MLGC, REC	4	4	4.5	5	-	—	—	—	
CE2	—	-	—	5	6	6.5	6.5	7	

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

(mm)

RB

J

D

-X

20-

Technical

Data

Solid State Switch/Band Mounting D-H7C

Connector



▲ Caution

Precautions

①Confirm that the connector is appropriately tightened. If tightened insufficiently, the water resistant performance will deteriorate. 2 Refer to p.5.3-68 for the details.

Applicable Actuator Series

Series	Bore size (mm)
CDJ2	ø6, ø10, ø16
CDVJ3, CDVJ5	ø10, ø16
CDLJ2	ø16
CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, REC	ø20, ø25, ø32, ø40
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63
RSDG	ø40, ø50
MGC	ø20, ø25, ø32, ø40, ø50
RHC, MLGC	ø20, ø25, ø32, ø40

Specifications


PLC: Programmable Logic Controller

(mm)

D-H7C (With indicator I	D-H7C (With indicator light)					
Auto switch model number	D-H7C					
Wiring	2 wire					
Output	_					
Application	24V DC Relay/PLC					
Power voltage	_					
Current consumption	_					
Load voltage	24V DC (10 to 28V DC)					
Load current	5 to 40mA					
Internal voltage drop	≤ 4V					
Current leakage	≤ 0.8mA at 24V DC					
Indicator light	ON: When red light emitting diode					

•Lead wire ---- Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions




Operation Range (*l* **Dimension)**

Actuator series	Bore size									
Actuator series	6	10	15	16	20	25	32	40	50	63
CJ2	5	8	-	9	—	-	—	—	—	-
CDVJ3, CDVJ5	_	8	-	9	_		_	—	—	_
CDLJ2	—	_	—	9	—	_	—	—	—	_
CDM2, CDBM2, CDVM3, CDVM5, CDM2, CDLG1, REC	_	_	_	—	7	8.5	9	10	—	_
CDG1, MGG	_		-	—	7	8.5	9	10	9.5	10.5
RSDQ	_	_	_	_	—	_	—	10	9.5	—
MGC	—		—	—	7	8.5	9	10	9.5	-
RHC, MLGC	—	-	—	—	7	8.5	9	10	—	_

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

Internal Circuit (): If not applicable for IEC Standard



Solid State Switch/Band Mounting **D-G39/D-K39**

Terminal conduit



Applicable Actuator Series

Series		Bore size (mm)			
CDA1, CDBA1, CDV3, CD	VS1, CDLA, CNA	ø40, ø50, ø63, ø80, ø100			
CDL1		ø40, ø50, ø6	3, ø80, ø100, ø125, ø140, ø160		
CDS1		ø125,	ø140, ø160, ø180, ø200		
CE2		ø40), ø50, ø63, ø80, ø100		
RHC			ø20, ø25, ø32, ø40		
Specifications					
D-G39/D-K39 (Wit	h indicator l	ight)			
Auto switch model number	D-G39		D-K39		
Wiring	3 wi	re	2 wire		
Output	NP	N			
Application	IC circuit/R	elay/PLC	24V DC Relay/PLC		
Power voltage	5/12/24V DC (4	.5 to 28V DC)			
Current consumption	≤ 1 0i	mA			
Load voltage	≤ 28V	DC	24V DC (10 to 28V DC)		
Load current	≤ 40i	mA	5 to 40mA		
Internal voltage drop	≤ 1.5 (0.8V or less) (of load curr	at 10mA	≤ 4V		
Current leakage	100µA or less	at 24V DC	0.8mA or less at 24V DC		
Indicator light		ON: When red lig	pht emitting diode		

▲ Caution


Precautions

^①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.

②After wiring, confirm that tightening gland and all screws are tightened.

Note) Refer to common specifications on p.5.3-5

Dimensions



Technical
Data

(mm)

RB

J

D

-X

20-

Operation Range (*t* **Dimension)**


Actuator series	Bore size												
Actuator series	20	25	32	40	50	63	80	100	125	140	160	180	200
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	_	_	_	9	9	10	10	11	_		_	_	_
CDL1	-	-	—	9	9	10	10	11	11	11	10	—	_
CDS1	—	—	—	—	—	—	—	—	11	11	10	10	10
CE2	—	—	—	9	9	10	10	11	—		_	-	-
RHC	8	9	9	9	-	—	-	-	—	_	_	_	—

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

SMC

5.3-32

Internal Circuit



Solid State Switch/Band Mounting D-G39A/D-K39A

Terminal conduit



▲ Caution

Precautions

①Use cable whose O. D. is within the size in the figure to maintain water resistant performance.

2 After wiring, confirm that tightening gland and all screws are tightened.

D-G39A ODC(+) 1st terminal ĸ main ∘out Switch 2nd terminal circuit ODC(-) 3rd terminal **D-K39A** \land OUT(+) 1st terminal mair Switch circuit 么 •OUT(−) 2nd termina

Applicable Actuator Series


Series	Bore size (mm)
CDM2, CDBM2, CDLM2	ø20, ø25, ø32, ø40

Specifications

Specifications	PLC: Programmable Logic Controller				
D-G39A/D-K39A					
Auto switch model number	D-G39A	D-K39A			
Wiring	3 wire	2 wire			
Output	NPN	—			
Application	IC circuit/Relay/PLC	24V DC Relay/PLC			
Power voltage	5/12/24V DC (4.5 to 28V DC)	—			
Current consumption	≤ 10mA	—			
Load voltage	≤ 28V DC	24V DC (10 to 28V DC)			
Load current	≤ 40mA	5 to 40mA			
Internal voltage drop	1.5V or less (0.8V or less at 10mA) of load current	4V or less			
Current leakage	100µA or less at 24V DC	0.8mA or less at 24V DC			
Indicator light	ON: When red light emitting diode				

Note) Refer to common specifications on p.5.3-5.

Dimensions



Operation Range (*l* **Dimension)**

Operation Range (ℓ Dimension)				(mm)			
Actuator series	Bore size						
Actualor series		25	32	40			
CDM2, CDBM2, CDLM2	8	9	9	9			
Note) Average value at normal temperature including hysteresis (Tolerance +30%)							

ue at normal temperature including hysteresis. (Tolerance ±30%)

Internal Circuit

Solid State Switch/Rail Mounting D-F79/D-F7P/D-J79

Grommet



Applicable Actuator Series

Series	Bore size (mm)
CDJ2, CDVJ3, CDVJ5	ø10, ø16
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CD□XW	Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40
RSDQ	ø20, ø25, ø32, ø40, ø50
MDU	ø25, ø32, ø40, ø50, ø63
CE1	ø12, ø20, ø32, ø40, ø50, ø63
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63
СХТ	ø32, ø40

Specifications


PLC: Programmable Logic Controller

D-F7□/D-J79 (With indicator light)												
Auto switch model number	D-F79	D-J79										
Wiring	3 w	2 wire										
Output	NPN	PNP	—									
Application	IC circuit/F	24V DC Relay/PLC										
Power voltage	5/12/24V DC (4	—										
Current consumption	≤ 10											
Load voltage	\leq 28V DC		24V DC (10 to 28V DC)									
Load current	≤ 40mA	80mA or less	5 to 40mA									
Internal voltage drop	1.5V or less (0.8V or less at 10mA) of load current	0.8V or less	4V or less									
Current leakage	≤ 100μA a	tt 24V DC	\leq 0.8mA at 24V DC									
Indicator light	ON: \	ON: When red light emitting diode										

Internal Circuit


(): If not applicable for IEC Standard


D-F79



•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions







Technical Data

(mm)

Operation Range (*l* Dimension)

Actuator series			Bore size														
		6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDVJ3, C	DVJ5	-	5	-	—	5	—	—	-	—	—	—		—	-	—	—
CDQ2		—	—	5.5	—	6	5.5	5	6	6	6	6.5	6.5	7	9	9	8.5
CD XW B	В		—			4	0.5	3.5	4								
	Ρ		3		_	2.5	3.5	3.5	2.5								
CDY1S, CY1	L	3	3	—	4	—	3	3	3	3.5	—	—		—		_	—
RSDQ		—	—	—	—	—	5.5	—	6	6	6	—	_	—	_	—	—
MDU			—	—	—	—	-	6.5	7	6.5	6.5	6.5		—		-	—
CE1		—	—	5.5	—	—	5.5	—	6	6	6	6.5	_	—	—	—	—
MK, MK2			—	—	—	—	5.5	5	6	6	6	6.5		—			—
СХТ		—	_	—	_	-	-	-	6	6	-	-	_	-	—	_	—

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)



Solid State Switch/Rail Mounting D-F7NV/D-F7PV/D-F7BV

Grommet **Electrical entry: Perpendicular**



Applicable Actuator Series

Series	Bore size (mm)
CDJ2, CDVJ3, CDVJ5	ø10, ø16
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CD□XW	Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40
RSDQ	ø20, ø32, ø40, ø50
MDU	ø25, ø32, ø40, ø50, ø63
CE1	ø12, ø20, ø32, ø40, ø50, ø63
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63
СХТ	ø32, ø40

Specifications


PLC: Programmable Logic Controller

D-F7□V (With inc	licator light)								
Auto switch model number	D-F7NV	D-F7PV	D-F7BV						
Wiring	3 w	ire	2 wire						
Output	NPN	—							
Application	IC circuit/F	24V DC Relay/PLC							
Power voltage	5/12/24V DC (4	_							
Current consumption	≤ 10	_							
Load voltage	\leq 28V DC		24V DC (10 to 28V DC)						
Load current	≤ 40mA	≤ 80mA	5 to 40mA						
Internal voltage drop	1.5V or less (0.8V or less at 10mA) of load current	0.8V or less	4V or less						
Current leakage	≤ 100μA a	t 24V DC	≤ 0.8mA at 24V DC						
Indicator light	ON: When red light emitting diode								

ngm ıy

•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions




Actuator series						_		Bore	size		_					
Actuator series	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDVJ3, CDVJ5	_	5	Ι	-	5	-	—	_	—	-	—		I	Ι	—	_
CDQ2	-	—	5.5	—	6	5.5	5	6	6	6	6.5	6.5	7	9	9	8.5
CD XW B		—			4	0.5	3.5	4								
		3			2.5	3.5	3.5	2.5								
CDY1S, CY1L	3	3		4	—	3	3	3	3.5	—	-	_	Ι		-	-
RSDQ	_	—	—	—	—	5.5	—	6	6	6	—	-	-	—	—	—
MDU	-	—	-	—	—	-	6.5	7	6.5	6.5	6.5	-	Ι		—	_
CE1	_	—	5.5	—	—	5.5	—	6	6	6	6.5	-	—	—	—	—
MK, MK2	—	—	—	—	—	5.5	5	6	6	6	6.5	—	—	—	—	_
СХТ	_	-	_	_	_	-	_	6	6	_	_	_	_	_	_	_

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

Internal Circuit

(): If not applicable for IEC Standard

D-F7NV




OUT Black(White)

DC(–) Blue(Black)

circuit



Solid State Switch/Rail Mounting **D-J79C**




▲ Caution

Precautions

 Confirm that the connector is appropriately tightened. If tightened insufficiently, the waterproof performance will deteriorate.
 Refer to p.5.3-68 for the details.

Internal Circuit

(): If not applicable for IEC Standard



Applicable Actuator Series

Series	Bore size (mm)
001100	
CDJ2, CDVJ3, CDVJ5	ø10, ø16
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CD□XW	Plate mounted ø10, ø16, ø20, ø25, ø32 Housing munted ø16, ø20, ø25, ø32
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40
RSDQ	ø20, ø32, ø40, ø50
MDU	ø25, ø32, ø40, ø50, ø63
CE1	ø12, ø20, ø32, ø40, ø50, ø63
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63
СХТ	ø32, ø40

Specifications


D-J79C									
Auto switch model number	D-J79C								
Wiring	2 wire								
Output	_								
Application	24V DC Relay/PLC								
Power voltage	_								
Current consumption	_								
Load voltage	24V DC (10 to 28V DC)								
Load current	5 to 40mA								
Internal voltage drop	≤ 4V								
Current leakage	≤ 0.8mA at 24V DC								
Indicator light	ON: When red light emitting diode								

PLC: Programmable Logic Controller

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 2 cores (Brown, Blue), 0.5m

Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions



Operation Range (*t* **Dimension)**

Indicator light

Actuator series									Bore	size							
Actuator se	nes	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDVJ3, C	DVJ5	—	5	-		5	—	—	—	-	—	—	—	-		-	—
CDQ2		—	—	5.5	_	6	5.5	5	6	6	6	6.5	6.5	7	9	9	8.5
	В		—	_		4	0.5	3.5	4	_							
CD□XW	Ρ		3] —	_	2.5	3.5	3.5	2.5						_	_	
CDY1S, CY1	IL	3	3	-	4	-	3	3	3	3.5	—	-	—	-	—	-	—
RSDQ		-	—	-	_	-	5.5	-	6	6	6	-	—	-	—	-	—
MDU		—	—	-	—	-	—	6.5	7	6.5	6.5	6.5	—	-	—	—	—
CE1		-	—	5.5	_	-	5.5	-	6	6	6	6.5	—	-	—	-	—
MK, MK2		—	_	-	_	-	5.5	5	6	6	6	6.5	_	-	—	—	—
СХТ		—	—	-		-	—	—	6	6	—	—	—	-	-	—	—

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)




(mm)

Solid State Switch/Tie-rod Mounting D-F5 //D-J5


Grommet




Internal Circuit (): If not applicable for IEC Standard









Applicable Actuator Series

Series	Bore size (mm)					
CDA1, CDBA1, CDV3, CDVS1,	ø40, ø50, ø63, ø80, ø100					
CDLA, CNA						
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160					
CDS1	ø125, ø140, ø160, ø180, ø200					
CE2	ø40, ø50, ø63, ø80, ø100					
MDB	ø32, ø40, ø63, ø80, ø100					

Specifications

PLC: Programmable Logic Controller


(mm)


D-F5□/D-J5□								
Auto switch model number	D-F59	D-F5P	D-J59	D-J51				
Wiring	3 w	/ire	2 wire					
Output	NPN	PNP		—				
Application	IC circuit/F	Relay/PLC	24V DC Relay/PLC	AC Relay/PLC				
Power voltage	5/12/24V DC (4	4.5 to 28V DC)						
Current consumption	≤ 10)mA		—				
Load voltage	≤ 28V DC		24V DC (10 to 28V DC)	80 to 260V AC				
Load current	≤ 40mA	≤ 80mA	5 to 40mA	5 to 80mA				
Internal voltage drop		0.8V or less	4V or less	14V or less				
Current lookage			< 0.8mA at 24V DC	≤ 1mA at 100 V DC				
Current leakage $\leq 100\mu$ A at 24V DC		al 24V DC	≤ 0.011A at 24V DC	≤ 1.5mA at 200V DC				
Indicator light		ON: When red light emitting diode						

Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m
 Note 1) Refer to common specifications on the p.5.3-5.
 Note 2) Refer to the p.5.3-5 for lead wire length.

Dimensions

*D-J51 differs in the shape, most sensitive position and operation range from other switches. Contact SMC for the details.





Operation Range (*l* **Dimension)**

											()
Actuator series	Bore size										
Actuator series	32	40	50	63	80	100	125	140	160	180	200
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	_	4	4	4.5	4.5	4.5	—	—	_		_
CDL1	-	4	4	4.5	4.5	4.5	5	5	5.5	—	—
CDS1	-	—	—	—	-	-	5	5	5.5	6	6
CE2	-	4	4	4.5	4.5	4.5	_	_		_	_
MDB	3.5	4	4	4.5	4.5	4.5	—	—	—	-	—



Solid State Switch/Tie-rod Mounting **D-G39C/D-K39C**

Terminal conduit



▲ Caution

Internal Circuit

mair

Switch

mair

Switch I

sircuit

К

К

D-G39C

D-K39C

Precautions

Use cable whose O. D. is within the size in the figure to maintain water resistant performance.

②After wiring, confirm that tightening gland and all screws are tightened.

• DC(+)

OUT

DC(–) 3rd terminal

OUT(+)

1st terminal

OUT(–) 2nd terminal


1st terminal

2nd terminal

Applicable Actuator Series

Se	Bore size (mm)				
CDA1, CDBA1, CDV3, C	DVS1, CDLA, CDL1, CNA	ø40, ø50, ø63, ø80, ø100			
C	E2	ø40, ø50, ø63, ø80, ø100			
Specifications	.C: Programmable Logic Controller				
D-G39C/D-K39C					
Auto switch model number	D-G39C	D-K39C			
Wiring	3 wire	2 wire			
Output	NPN				
Application	IC circuit/Relay/PLC	24V DC Relay/PLC			
Power voltage	5/12/24V DC (4.5 to 28V DC)				
Current consumption	≤ 10mA				
Load voltage	≤ 28V DC	24V DC (10 to 28V DC)			
Load current	≤ 40mA	5 to 40mA			
Internal voltage drop	≤ 1.5V (≤ 0.8V at 10mA of load current) ≤ 4V			
Current leakage	100µA or less at 24V DC	0.8mA or less at 24V DC			
Indicator light ON: When red light emitting diode					
Note 1) Refer to common specifica	itions on p.5.3-5.				

Dimensions



Operation Range (*t* **Dimension)**

Actuator series	Bore size							
Actuator series	40	50	63	80	100			
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CNA	9	10	11	11	11			
CE2	9	10	11	11	11			

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

Dimensions

Auto switch part number	Bore size (mm)	С	нพ	Н	H'	Т	T'	Z
D-G39C-4, D-K39C-4	40	44	69	57	49.5	7.5	6.5	
D-G39C-5, D-K39C-5	50	52	77	58	50.5	8.5	6.5	M5 X 16
D-G39C-6, D-K39C-6	63	64	91	60.5	52	10.5	7.5	M5 X 20
D-G39C-8, D-K39C-8	80	78	107	64	53.5	12.5	9.5	
D-G39C-10, D-K39C-10	100	92	121	67	56.5	15.5	9.5	M5 X 25




Technical Data

Solid State Switches: Direct Mounting Type D-M9N(V), D-M9P(V), D-M9B(V)

Grommet


- 2-wire load current is reduced (2.5 to 40 mA).
 Lead-free
- Use of lead wire compliant with UL standards (style 2844)
- 1.5 times the flexibility compared with conventional products (comparison with other SMC products)




▲Caution Operating Precautions

When the cable sheath is stripped, confirm the stripping direction.

The insulator may be split or damaged depending on the direction.



Auto Switch Internal Circuit



Auto Switch Specifications

Refer to www.smcworld.com for details of products compatible with overseas standards.

Unit: g

	PLC: Programable Logic Controller									
D-M9 ⁽⁾ (with indicator light)										
Switch model	D-M9N	D-M9P	D-M9B							
Wiring type	3-w	vire	2-wire							
Output type	NPN	PNP	—							
Applicable load	IC circuit, F	24 VDC relay, PLC								
Power supply voltage	5, 12, 24 VDC	_								
Current consumption	10 mA	or less	—							
Load voltage	28 VDC or less	—	24 VDC (10 to 28 VDC)							
Load current	40 mA	or less	2.5 to 40 mA							
Internal voltage drop	0.8 V (4 V or less								
Leakage current	100 μA or less at 24 VDC 0.8 mA or less									
Indicator light	Red LED lights when ON									

• Lead wire Oil proof heavy duty vinyl cord: 2.7 × 3.2 ellipse

D-M9B $0.15 \text{ mm}^2 \times 2 \text{ cores}$

D-M9N, D-M9P 0.15 mm² \times 3 cores Note 1) Refer to page 15 for solid state auto switch common specifications and lead wire length.

Note 1) Refer to page 15 for solid state auto switch common specifications and lead

Weight

Auto switch model		D-M9N(V)	D-M9P(V)	D-M9B(V)
Lood wire longth m	0.5	8	8	7
Lead wire length m	3	41	41	38


Dimensions

D-M9




4

Mounting screw M2.5 x 4 L Slotted set screw



Most sensitive position

20



6

5.3-39

2.8

Solid State Switch/Direct Mounting D-Y59^A/D-Y69^A/D-Y7P(V)



Applicable Actuator Series

Series	Bore size (mm)					
MGQ, MVGQ, MGP	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100					
CXS	ø6, ø10, ø15, ø20, ø25, ø32					
MY1B	ø25, ø32, ø40, ø50, ø63, ø80, ø100					
MY1C, MY1M, CY1R	ø25, ø32, ø40, ø50, ø63					
MY1H, ML2B	ø25, ø32, ø40					
MGF	ø40, ø63, ø100					
CY1H	ø10, ø15, ø20, ø25, ø32					
RSH	ø20, ø32, ø50, ø63, ø80					

Specifications

Dimensions

D-Y59B

- 🕑

2.5

6.2

D-Y59A, D-Y7P,

12.5


Ø 🖁


PLC: Programmable Logic Controller

D-Y5/D-Y6/D-Y7P/D-Y7PV (With indicator light)										
Auto switch model number	D-Y59A	D-Y69A	D-Y7P	D-Y7PV	D-Y59B	D-Y69B				
Electrical entry	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular				
Wiring		3 w	/ire		2 ۷	wire				
Output	N	PN	PI	NP	-	-				
Application		IC circuit/F		24V DC Relay/PLC						
Power voltage	5,	/12/24V DC (4	C)	_						
Current consumption		≤ 10)mA		_					
Load voltage	≤ 28	V DC	-	_	24V DC (10) to 28V DC)				
Load current	≤ 40	OmA	80mA	or less	5 to 40mA					
Internal voltage drop		or less ss at 10mA rrent	0.8V	or less	4V o	r less				
Current leakage		100µA or les	0.8mA or lea	ss at 24V DC						
Indicator light		ON: When red light emitting diode								

ndicator light ON: When red light emitting diode

•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.15mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.





Operation Range (*t* Dimension)

F.

29


Indicator light

03.4

Actuator corico		Bore size											
Actuator series	6	10	12	15	16	20	25	32	40	50	63	80	100
MGQ, MVGQ	—	-	5	-	6	6	6.5	8.5	8.5	9	10	10	11.5
CXS	3	3	—	3.5	—	3.5	4	4.5	—	—	—	—	-
MGP	—	-	5.5	-	7.5	7.5	7	6.5	6	7	8	9.5	10
MY1B	—	—	—	—	—	—	6	9	10	3.5	3.5	3.5	3.5
MY1C, MY1M	—	—	-	—	—	—	5	5	5	5.5	5.5	—	_
MY1H	—	—	—	—	—	—	6	9	10	—	—	—	—
RSH	—	—	-	—	—	7.5	-	5	—	6.5	7.5	10	—
CY1R	—	—	—	—	—	—	7	6	6	7	6	—	—
CY1H	—	6	-	5	—	5	5	6	—	-	-	—	—
ML2B	-		—	—	—	_	6	6	6	-	—	_	_
MGF	-	-	-	—	-	-	-	-	9	-	5	-	7.5
Note) Average value at no	Average value at normal temperature including hysteresis. (Tolerance +30%)												

Internal Circuit

(): If not applicable for IEC Standard



o OUT(—) Blue(Black)

5.3-40

(mm)

RB J D -X 20-

Technical Data

Solid State Switch/Direct Mounting D-M5N/D-M5P/D-M5B

Grommet



Applicable Actuator Series

Series	Bore size (mm)
MYC	ø25, ø32, ø40
МҮН	ø25, ø32, ø40
ML1	ø25, ø32, ø40


Specifications

PLC: Programmable Logic Controller

D-M5⊡(With indicator light)								
Auto switch model number	D-M5N	D-M5P	D-M5B					
Wiring	3 w	vire	2 wire					
Output	NPN	PNP	—					
Application	IC circuit/F	24V DC Relay/PLC						
Power voltage	5/12/24V DC (4	—						
Current consumption	≤ 10)mA	—					
Load voltage	≤ 28V DC	—	24V DC (10 to 28V DC)					
Load current	≤ 40mA	≤ 80mA	5 to 40mA					
Internal voltage drop	1.5V or less (0.8V or less at 10mA) of load current	0.8V or less at 10mA) 0.8V or less						
Current leakage	≤ 100μA a	≤ 0.8mA at 24V DC						
Indicator light	ON: When red light emitting diode							

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions




Operation Range (*l* Dimension) (mm)

Actuator series	Bore size						
Actuator series	25	32	40				
MYC	4	4	4				
MYH	4	4	4				
ML1	4	4	4				

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

Internal Circuit

(): If not applicable for IEC Standard



2 Colour Indication Style Solid State Switch/Band Mounting D-H7NW/D-H7PW/D-H7BW


Grommet

The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)



Internal Circuit

(): If not applicable for IEC Standard



Suitable operating point

Applicable Actuator Series

Series	Bore size (mm)
CDJ2	ø6, ø10, ø16
CDVJ3, CDVJ5	ø10, ø16
CDLJ2	ø16
CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, REC	ø20, ø25, ø32, ø40
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63
RSDG	ø40, ø50
MGC	ø20, ø25, ø32, ø40, ø50
RHC, MLGC	ø20, ø25, ø32, ø40


Specifications

PLC: Programmable Logic Controller

D-H7□W(With	indicator light)					
Auto switch model number	D-H7NW	D-H7PW	D-H7BW			
Wiring	3 w	vire	2 wire			
Output	NPN	PNP	—			
Application	IC circuit/F	Relay/PLC	24V DC Relay/PLC			
Power voltage	5/12/24V DC (4	_				
Current consumption	≤ 10					
Load voltage	≤ 28V DC		24V DC (10 to 28V DC)			
Load current	≤ 40mA	≤ 80mA	5 to 40mA			
Internal voltage drop	1.5V or less (0.8V or less at 10mA) of load current	0.8V or less	4V or less			
Current leakage	100μA or les	0.8mA or less at 24V DC				
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode					

• Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions



RB J D -X 20-



Operation Range (*l* Dimension)

Actuator series	Bore size											
Actuator series	6	10	15	16	20	25	32	40	50	63		
CDJ2	3	4		4	—	—	—		_	—		
CDVJ3, CDVJ5	-	4	_	4	_	_	—	-	_	_		
CDLJ2	-	-	-	4	—	—	—	-	—	—		
CDM2, CDBM2, CDVM3, CDVM5, CDLM2, CDLG1, REC	Ι	_	_	-	4	4	4.5	5	_	_		
CDG1, MGG	-	-	-	-	4	4	4.5	5	6	6.5		
RSDG	_	_	_	_	—	_	_	5	6	_		
MGG, MGC		-	_	_	4	4	4.5	5	6	-		
RHC, MLGC	_	-	_	_	4	4	4.5	5	_	_		

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)




2 Colour Indication Style Solid State Switch/Band Mounting D-G59W/D-G5PW/D-K59W

Grommet


The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)




Internal Circuit (): If not applicable for IEC Standard




D-G5PW



D-K59W



Indicator light/Operation



Applicable Actuator Series

Series	Bore size (mm)
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CNA	ø40, ø50, ø63, ø80, ø100
MGC	ø20, ø25, ø32, ø40, ø50
RHC, MLGC, REC	ø20, ø25, ø32, ø40
CE2	ø40, ø50, ø63, ø80, ø100

Specifications


PLC: Programmable Logic Controller

(mm)

D-G5□/D-K59 (With indicator light)								
Auto switch model number	D-G59W	D-G5PW	D-K59W					
Wiring	3 w	ire	2 wire					
Output	NPN	PNP	—					
Application	IC circuit/F	Relay/PLC	24V DC Relay/PLC					
Power voltage	5/12/24V DC (4	—						
Current consumption	≤ 10	mA	—					
Load voltage	≤ 28V DC		24V DC (10 to 28V DC)					
Load current	≤ 40mA	80mA or less	5 to 40mA					
Internal voltage drop		0.8V or less	4V or less					
Current leakage	100μA or les	0.8mA or less at 24V DC						
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode							

•Lead wire—Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions



Operation Range (*t* Dimension)

Actuator series		Bore size									
Actuator series	20	25	32	40	50	63	80	100			
CDG1, MGG	4	4	4.5	5	6	6.5	6.5	7			
CDA1, CDBA1, CDV3, CDVS, CDLA, CDL1, CNA	-	_	-	5	6	6.5	6.5	7			
MGC	4	4	4.5	5	6	-	-	—			
RHC, MLGC, REC	4	4	4.5	5	-	-	—	-			
CE2	—	—	—	5	6	6.5	6.5	7			



2 Colour Indication Style Solid State Switch/Rail Mounting D-F79W/D-F7PW/D-J79W

Grommet

The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)



(): If not applicable for IEC Standard

DC(+) Brown(Red)

OUT Black(White)

DC(-)

OUT(+)

OUT(-)

DC(+)

OUT

DC(–) Blue(Black)

Brown(Red)

Black(White)

Blue(Black

Brown(Red)

Blue(Black)

Internal Circuit

nain

witch

D-F79W

D-F7PW

D-J79W

Switch

nain

Switch

circuit

Applicable Actuator Series

Series	Bore size (mm)					
CDJ2, CDVJ3, 5	ø10, ø16					
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160					
CD□XW	Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32					
CDY1S, CY1L	. ø6, ø10, ø15, ø20, ø25, ø32, ø40					
RSDQ	ø20, ø25, ø32, ø40, ø50					
MDU	ø25, ø32, ø40, ø50, ø63					
CE1	ø12, ø20, ø32, ø40, ø50, ø63					
МК, МК2	ø20, ø25, ø32, ø40, ø50, ø63					
СХТ	ø32, ø40					

Specifications


PLC: Programmable Logic Controller

D-F7 W/D-J7	9W						
Auto switch model number	D-F79W	D-J79W					
Wiring	3 w	ire	2 wire				
Output	NPN	PNP	—				
Application	IC circuit/F	24V DC Relay/PLC					
Power voltage	5/12/24V DC	_					
Current consumption	≤ 10	—					
Load voltage	≤ 28V DC		24V DC (10 to 28V DC)				
Load current	≤ 40mA	≤ 80mA	5 to 40mA				
Internal voltage drop	\leq 1.5V (\leq 0.8V at 10mA load current)	≤ 4V					
Current leakage	≤ 100μA a	≤ 0.8mA at 24V DC					
la dia atau limba	Operating point: Red light emitting diode						
Indicator light							

Suitable operating point: Green light emitting diode

●Lead wire ——Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.





Operation Range (*t* Dimension)


		-					-										()
Actuator se	wi e e		Bore size														
Actuator se	nes	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDV	J3, 5	-	5	-	-	5	-	-	-	-	-	-	—	-	—	—	-
CDQ2		-	—	5.5	-	6	5.5	5	6	6	6	6.5	6.5	7	9	9	8.5
CD□XW	В		—			4	3.5	3.5	4								
	P		3		_	2.5	3.5	3.5	2.5					-	_		
CDY1S, CY	1L	3	3	-	4	-	3	3	3	3.5	—	—	—	-	—	—	—
RSDQ		-	-	-	-	-	5.5	-	6	6	6	-	—	-	Ι	—	-
MDU		—	—	—	—	-	—	6.5	7	6.5	6.5	6.5	—	-	—	—	—
CE1		-	-	5.5	-	-	5.5	-	6	6	6	6.5	—	-	-	—	-
MK, MK2		—	—	-	_	-	5.5	5	6	6	6	6.5	—	-	-	-	_
СХТ		_	_	-	—	-	_	_	6	6	_	-	—	-	—	-	_
СХТ		-	-	-	—	-	—	-	6	6	—	-	-	-	-	-	

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)



Technical Data

Indicator light/Operation





2 Colour Indication Style Solid State Switch/Rail Mounting D-F7NWV/D-F7BWV

Grommet Electrical entry: Perpendicular

The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)



Applicable Actuator Series

Series	Bore size (mm)						
CDJ2, CDVJ3, 5	ø10, ø16						
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160						
CD□XW	Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32						
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40						
RSDQ	ø20, ø25, ø32, ø40, ø50						
MDU	ø25, ø32, ø40, ø50, ø63						
CE1	ø12, ø20, ø32, ø40, ø50, ø63						
МК, МК2	ø20, ø25, ø32, ø40, ø50, ø63						
СХТ	ø32, ø40						

Specifications


PLC: Programmable Logic Controller

(mm)

D-F7 WV (With indicator light)								
Auto switch model number	D-F7NWV	D-F7BWV						
Wiring	3 wire	2 wire						
Output	NPN							
Application	IC circuit/Relay/PLC	24V DC Relay/PLC						
Power voltage	5/12/24V DC (4.5 to 28V DC)	—						
Current consumption	≤ 10mA	—						
Load voltage	\leq 28V DC	24V DC (10 to 28V DC)						
Load current	≤ 40mA	5 to 40mA						
Internal voltage drop	≤ 1.5V (≤ 0.8V at 10mA load current)	≤ 4V						
Current leakage	100 μ A or less at 24V DC	0.8mA or less at 24V DC						
la dia atau Kalat	Operating point: Red light emitting diode							
Indicator light	Suitable operating point: Green light emitting diode							

 Oliproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions




Operation Range (*l* Dimension)

Actuator se	vrioe		Bore size														
Actuator se	nes	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDV	J3, 5	_	5	-	-	5	-	_	-	-	-	-	-	-	-	-	-
CDQ2		—	—	5.5	—	6	5.5	5	6	6	6	6.5	6.5	7	9	9	8.5
CD□XW	В		—			4	0.5	3.5	4								
	Ρ		3	_		2.5	2.5 3.5	3.5	2.5	_	_	_	-			_	
CDY1S, CY	/1L	3	3	-	4	—	3	3	3	3.5	-	—	-	—	-	_	-
RSDQ		_	—	_	—	—	5.5	_	6	6	6	—	—	—	_	—	—
MDU		_	-	-	-	—	-	6.5	7	6.5	6.5	6.5	-	—	-	—	_
CE1		_	—	5.5	—	—	5.5	_	6	6	6	6.5	_	—	_	—	_
MK, MK2		_	_	-	_	_	5.5	5	6	6	6	6.5	-	_	_	—	_
СХТ		—	_	—	_	_	_	—	6	6	-	—	-	_	_	_	_
Note) Average value at normal temperature including hystoresis. (Tolerance +30%)																	

Internal Circuit

(): If not applicable for IEC Standard



2 Colour Indication Style Solid State Switch/Tie-rod Mounting D-F59W/D-F5PW/D-J59W


Grommet

The suitable operating point can be indicated with a green light. (Red→Green←Red)




Internal Circuit (): If not applicable for IEC Standard

D-F59W • DC(+) Brown(Red) main OUT Black(White) Switch DC(-) Blue(Black)



Indicator light/Operation



Blue(Black)

Applicable Actuator Series

Series	Bore size (mm)					
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	ø40, ø50, ø63, ø80, ø100					
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160					
CDS1	ø125, ø140, ø160, ø180, ø200					
CE2	ø40, ø50, ø63, ø80, ø100					
MDB	ø32, ø40, ø63, ø80, ø100					


Specifications

Specifications	ns PLC: Programmable Logic Controller									
D-F5 W/D-J59W (With indicator light)										
Auto switch model number	D-F59W	D-J59W								
Wiring	3 w	ire	2 wire							
Output	NPN	PNP								
Application	IC circuit/F	24V DC Relay/PLC								
Power voltage	5/12/24V DC (5/12/24V DC (4.5 to 28V DC)								
Current consumption	10	mA	—							
Load voltage	\leq 28V DC	_	24V DC (10 to 28V DC)							
Load current	≤ 40mA	≤ 80mA	5 to 40mA							
Internal voltage drop	\leq 1.5V (\leq 0.8V at 10mA load current)	$\leq 1.5V$ ($\leq 0.8V$ at 10mA load current) $\leq 0.8V$								
Current leakage	\leq 100µA at 24V DC \leq 0.8mA at 24V DC									
Indiantar light	Operating point: Red light emitting diode									
Indicator light	Suitable operating point: Green light emitting diode									


Lead wire Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length

Dimensions



10.8



Technical Data

Operation Range (*t* **Dimension)**

Actuator series		Bore size											
		40	50	63	80	100	125	140	160	180	200		
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	-	4	4	4.5	4.5	4.5	_	_	_	-	-		
CDL1	-	4	4	4.5	4.5	4.5	5	5	5.5	-	-		
CDS1	-	-	—	-	-	—	5	5	5.5	6	6		
CE2	-	4	4	4.5	4.5	4.5	—	—	-	-	-		
MDB	3.5	4	4	4.5	4.5	4.5	—	—	—	—	—		

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



2 Colour Indication Style Solid State Switch/Direct Mounting D-M5NW/D-M5PW/D-M5BW


Grommet


The suitable operating point can be indicated with a green light. (Red \rightarrow Green \leftarrow Red)




Internal Circuit

(): If not applicable for IEC Standard






D-M5BW



Indicator light/Operation



Applicable Actuator Series


Series	Bore size (mm)
MYC	ø25, ø32, ø40
МҮН	ø25, ø32, ø40
ML1	ø25, ø32, ø40

Specifications

Specifications	pecifications PLC: Programmable Logic Controlle										
D-M5 W (Wit	D-M5⊡W (With indicator light)										
Auto switch model number	D-M5NW	D-M5BW									
Wiring	3 w	rire	2 wire								
Output	NPN	PNP	—								
Application	IC circuit/R	IC circuit/Relay/PLC 24V DC Relay/PLC									
Power voltage	5/12/24V DC (4.5 to 28V DC)										
Current consumption	≤ 10	mA	—								
Load voltage	≤ 28V DC		24V DC (10 to 28V DC)								
Load current	≤ 40mA	≤ 80mA	5 to 40mA								
Internal voltage drop	\leq 1.5V (\leq 0.8V at 10mA load current)	≤ 0.8V	≤ 4V								
Current leakage	\leq 100µA at 24V DC \leq 1mA at 24V DC										
Indiantar light											
Indicator light	Suitable operating point: Green light emitting diode										

Lead wire – ---- Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to the p.5.3-5 for lead wire length.

Dimensions



Operation Range (*t* Dimension) (mm)

	.	Bore size						
Actuator series		25	32	40				
	MYC	4	4	4				
	MYH	4	4	4				
	ML1	4	4	4				


2 Colour Indication Style Solid State Switch/Direct Mounting D-Y7NW(V)/D-Y7PW(V)/D-Y7BW(V)

Grommet


The suitable operating point can be indicated with a green light. (Red→Green←Red)




Internal Circuit (): If not applicable for IEC Standard




D-Y7PW(V)





Indicator light/Operation




Applicable Actuator Series

Series	Bore size (mm)
CXS	ø6, ø10, ø15, ø20, ø25, ø32
MGQ, MVGQ	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
MGP	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
MY1B	ø25, ø32, ø40, ø50, ø63, ø80, ø100
MY1C	ø25, ø32, ø40, ø50, ø63
MY1H	ø25, ø32, ø40
MY1M	ø25, ø32, ø40, ø50, ø63
RSH	ø20, ø32, ø50, ø63, ø80

Specifications PLC: Programmable Logic Controller D-Y7 W/D-Y7 WV (With indicator light) D-Y7NWV D-Y7NW D-Y7PW D-Y7PWV Auto switch model number D-Y7BW D-Y7BWV In-line Perpendicular In-line In-line Electrical entry Perpendicular Perpendicular Wiring 3 wire 2 wire NPN PNP Output Application IC circuit/Relay/PLC 24V DC Relay/PLC Power voltage 5/12/24V DC (4.5 to 28V DC) Current consumption 10mA or less Load voltage 28V DC or less 24V DC (10 to 28V DC) Load current 40mA or less 5 to 40mA 80mA or less ≤1.5V ≤ 4V Internal voltage drop ≤ 0.8V (≤ 0.8V at 10mA load current) Current leakage $100 \mu A$ or less at 24V DC 0.8mA or less at 24V DC Operating point: Red light emitting diode Indicator light Suitable operating point: Green light emitting diode

•Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.15mm², 3 cores (Brown, Black, Blue), 2 cores (Brown, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.



Actuator series	Bore size												
Actuator series	6	10	12	15	16	20	25	32	40	50	63	80	100
MGQ, MVGQ	-	-	5	—	6	6	6.5	8.5	8.5	9	10	10	11.5
CXS	3	3	-	3.5	-	3.5	4	4.5	_	-	_	-	
MGP	-	-	5.5	—	7.5	7.5	7	6.5	6	7	8	9.5	10
MY1B	-	_	-	_	-	—	6	9	10	3.5	3.5	3.5	3.5
MY1C, MY1M	-	—	-	—	-	-	5	5	5	5.5	5.5	-	_
MY1H	-	-	-	-	-	-	6	9	10	-	_	-	-
RSH	-	-	-	—	-	7.5	-	5	—	6.5	7.5	10	_
CY1R	-	_	-	-	-	-	7	6	6	7	6	-	_
CY1H		6	_	5	-	5	5	6	—	-	_		_
ML2B	-	_	-	-	-	-	6	6	6	-	_	-	-
MGF	-	-	-	—	-	-	-	-	9	-	5	-	7.5
Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)								5.3	3-48				

SMC



RB

Technical Data

2 Colour Indication Style with Diagnostic Output Solid State Switch/Band Mounting **D-H7LF** (Latching Style)

Grommet

The output signal can be detected in an unsteady detecting area.



Applicable Actuator Series

Series	Bore size (mm)
CDJ2	ø6, ø10, ø16
CDVJ3, 5	ø10, ø16
CDLJ2	ø16
CDM2, CDBM2, CDVM3, 5, CDLM2, CDLG1, REC	ø20, ø25, ø32, ø40
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63
RSDG	ø40, ø50
MGC	ø20, ø25, ø32, ø40, ø50
RHC, MLGC	ø20, ø25, ø32, ø40


Specifications

PLC: Programmable Logic Controller


D-H7LF (With indicator light)						
Auto switch model number	D-H7LF					
Wiring	4 wire					
Output	NPN					
Diagnostic output	Latching operation					
Application	24V DC Relay/PLC					
Power voltage	24V DC (20 to 26V DC)					
Current consumption	≤ 20mA					
Load voltage	≤ 26V DC					
Load current	≤ 40mA					
Internal voltage drop	≤ 0.8V					
Current leakage	\leq 100 μ A at 24V DC					
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode Orange colour indicator lights on when diagnostic output is ON.					

Internal Circuit

): If not applicable for IEC Standard (




Dimensions



Lead wire --Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length

Diagnostic Output Operation

The diagnostic signal is output when detecting position remains within unsteady area (where indicator light is Red.) for more than 0.5 sec. This signal keeps outputting even after normal output goes to OFF. The diagnostic output becomes OFF when detecting position remains within the most suitable operating range (where indicator light is Green.) for more than 0.5 sec.



Operation Range (*t* **Dimension)**

									(
Bore size											
6	10	15	16	20	25	32	40	50	63		
4	5	-	5	-	-	-	-	-	-		
-	5	-	5	-	-	-	-	-	—		
-	-	-	5	-	-	-	-	-	-		
_	_	-	_	5	5	5.5	6	_	_		
-	-	-	-	5	5	5.5	6	7	7.5		
-	-	-	-	-	-	-	6	7	-		
-	_	_	-	5	5	5.5	6	7	_		
-	-	-	-	4	4	4.5	5	-	-		
	4 - - -	4 5 - 5 	4 5 - - 5 - - - - - - - - - - - - - - - - - - -	$\begin{array}{cccccccccccccccccccccccccccccccccccc$	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	6 10 15 16 20 25 4 5 - 5 - - - 5 - 5 - - - 5 - 5 - - - - 5 5 - - - - 5 5 - - - - - 5 5 5 - - - 5 5 - - - 5 5 - - - 5 5 - - - 5 5	6 10 15 16 20 25 32 4 5 - 5 - - - - 5 - 5 - - - - 5 - 5 - - - - - 5 - - - - - - 5 5 5.5 5.5 - - - 5 5 5.5 - - - - - - - - - - - - - - 5 5 5.5 - - - - - - - - 5 5 5.5	$\begin{array}{c ccccccccccccccccccccccccccccccccccc$	$\begin{array}{cccccccccccccccccccccccccccccccccccc$		

(mm)



2 Colour Indication Style with Diagnostic Output Solid State Switch/Band Mounting D-H7NF


Grommet

The output signal can be detected in an unsteady detecting area.



Internal Circuit

): If not applicable for IEC Standard



Applicable Actuator Series

Series	Bore size (mm)				
CDJ2	ø6, ø10, ø16				
CDVJ3, 5	ø10, ø16				
CDLJ2	ø16				
CDM2, CDBM, CDVM3, 5, CDLM2, CDLG1, REC	ø20, ø25, ø32, ø40				
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63				
RSDG	ø40, ø50				
MGC	ø20, ø25, ø32, ø40, ø50				
RHC, MLGC	ø20, ø25, ø32, ø40				

Specifications


PLC: Programmable Logic Controller

D-H7NF (With indicator light)									
Auto switch model number	D-H7NF								
Wiring	4 wire								
Output	NPN								
Diagnostic output	Normal operation								
Application	IC circuit/Relay/PLC								
Power voltage	5/12/24V DC (4.5 to 28V DC)								
Current consumption	≤ 10mA								
Load voltage	≤ 28V DC								
Load current	≤ 40mA								
Internal voltage drop	≤ 1.5V (≤ 0.8V at 10mA)								
Current leakage	\leq 100 μ A at 24V DC								
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode								


•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on tp.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length

Diagnostic Output Operation

The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, thus diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.



Dimensions



Operation Range (*t* **Dimension)**

	• •					,						
	Bore size											
Actuator series	6	10	15	16	20	25	32	40	50	63		
CDJ2	4	5	-	5	-	-	-	-	-	-		
CDVJ3, 5	-	5	-	5	-	-	-	-	-	-		
CDLJ2	-	-	-	5	-	-	-		-	-		
CDM2, CDBM2, CDVM3,					5	5	5.5	6				
CDVM5, CDLM2, CDLG1, REC				_	5	5	5.5	0	_	_		
CDG1, MGG	-	-	-	-	5	5	5.5	6	7	7.5		
RSDG	-	—	—	—	-	-	—	6	7	-		
MGC	-	-	-	-	5	5	5.5	6	7	-		
RHC, MLGC	-	_	_	-	4	4	4.5	5	_	_		

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

Data

2 Colour Indication Style with Diagnostic Output Solid State Switch/Band Mounting **D-G59F**


Grommet

The output signal can be detected in an unsteady detecting area.



Internal Circuit

(): If not applicable for IEC Standard



Applicable Actuator Series

Series	Bore size (mm)
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA	ø40 [*] , ø50 [*] , ø63, ø80, ø100
MGC	ø20, ø25, ø32, ø40, ø50
RHC, MLGC	ø20, ø25, ø32, ø40
CE2	ø40, ø50, ø63, ø80, ø100

* Can not be used for lube type.

Specifications


PLC: Programmable Logic Controller

D-G59F (With indicator light)								
Auto switch model number	D-G59F							
Wiring	4 wire							
Output	NPN							
Application	IC circuit/Relay/PLC							
Diagnostic output	Normal operation							
Current consumption	≤ 10mA							
Load voltage	≤ 28V DC							
Load current	≤ 40mA							
Internal voltage drop	≤ 1.5V (≤ 0.8V at 10mA)							
Current leakage	\leq 100 μ A at 24V DC							
Indicator light	Operating point: Red light emitting diode							
mulcator light	Suitable operating point: Green light emitting diode							


Oilproof vinyl heavy insulation cable, ø4, 0.2mm², 4 cores (Brown, Black, Orange, Blue), 0.5m Lead wire Note 1) Refer to common specifications on the p.5.3-5. Note 2) Refer to the p.5.3-5 for lead wire length


Diagnostic Output Operation

The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, that is to say, diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.



Dimensions





Operation Range (*l* **Dimension)**

Operation Range (<i>e</i> Dimension) (mm)												
A - t -	Bore size											
Actuator series	20	25	32	40	50	63	80	100				
CDG1, MGG	5	5	5.5	6	7	7.5	7.5	8				
CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA		_	-	6	7	7.5	7.5	8				
MGC		5	5.5	6	7	-	-	-				
RHC, MLGC	5	5	5.5	6	-	-	-	-				
CE2	-	-	-	6	7	7.5	7.5	8				

2 Colour Indication Style with Diagnostic Output Solid State Switch/Rail Mounting **D-F7LF** (Latching Style)

Grommet

The output signal can be detected in an unsteady detecting area.



Applicable Actuator Series

Series	Bore size (mm)						
CDJ2, CDVJ3, 5	ø10, ø16						
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160						
CD□XW	Housing mounted(B), ø16, ø20, ø25, ø32						
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40						
RSDQ	ø20, ø25, ø32, ø40, ø50						
MDU	ø25, ø32, ø40, ø50, ø63						
CE1	ø12, ø20, ø32, ø40, ø50, ø63						
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63						
СХТ	ø32, ø40						


Specifications

PLC: Programmable Logic Controller

D-F7LF (With indicator light)							
Auto switch model number	D-F7LF						
Wiring	4 wire						
Output	NPN						
Diagnostic output	Latching operation						
Application	24V DC Relay/PLC						
Power voltage	24V DC (20 to 26V DC)						
Current consumption	≤ 20mA						
Load voltage	≤ 26V DC						
Load current	≤ 40mA						
Internal voltage drop	≤ 0.8V						
Current leakage	\leq 100 μ A at 24V DC						
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode						

Internal Circuit


): If not applicable for IEC Standard (



- Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 4 cores (Brown,Black, Orange, Blue), 0.5m Lead wire Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length


Diagnostic Output Operation

The diagnostic signal is output when detecting position remains within unsteady area (where indicator light is Red.) for more than 0.5 sec. This signal keeps outputting even after normal output goes to OFF. The diagnostic output becomes OFF when detecting position remains within the most suitable operating range (where indicator light is Green.) for more than 0.5 sec



Orange colour indicator lights on when diagnostic output is ON.

Dimensions



Operation Range (*l* **Dimension)**

			-	•												· /
Actuator								Bore	e siz	е						
series	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDVJ3, CDVJ5	-	6.5	-	-	5.5	—	-	-	Ι	-	-	-	-	-	-	-
CDQ2	-	-	6	—	7	7	7	8	7	8	8.5	8	9	10.5	11	10.5
CD XW B	_	_	_	_	4.5	4.5	5	4.5	_	-	—	_	_	-	_	_
CDY1S, CY1L	4.5	4.5	—	4.5	—	4.5	4.5	4.5	4.5	—	-	-	-	-	-	_
RSDQ	-	_	_	_	_	7	_	8	7	7	-	_	_	-	_	_
MDU	-	-	—	—	—	—	7	7.5	7	7	7	-	-	-	-	_
СХТ	-	-	_	_	_	-	_	6	6	-	-	_	_	-	_	-
CE1	-	-	6	—	—	7	7	8	7	8	8.5	-	-	-	_	-
MK, MK2	-	-	-	-	-	7	7	8	7	8	8.5	—	-	-	-	-

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

Technical Data




2 Colour Indication Style with Diagnostic Output Solid State Switch/Rail Mounting **D-F79F**

Grommet


The output signal can be detected in an unsteady detecting area.



Internal Circuit (): If not applicable for IEC Standard



Dimensions



Applicable Actuator Series

Series	Bore size (mm)						
CDJ2, CDVJ3, 5	ø10, ø16						
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160						
CD□XW	Plate mounted(P), ø10, ø16, ø20, ø25, ø32 Housing mounted, ø16, ø20, ø25, ø32						
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40						
RSDQ	ø20, ø32, ø40, ø50						
MDU	ø25, ø32, ø40, ø50, ø63						
СХТ	ø32, ø40						
CE1	ø12, ø20, ø32, ø40, ø50, ø63						
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63						

Specifications


PLC: Programmable Logic Controller

D-F79F (With indicator light)								
Auto switch model number	D-F79F							
Wiring	4 wire							
Output	NPN							
Diagnostic output	Normal operation							
Application	IC circuit/Relay/PLC							
Power voltage	5/12/24V DC (4.5 to 28V DC)							
Current consumption	≤ 10mA							
Load voltage	≤ 28V DC							
Load current	≤ 40mA							
Internal voltage drop	≤ 1.5V (0.8V at 10mA)							
Current leakage	\leq 100 μ A at 24V DC							
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode							

•Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Diagnostic Output Operation

The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, that is to say, diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.



(mm)

Operation Range (*l* Dimension)

Actuator	r							В	ore	size							
series		6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDVJ3, CD	IVJ5	-	6.5	-	-	5.5	-	-	-	-	-	Ι	-	-	-	-	-
CDQ2		-	-	6	-	7	7	7	8	7	8	8.5	8	9	10.5	11	10.5
CD	В		-			4.5	4.5	5	4.5								
	Ρ	-	4.5	_	-	3.5	4.5	5	3.5	-	_	_	_	_	_	_	-
CDY1S, CY	'1L	4.5	4.5	-	4.5	-	4.5	4.5	4.5	4.5	_	-	-	_	-	—	-
RSDQ		-	-	-	-	-	7	-	8	7	7		-		-	-	-
MDU		-	-	-	-	-	-	7	7.5	7	7	7	-	—	-	—	-
СХТ		-	-	-	-	-	-	-	6	6	-	—	-	-	-	-	-
CE1		—	—	6	-	-	7	-	8	7	8	8.5	-	-	-	-	-
MK, MK	2	—	—	-	-	-	7	7	8	7	8	8.5	-	-	-	-	-
Note) Avera	ana	value	atn	orma	l tomr	orati	iro in	ludir	na hve	teres	is (T	olera	nce +	30%)		




2 Colour Indication Style with Diagnostic Output Solid State Switch/Tie-rod Mounting **D-F59F**

Grommet

The output signal can be detected in an unsteady detecting area.



Internal Circuit



Applicable Actuator Series

Series	Bore size (mm)
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	ø40, ø50, ø63, ø80, ø100
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CDS1	ø125, ø140, ø160, ø180, ø200
CE2	ø40, ø50, ø63, ø80, ø100
MDB	ø32, ø40, ø50, ø63, ø80, ø100

Specifications


PLC: Programmable Logic Controller

D-F59F	
Auto switch model number	D-F59F
Wiring	4 wire
Output	NPN
Diagnostic output	Normal operation
Application	IC circuit/Relay/PLC
Power voltage	5/12/24V DC (4.5 to 28V DC)
Current consumption	≤ 10mA
Load voltage	≤ 28V DC
Load current	≤ 40mA
Internal voltage drop	≤ 1.5V (≤ 0.8V at 10mA)
Current leakage	≤ 100μA at 24V DC
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode


•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.2mm², 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.


Diagnostic Output Operation

The diagnostic output is detected when detecting position remains at unsteady area only, not available at the most suitable operating area, that is to say, diagnostic signal can be output only when the detecting position is far from the suitable position for normal operation.



Dimensions





Operation	Range	(<i>l</i> Dimension)
-----------	-------	-----------------------

Operation Range (<i>l</i> Dimension)											
A strategy as view	Bore size										
Actuator series	32	40	50	63	80	100	125	140	160	180	200
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA		5.5	5	5.5	5.5	5.5	-	_	—	_	_
CDL1	-	5.5	5	5.5	5.5	5.5	5.5	6	6.5	—	—
CDS1	-	-	-	-	-	-	5.5	6	6.5	7	7
CE2	Ι	5.5	5	5.5	5.5	5.5	—	—	—	—	—
MDB	5	5.5	5.5	6	6	6	-	—	_	—	-
Note) Average value at norma	l temp	erature	includi	na hvs	teresis.	(Tolera	ance ±3	30%)			



RB
J
D
-X
20-

Technical Data

Water Resistant 2 Colour Inudication Style Solid State Switch/Band Mounting **D-H7BAL**

Grommet

Water (coolant) resistant performance



▲ Caution

Precautions

Consult SMC if using coolant liquid other than water based solution.

Applicable Actuator Series

Series	Bore size (mm)
CDJ2	ø6, ø10, ø16
CDVJ3, 5	ø10, ø16
CDLJ2	ø16
CDM2, CDBM2, CDVM3, 5, CDLM2, CDLG1, REC	ø20, ø25, ø32, ø40
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63
RSDG	ø40, ø50
MGC	ø20, ø25, ø32, ø40, ø50
MLGC	ø20, ø25, ø32, ø40

Specifications

PLC: Programmable Logic Controller

(mm)


D-H7BAL (With indicator light)

Auto switch model number	D-H7BAL
Wiring	2 wire
Output	_
Application	24V DC Relay/PLC
Power voltage	_
Current consumption	_
Load voltage	24V DC (10 to 28V DC)
Load current	≤ 5 to 40mA
Internal voltage drop	≤ 4V
Current leakage	≤ 0.8mA at 24V DC
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode

Internal Circuit


5.3-55

(): If not applicable for IEC Standard



•Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions



Operation Range (*t* **Dimension)**

Actuator series		Bore size									
		10	15	16	20	25	32	40	50	63	
CDJ2	4	5	-	5	—	-	-	—	—	-	
CDVJ3, 5	-	5	_	5	_	-	-	-	_	-	
CDLJ2	-	—	-	5	—	—	-	—	—	-	
CDM2, CDBM2, CDVM3, 5 CDLM2, CDLG1, REC	_	_	Ι	_	5	5	5.5	6	_	-	
CDG1, MGG	-	-	-	-	5	5	5.5	6	7	7.5	
RSDG	-	—	-	—	-	-	-	6	7	-	
MGC	-	—		—	5	5	5.5	6	7	-	
RHC, MLGC	-	-	-	_	5	5	5.5	6	-	-	

Water Resistant 2 Colour Indication Style Solid State Switch/Band Mounting D-G5BAL

Grommet

Water (coolant) resistant performance



▲ Caution **Precautions**

Consult SMC if using coolant liquid other than water based solution.

Applicable Actuator Series

Series	Bore size (mm)
CDG1, MGG	ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA	ø40 [*] , ø50 [*] , ø63, ø80, ø100
MGC	ø20, ø25, ø32, ø40, ø50
RHC, MLGC, REC	ø20, ø25, ø32, ø40
CE2	ø40, ø50, ø63, ø80, ø100

* Can not be used for lube type

Specifications

PLC: Programmable Logic Controller

D-G5BAL (With indicator light)							
Auto switch model number	D-G5BAL						
Wiring	2 wire						
Output	_						
Application	24V DC Relay/PLC						
Power voltage	_						
Current consumption	-						
Load voltage	24V DC (10 to 28V DC)						
Load current	≤ 5 to 40mA						
Internal voltage drop	≤ 4V						
Current leakage	\leq 0.8mA at 24V DC						
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode						


Internal Circuit (): If not applicable for IEC Standard

OUT(+) Brown(Red) main Switch Lo L OUT(-) Blue(Black) **Indicator light/Operation** ON Operation range OFF Indication Red Green Red Suitable operating point

- Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 3m (Standard) Lead wire Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length

Dimensions



Operation Range (*l* **Dimension)**

Operation Range (<i>e</i> Dimension) (mm)										
Actuator series		Bore size								
		25	32	40	50	63	80	100		
CDG1, MGG	5	5	5.5	6	7	7.5	7.5	8		
CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA	_	-	-	6	7	7.5	7.5	8		
MGC	5	5	5.5	6	7	—	—	—		
RHC, MLGC, REC	5	5	5.5	6	-	—	—	—		
CE2	—	-	-	6	7	7.5	7.5	8		

Note) Average value at normal temperature including hysteresis.(Tolerance ±30%)

Technical Data

SMC

Water Resistant 2 Colour Indication Style Solid State Switch/Rail Mounting **D-F7BAL**

Grommet

Water (coolant) resistant performance



▲ Caution

Precautions

Consult SMC if using coolant liquid other than water based solution.


Applicable Actuator Series

Bore size (mm)
ø10, ø16
ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Husuing mounted(B), ø16, ø20, ø25, ø32
ø6, ø10, ø15, ø20, ø25, ø32, ø40
ø20, ø25, ø32, ø40, ø50
ø25, ø32, ø40, ø50, ø63
ø12, ø20, ø32, ø40, ø50, ø63
ø20, ø25, ø32, ø40, ø50, ø63
ø32, ø40


Specifications	PLC: Programmable Logic Controller
D-F7BAL (With indica	tor light)
Auto switch model number	D-F7BAL
Wiring	2 wire
Output	_
Application	24V DC Relay/PLC
Power voltage	_
Current consumption	-
Load voltage	24V DC (10 to 28V DC)
Load current	≤ 5 to 40mA
Internal voltage drop	≤ 4V
Current leakage	\leq 0.8mA at 24V DC
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode

●Lead wire —— Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Internal Circuit (): If not applicable for IEC Standard



Dimensions



Actuator se	rico		Bore size														
Actuator se	lies	6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
CDJ2, CDV	J3, 5	_	5	—	_	5	-	—	-	-	-	-	—	—	_	—	—
CDQ2		_	-	5.5	-	6	5.5	5	6	6	6	6.5	6.5	7	9	9	8.5
	В		-			4	0.5	3.5	4								
CD□XW	Ρ	_	3		_	2.5	3.5	3.5	2.5		_		_		_		_
CDY1S, CY	/1L	3	3	-	4	-	3	3	3	3.5	—	-	—	-	-	-	-
RSDQ		_	-	-	_	—	5.5	-	6	6	6	-	—	-	_	-	—
MDU		-	-	-	-	-	-	6.5	7	6.5	6.5	6.5	-	-	-	-	-
CE1		—	-	5.5	—	—	5.5	—	6	6	6	6.5	-	-	_	—	-
MK, MK2		—	—	—	-	—	5.5	5	6	6	6	6.5	—	—	_	—	—
СХТ		-	-	_	_	_	-	_	6	6	-	-	-	-	—	—	_
Note) Average v					in ali	ا به ماله،		ania (Talara		00/)						



Water Resistant 2 Colour Indication Style Solid State Switch/Tie-rod Mounting D-F5BAL

Grommet

Water (coolant) resistant performance




Precautions

Consult SMC if using coolant liquid other than water based solution.

Internal Circuit

(): If not applicable for IEC Standard



Applicable Actuator Series

Applicable Actuator 5	enes						
Series		Bore size (mm)					
CDA1, CDBA1, CDV3, CDV CDLA, CNA	′S1,	ø40, ø50, ø63, ø80, ø100					
CDL1		ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160					
CDS1		ø125, ø140, ø160, ø180, ø200					
CE2		ø40, ø50, ø63, ø80, ø100					
MDB		ø32, ø40, ø63, ø80, ø100					
Specifications		PLC: Programmable Logic Controlle					
D-F5BAL (With indica	tor light	1					
Auto switch model number		D-F5BAL					
Wiring		2 wire					
Output		-					
Application		24V DC Relay/PLC					
Power voltage		_					
Current consumption		_					
Load voltage		24V DC (10 to 28V DC)					
Load current		≤ 5 to 40mA					
Internal voltage drop	≤ 4V						
Current leakage	≤ 0.8mA at 24V DC						
Indicator light	Oper	rating point: Red light emitting diode					


Suitable operating point: Green light emitting diode - Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 2 cores (Brown, Blue), 3m (Standard) Lead wire


Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions

Indicator light





RB
J
D
-X
20-

Technical Data

Operation Range (*t* **Dimension)**

Actuator series		Bore size												
Actuator series	32	40	50	63	80	100	125	140	160	180	200			
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	-	4	4	4.5	4.5	4.5	_	_	_	I	_			
CDL1	-	4	4	4.5	4.5	4.5	5	5	5.5	-	—			
CDS1	-	-	_	—	—	-	5	5	5.5	6	6			
CE2	_	4	4	4.5	4.5	4.5	-	_	_	_	_			
MDB	3.5	4	4	4.5	4.5	4.5	—	-	—	-	—			

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)




Solid State Switch with Timer/Band Mounting D-G5NTL

Grommet

With built-in OFF-delay timer (200ms)



Internal Circuit (): If not applicable for IEC Standard




Applicable Actuator Series

Series		Bore size (mm)					
CDM2, CDBM2, CDVM3, 5, CDL	M2, CDLG1	ø20, ø25, ø32, ø40					
CDG1, MGG		ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100					
CDA1, CDBA1, CDV3, CDVS1, CDLA	, CDL1, CNA	ø40, ø50, ø63, ø80, ø100					
MGC		ø20, ø25, ø32, ø40, ø50					
RHC, MLGC, REC		ø20, ø25, ø32, ø40					
CE2		ø40, ø50, ø63, ø80, ø100					
Specifications		PLC: Programmable Logic Controller					
D-G5NTL (With indicator	light)						
Auto switch model number		D-G5NTL					
Wiring		3 wire					
Output		NPN					
Output operation		Off-delay					
Operation time		≤ 1ms					
Off-delay time		200±50ms					
Application		IC circuit/Relay/PLC					
Power voltage		5/12/24V DC (4.5 to 28V DC)					
Current consumption		≤ 10mA					
Load voltage		≤ 28V DC					
Load current	≤ 80mA						
Internal voltage drop	≤ 2V (≤ 0.8V at 10mA)						
Current leakage		\leq 100µA at 24V DC					
Indicator light		ON: When red light emitting diode					
	ation apple at (3mm ² 3 coros (Brown Black Blue) 3m (Standard)					


Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 3 cores (Brown, Black, Blue), 3m (Standard) Lead wire Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length.

Timer Operation



Dimensions



(mm)

Actuator series				Bore	size			
Actuator series	20	25	32	40	50	63	80	100
CDM2, CDBM2, CDVM3, 5, CDLM2, CDLG1	4	4	4.5	5	_	-	_	—
CDG1, MGG	4	4	4.5	5	6	6.5	6.5	7
CDA1, CDBA1, CDV3, CDVS1, CDLA, CDL1, CNA	-	-	-	5	6	6.5	6.5	7
MGC	4	4	4.5	5	6	-	—	_
RHC, MLGC, REC	4	4	4.5	5	-	-	-	-
CE2	-	-	-	5	6	6.5	6.5	7


Solid State Switch with Timer/Rail Mounting **D-F7NTL**

Grommet

With built-in OFF-delay timer (200ms)



Internal Circuit



Applicable Actuator Series

Series								
001100	Bore size (mm)							
CDJ2, CDVJ3, 5	ø10, ø16							
CDQ2	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160							
CD□XW	Plate mounted(P), ø10, ø16, ø20, ø25, ø32, Housing mounted(B), ø16, ø20, ø25, ø32							
CDY1S, CY1L	ø6, ø10, ø15, ø20, ø25, ø32, ø40							
RSDQ	ø20, ø25, ø32, ø40, ø50							
MDU	ø25, ø32, ø40, ø50, ø63							
CE1	ø12, ø20, ø32, ø40, ø50, ø63							
MK, MK2	ø20, ø25, ø32, ø40, ø50, ø63							
СХТ	ø32, ø40							

Specifications

PLC: Programmable Logic Controller

ON

ON(200ms)

OFF

Switch operating range(mm)

-/Cylinder speed(mm/s)


D-F7NTL (With indicator	light)
Auto switch model number	D-F7NTL
Wiring	3 wire
Output	NPN
Output operation	Off-delay
Operation time	≤ 1ms
Off-delay time	200±50ms
Application	IC circuit/Relay/PLC
Power voltage	5/12/24V DC (4.5 to 28V DC)
Current consumption	≤ 10mA
Load voltage	≤ 28V DC
Load current	≤ 80mA
Internal voltage drop	≤ 1.5V (≤0.8V at 10mA)
Current leakage	\leq 100 μ A at 24V DC
Indicator light	ON: When red light emitting diode

●Lead wire —— Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 3m (Standard) Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Timer Operation

Dimensions

Detection of immediate positioning for high-speed cylinder Detecting point dispersion occurs due to response time of PLC (sequencer); e. g. scanning. Ex.) Cylinder speed-1000 mm/sec. Sequencer response time-0.1 sec. Detecting point despersion-Within




Switch detecting




Technical Data

(mm)



100mm (=1000mm/sec. X 0.1sec.)

Take PLC response time into consideration when using.



Operation Range (*t* Dimension)

	Actuator series						_		_	Bore	size							
	Actuator series		6	10	12	15	16	20	25	32	40	50	63	80	100	125	140	160
	CDJ2, CDVJ3,	5	-	5	Ι	—	5		_		—	—	_	_	-	_	—	-
-	CDQ2		-	—	5.5	—	6	5.5	5	6	6	6	6.5	6.5	7	9	9	8.5
		3					4	0 E	3.5	4	_			_				
)	_	3			2.5	3.5	3.5	2.5		_				_		_
	CDY1S, CY1L		3	3	Ι	4	—	3	3	3	3.5	_	—	-	-	-	—	-
	RSDQ		-	—	-	—	—	5.5	—	6	6	6	—	_	-	_	—	—
	MDU		-	-	Ι	—	—	Ι	6.5	7	6.5	6.5	6.5		-		—	-
	CE1		-	_	5.5	—	_	5.5	—	6	6	6	6.5	_	_	_	_	_
	MK, MK2		-	_	Ι	—	-	5.5	5	6	6	6	6.5		-		_	-
	СХТ		—	_	-	_	_	_	_	6	6	—	_	_	_	_	_	_



Solid State Switch with Timer/Tie-rod Mounting D-F5NTL


Grommet

With built-in OFF-delay timer (200ms)



Internal Circuit

(): If not applicable for IEC Standard



Applicable Actuator Series


Series	Bore size (mm)							
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	ø40, ø50, ø63, ø80, ø100							
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160							
CDS1	ø125, ø140, ø160, ø180, ø200							
CE2	ø40, ø50, ø63, ø80, ø100							
MDB	ø32, ø40, ø63, ø80, ø100							
Specifications	PLC: Programmable Logic Controller							
D-F5NTL (With indicator lig	ght)							
Auto switch model number	D-F5NTL							
Wiring	3 wire							
Output	NPN							
Output operation	Off-delay							
Operation time	≤ 1ms							
Off-delay time	200±50ms							
Application	IC circuit/Relay/PLC							
Power voltage	5/12/24V DC (4.5 to 28V DC)							
Current consumption	≤ 10mA							
Load voltage	≤ 28V DC							
Load current	≤ 80mA							
Internal voltage drop	≤ 1.5V (≤ 0.8V at 10mA)							
Current leakage	≤ 100μA at 24V DC							
Indicator light	ON: When red light emitting diode							

---- Oilproof vinyl heavy insulation cable, ø4, 0.3mm², 3 cores (Brown, Black, Blue), 3m (Standard) Lead wire -Note 1) Refer to common specifications on p.5.3-5.


Note 2) Refer to p.5.3-5 for lead wire length.

Timer Operation

Detection of immediate positioning for high-speed cylinder Detecting point dispersion occurs due to response time of PLC (sequencer); e. g. scanning. Ex.) Cylinder speed-1000 mm/sec. Sequencer response time-0.1 sec. Detecting point despersion-Within 100mm (=1000mm/sec. X 0.1sec.) Take PLC response time into consideration when using.



Dimensions



(mm) Bore size Actuator series 32 40 50 63 80 100 125 140 160 180 200 CDA1, CDBA1, CDV3, CDVS1, _ 4 4 4.5 4.5 4.5 _ CDLA, CNA CDL1 4 4 4.5 4.5 4.5 5 5 5.5 CDS1 _ _ 5 5 5.5 6 6 4 4 4.5 4.5 4.5 CE2 MDB 3.5 4 4 4.5 4.5 4.5 MDB | 3.5 | 4 | 4 | 4.5 | 4.5 | 4 Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

Solid State Switch with Timer/Direct Mounting D-M5NTL/D-M5PTL

Grommet

With built-in OFF-delay timer (200ms)



Applicable Actuator Series

D MEDTI (With indicator light

Series	Bore size (mm)
MYC	ø25, ø32, ø40
МҮН	ø25, ø32, ø40
ML1	ø25, ø32, ø40

Specifications

PLC: Programmable Logic Controller

D-M5LIL (With Indicator light)						
Auto switch model number	D-M5NTL D-M5PTL					
Wiring	3 wire					
Output	NPN PNP					
Output operation	Off-	delay				
Operation time	≤ 1	Ims				
Off-delay time	200 <u>+</u>	50ms				
Application	IC circuit/Relay/PLC					
Power voltage	5/12/24V DC (4.5 to 28V DC)					
Current consumption	≤ 10mA	≤ 12mA				
Load voltage	≤ 28V DC –					
Load current	≤ 80)mA				
Internal voltage drop	\leq 2V (\leq 0.8V at 10mA load current)	≤ 0.8V				
Current leakage	100μA or le	ss at 24V DC				
Indicator light	ON: When red light emitting diode					
Oilproof vinul boout	inculation apple a2.4.0.0mm ² .2.corec.(Prown Block Blue) 2m (Standard)				


Oilproof vinyl heavy insulation cable, ø3.4, 0.2mm², 3 cores (Brown, Black, Blue), 3m (Standard) Lead wire

Note 1) Refer to common specifications on the p.5.3-5. Note 2) Refer to the p.5.3-5 for lead wire length

Timer Operation

mair Switch circuit

.



Operation Range (*l* **Dimension)**

DC(+) Brown(Red)

DOUT Black(White)

DC(-) Blue(Black)

Operation Range (2 Dimension)					
Actuator series	Bore size				
Actualor series	25	32	40		
MYC	4	4	4		
MYH	4	4	4		
ML1	4	4	4		

36

ø3 mounting hole

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)



3000

4.6

Water Resistant 2 Colour Indication Style Solid State Switch/Direct Mounting **D-Y7BAL**

Grommet

Improved coolant-resistant performance




▲ Caution

Precautions

Consult SMC if using coolant liquid other than water based solution.

Internal Circuit

(): If not applicable for IEC Standard



Applicable Actuator Series


Series	Bore size (mm)
CXS	ø6, ø10, ø15, ø20, ø25, ø32
MGQ, MVGQ	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
MGP	ø12, ø16, ø20, ø25, ø32, ø40, ø50, ø63, ø80, ø100
RSH	ø20, ø32, ø50, ø63, ø80

Specifications	PLC: Programmable Logic Controller
D-Y7BAL (With indicator light)	
Auto switch model number	D-Y7BAL
Wiring	2 wire
Application	24V DC Relay/PLC
Load voltage	24V DC (10 to 28V DC)
Load current	\leq 5 to 40mA
Internal voltage drop	≤ 4V
Current leakage	\leq 0.8mA at 24V DC
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode

•Lead wire — Oilproof vinyl heavy insulation cable, ø3.4, 0.15mm², 2 cores (Brown, Blue), 3m (Standard) Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions



9

5

7.5

Note) Average value at normal temperature including hysteresis. (Tolerance $\pm 30\%$)

MGF

Strong Magnetic Field Resistant 2 Colours Indication Style Solid State Switch/Rail Mounting D-P5DWL

Grommet

Possible to use in an environment where disturbance magnetic field is generated.



▲ Caution

Precautions

Monophase current welding. Not applicable for DC inverter welding, arc welding nor capacitor welding.

Applicable Actuator Series

Series	Bore size(mm)
CDQ2	ø40, ø50, ø63, ø80, ø100
CDA1	ø40, ø50, ø63, ø80, ø100
MK, MK2, MDU	ø40, ø50, ø63

Specifications

Specifications PLC: Programmable Logic C			
D-P5DW (With indicator light)			
Auto switch model number	D-P5DWL		
Wiring	2 wire (Non-polar)		
Application	24V DC Relay/PLC		
Load voltage	24V DC (20 to 28V DC)		
Load current	6 to 40mA		
Internal voltage drop	≤ 5V		
Current leakage	≤ 1mA at 24V DC		
Operation time	≤ 40ms		
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode		


- Oilproof vinyl heavy insulation cable, ø6, 0.5mm², 2 cores (Brown, Blue), 3m Lead wire Note 1) Refer to common specifications on p.5.3-5.


Note 2) Refer to p.5.3-5 for lead wire length

Strong Magnetic Field Resistance

It is possible to use switches next to welding conductor (gun cable) in case that A. C. welding current is ≤ 16,000A. Consult SMC if exceeding 16,000A.







Operation Range(*t* **Dimension)**

SMC

• • • •	Bore size				
Actuator series	40	50	63	80	100
CDQ2	5	5	5	5	5.5
CDA1	4	4	4.5	4	4.5
MDL	5	5	5	—	_
MK, MK2	5	5	5	—	_



2 Colour Indication Style with Diagnostic Output Solid State Switch/Tie-rod Mounting **D-F5LF (Latching Style)**

Grommet

The output signal can be detected in an unsteady detecting area.




Applicable Actuator Series

Series	Bore size(mm)
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA	ø40, ø50, ø63, ø80, ø100
CDL1	ø40, ø50, ø63, ø80, ø100, ø125, ø140, ø160
CDS1	ø125, ø140, ø160, ø180, ø200
CE2	ø40, ø50, ø63, ø80, ø100
MDB	ø32, ø40, ø63, ø80, ø100
Specifications D-F5LF (With indicator light)	PLC: Programmable Logic Controlle
Auto switch model number	D-F5LF
Wiring	4 wire
Output	NPN
Diagnostic output	Latching operation
Application	24V DC Relay/PLC
Power voltage	24V DC (10 to 26V DC)
Current consumption	20mA
Load voltage	≤ 26V DC
Load current	≤ 40mA
Internal voltage drop	≤ 0.8V
Current leakage	≤ 100μA at 24V DC
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode Orange colour indicator lights on when diagnostic output is Of

•Lead wire — Oilproof vinyl heavy insulation cable, ø4, 0.2mm², 4 cores (Brown, Black, Orange, Blue), 0.5m Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length.

Diagnostic Output Operation (Latching Style)


The diagnostic signal is output when detecting position remains within unsteady area (where indicator light is Red.) for more than 0.5 sec. This signal keeps outputting even after normal output goes to OFF. The diagnostic output becomes OFF when detecting position remains within the most suitable operating range (where indicator light is Green.) for more than 0.5 sec.




(mm)

Internal Circuit

(): If not applicable for IEC Standard



Dimensions



Operation Range (*t* **Dimension)**

Actuator series	Bore size										
Actuator series	32	40	50	63	80	100	125	140	160	180	200
CDA1, CDBA1, CDV3, CDVS1, CDLA, CNA		5.5	5	5.5	5.5	5.5	_	-	-	-	-
CDL1	-	5.5	5	5.5	5.5	5.5	5.5	6	6.5	-	-
CDS1	-	—	-	-	-	-	5.5	6	6.5	7	7
CE2	—	5.5	5	5.5	5.5	5.5	—	-	-	_	-
MDB	5	5.5	5.5	6	6	6	-	_	_	_	_



2 Colour Indication Style Solid State Switch/Direct Mounting D-F9NW(V)/D-F9PW(V)/D-F9BW(V)

Grommet



Applicable Actuator Series

Series	Bore size (mm)
CDU	ø6, ø10, ø16, ø20, ø25, ø32
CDQ2*	ø32, ø40, ø50, ø63, ø80, ø100
CDQS	ø12, ø16, ø20, ø25
MY1	ø16, ø20
MXW	ø8, ø12, ø16, ø20, ø25
MXF	ø8, ø12, ø16, ø20
MXU	ø6, ø10, ø16

Series	Bore size (mm)		
MXS/MXQ	ø6, ø8, ø12, ø16, ø20, ø25		
MXP	ø10, ø12, ø16		
MTS	ø20, ø25, ø32, ø40		
МК	ø12, ø16		
MK2	ø32, ø40, ø50, ø63		
* Not available for series CDOP2			

Not available for series CDQP2


Specifications

PLC: Programmable Logic Controller

D-F9□W/D-F9□WV (With indicator light)										
Auto switch model number	D-F9NW	D-F9NWV	D-F9PW	D-F9PWV	D-F9BW	D-F9BWV				
Electrical entry	In-line	Perpendicular	In-line	Perpendicular	In-line	Perpendicular				
Wiring		3 w	/ire		2	wire				
Output	N	NPN PNP -								
Application	IC circuit/Relay IC/PLC 24V DC Relay/PLC									
Power voltage	5/12/24V DC (4.5 to 28V DC) -									
Current consumption		10	mA			_				
Load voltage	28V	DC	-	_	24V DC (10 to 28V DC)					
Load current	≤ 4()mA	≤ 80	OmA	5 to	40mA				
Internal voltage drop	$\leq 1.5V$ ($\leq 0.8V$ at 10mA or load current) 0.8V or less 4V or less									
Current leakage	\leq 100µA at 24V DC 0.8mA or less									
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode									


Internal Circuit

(): If not applicable for IEC Standard



- Oilproof vinyl heavy insulation cable, ø2.7, 3 cores (Brown, Black, Blue), 0.15mm², 2 cores (Brown, Blue), 0.18mm², 0.5m •Lead wire Note 1) Refer to common specifications on p.5.3-5. Note 2) Refer to p.5.3-5 for lead wire length

Dimensions



Operation Range (*l* **Dimension)**

	-					-									()
Actuator series			_	_	_	_	Bore	size	_						
Actuator series	6	8	10	12	15	16	20	25	32	40	50	63	80	100	125
CDU(Without shield plate)	3	-	3.5	-	-	5.5	6.5	7	7	-	-	-	-	-	-
CDQ2	-	-	-	-	-	-	-	-	5.5	5.5	5.5	6.5	5.5	6.5	-
MY1B, MY1H	-	-	-	-	_	4	5	_	-	-	-	-	-	-	_
MY1C, MY1M	-	-	-	-	-	8.5	6.5	-	-	-	-	-	_	-	-
MXW	-	2.5	-	3	-	4	6	6	-	-	-	-	-	-	-
MXF	-	2	-	2.5	—	3	4	—	-	—	-	-	_	-	—
MXU	3	-	3.5	-	-	5.5	-	-	-	-	-	-	Ι	-	-
MXS, MXQ	2	2.5	-	3	—	4	6	6	-	—	-	-	-	-	—
CDQS	-	-	-	3	-	4	5	5.5	-	-	-	-	Ι	-	-
МК	-	-	-	3	—	4	-	—	-	—	-	-	-	-	—
MK2	-	-	-	-	-	-	-	-	5.5	5.5	5.5	6.5	Ι	-	_
МХР	-	-	3	3	-	3	_	_	-	_	_	-	_	-	_
MTS	-	-	-	-	_	-	5	5.5	5.5	5.5	-	-	-	-	-

Note) Average value at normal temperature including hysteresis. (Tolerance ±30%)

SMC

Technical Data

5.3-66

Water Resistant 2 Colour Indication Style Solid State Switch/Direct Mounting **D-F9BAL**

Grommet

Water (coolant) resistant performance




▲ Caution

Precautions

Consult SMC if using coolant liquid other than water based solution.

Internal Circuit

(): If not applicable for IEC Standard



Applicable Actuator Series

Series	Bore size (mm)
CDU	ø6, ø10, ø16, ø20, ø25, ø32
CDQ2 [*]	ø32, ø40, ø50, ø63, ø80, ø100
CDQS	ø12, ø16, ø20, ø25
МК	ø12, ø16
МК2	ø32, ø40, ø50, ø63

*Not available for series CDQP2

Specifications

PLC: Programmable Logic Controller


(mm)

D-F9BAL (With indicator light)										
Auto switch model number	D-F9BAL									
Wiring	2 wire									
Output	-									
Application	24V DC Relay/PLC									
Power voltage	-									
Current consumption	-									
Load voltage	24V DC (20 to 28V DC)									
Load current	5 to 30mA									
Internal voltage drop	≤ 5V									
Current leakage	≤ 1mA at 24V DC									
Indicator light	Operating point: Red light emitting diode Suitable operating point: Green light emitting diode									

•Lead wire —— Oilproof vinyl heavy insulation cable, ø2.7, 2 cores (Brown, Blue), 0.18mm², 0.5m Note 1) Refer to common specifications on p.5.3-5.

Note 2) Refer to p.5.3-5 for lead wire length.

Dimensions




Operation Range (*l* **Dimension)**

Actuator series	Bore size													
Actuator series	6	8	10	12	15	16	20	25	32	40	50	63	80	100
CDU(Without shield plate)	3	—	3.5	-	—	5.5	6.5	7	7	_	-	—	_	-
CDQ2	-	-	-	-	-	-	-	-	5.5	5.5	5.5	6.5	5.5	6.5
CDQS	_	—	-	3	-	4	5	5.5	—	—	-	-	_	-
МК	—	—	—	3	—	4	—	-	-	—	-	—	—	-
MK2	_	_	-	-	_	-	_	_	5.5	5.5	5.5	6.5	_	_

Information **1** Plug-in Connector Assembly/How to Use DIN Terminal

Plug-in Connector Assembly

D-A73C, D-A80C, D-J79C D-C73C, D-C80C, D-H7C



With the convex port of the connector, insert the connector into the auto switch into the sleeve. Screw the locking ring onto the switch. (Do not tighten with pliers.)

How to Use DIN Terminal/D-A44/A44A/A44C

Connection

①Loosen the set screw and pull out the connector from the pin plug. ②Be sure to remove the set screw first and then insert a screw driver into a recessed groove under the terminal block to separate the terminal cover from the terminal block.


 $\ensuremath{(3)}\xspace{\ens$

④In standard cases, crimp-style terminals are used to connect wires. Please select proper crimp-style terminals so that the wire can be properly connected to terminal fittings.

Method of connection



AC: Connect to terminal No.1 and No.2 DC: Connect (+) to No.1 terminal and (–) to No.2 terminal.



After separating the terminal block from the terminal cover, change the position of the terminal cover to any desired direction (4 directions at every 90°) to change the position of electrical entry. **Caution**

When taking in or out the connector pin to or from the pin plug, hold the connector as perpendicular as possible.

Applicable cable (heavy insulation cable) Applicable to cable O. D. of Ø6.8 to Ø11.5. Applicable crimp-style terminal 1.25Y-3L, 1.25-3.5S, 1.25-4M




Technical Data

Mounting Bracket Band mounting

▲ Caution

 Tighten the screw under the specified torque when mounting auto switch.






Correct mounting Wrong mounting <Applicable auto switch> Reed switch D-B53, D-B54, D-B64 D-B59W Solid state switch D-G59, D-G5P, D-K59, D-G5BAL D-G59W, D-G5PW, D-K59W

D-G59F

D-G5NTL

How to mount and move the auto switch



①Put a mounting band on the cylinder tube and set it at the auto switch mounting position.

②Put the mounting section of the auto switch between the band mounting holes, then adjust the position of mounting holes of switch to those of mounting band.
③Lightly thread the auto switch mounting screw through the mounting hole into the thread part of band fitting.

④After setting the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (The tightening torque of M4 screw should be about 1 to 1.2Nm.)

SModification of the detection position should be made in the condition of ③.
Part No. of auto switch mounting bracket (including band and screw)


	-		•	-							
Bore size (mm)											
20	25	32	40	50	63	80	100				
BA2	BA2	BA2	BA2								
-020	-025	-032	-040								
D A				BA	BA-06	BA-08	BA-10				
				-05	_	_	-				
-01	-02	-32	BA	_	-	_	_				
_	_		-04	BA	BA	BA	BA				
	_			-05	-06	-08	-10				
BA- 01	BA- 02	BA- 32		-	_	_	-				
	BA2 -020 BA -01 — BA-	20 25 BA2 BA2 -020 -025 BA BA -01 -02 - - BA- BA-	E 20 25 32 BA2 BA2 BA2 -020 -025 -032 BA BA BA -01 -02 -32 BA- BA- BA-	Bore siz 20 25 32 40 BA2 BA2 BA2 BA2 -020 -025 -032 -040 BA BA BA -040 -01 -02 -32 BA 04 -04	20 25 32 40 50 BA2 BA2 BA2 BA2 - - -020 -025 -032 -040 - - BA BA BA - - - - -01 -02 -32 - BA - - - - - - - - - - - -	Bore size (mm) 20 25 32 40 50 63 BA2 BA2 BA2 BA2 BA2 Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3" BA2 Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3">Colspan="3" BA3 BA4 BA5 Colspan="3">Colspan="3">Colspan="3">Colspan="3" Colspan="3">Colspan="3" BA4 BA5 Colspan="3">Colspan="3" Colspan="3">Colspan="3" Colspan="3" Colspan="3" <thcolspan="3"< th=""> Colspan="3" Colspa=</thcolspan="3"<>	Bore size (mm) 20 25 32 40 50 63 80 BA2 BA2 BA2 BA2 BA2 BA2 -020 -025 -032 -040 EA BA BA BA <				


Mounting screw set (Stainless steel specification)

Use the following mounting screw set (Set screw included.) according to the required operating conditions. (Mounting band is not included.)

BBA3: For D-B5/B6/G5/K5

D-G5BAL is mounted on the cylinder with the above stainless steel screw BBA3 before shipment or BBA3 is enclosed with D-G5BAL when shipped without cylinder.





①For series CDJ2/Put a mounting bracket on the cylinder tube. For series CDM2/Put a mounting band on the cylinder tube and set it at the auto switch mounting position.

②Put the mounting part of auto switch in the interval of stationary fitting to fit the mounting hole to the hole of stationary fitting.

③Screw lightly the auto switch mounting screw through the mounting hole into the thread part of band fitting.

(4)After setting the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (The tightening torque of M3 screw should be about 0.8 to 1Nm.)

 $\textcircled{5}\mbox{Modification}$ of the detection position should be made in the condition of 3.

Part No. of auto switch mounting bracket (including band and screw)

Cylinder		Bore size (mm)								
series	6	10	15	16	20	25	32	40	50	63
CDJ2	BJ2-006	BJ2	—		-	—	—	—	-	-
CDVJ3, 5	-	-010	-	BJ2 -016	-	-	—	—	-	-
CDLJ2	-	_	—	-010	_	—	—	—	—	-
CDM2, CDBM2	_	_	_		BM2	BM2	BM2	BM2		_
CDVM3, 5, CDLM2					-020	-025	-032	-040		
CDG1, MGG	_	_	_	-					BMA2 -050	BMA2 -063
CDLG1	-	_	-	-	BMA2	BMA2	BMA2			
MGC	-	_	-	-	-020	-025	-032	BMA2 -040	BMA2 -050	_
RHC, MLGC, REC	-	-	-	-					_	-
RSDG	_	_	_	_	-	-	-		BMA2	_

Mounting screw set (Stainless steel specification)

Use the following mounting screw set according to the required operating conditions. (Mounting band is not included.)

BBA4: For D-C7/C8/H7


D-H7BAL is mounted on the cylinder with the above stainless steel screw BBA4 before shipment or BBA4 is enclosed with D-H7BAL when shipped without cylinder.



Mounting Bracket

Band mounting

<Applicable auto switch> Reed switch D-A33, D-A34, D-A44 Solid state switch D-G39, D-K39



①Loosen the auto switch mounting screws at both sides to pull down the hook. ②Put a mounting band on the cylinder tube and set it at the auto switch mounting position, and then hook the band.

③Screw lightly the auto switch mounting screw.


④Set the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (The tightening torque should be about 2 to 3Nm.)

SModification of the detecting position should be made in the condition of S.

Part No. of auto switch mounting band

								<u> </u>					
Cylinder					I	Bore	size ((mm)					
series	20	25	32	40	50	63	80	100	125	140	160	180	200
CDA1, CDBA1, CDV3 CDVS, CDLA, CE2, CNA	_	_	_	BD1 -04M	BD1				—	_	-	_	-
CDL1				-04101	-05101	-00101	-00101	- 10101	BS1	BS1	BC1	_	_
CDS1	_	_	_	_	_	_	_	_		-140		BS1 -180	BS1 -200
RHC	BD1 -01M			BD1 -04M	_	_	-	_	-	_	-	-	_

<Applicable auto switch> Reed switch D-A33A, D-A34A, D-A44A Solid state switch D-G39A, D-K39A



①Tighten completely the switch mounting screw on the switch body side.
②Put a mounting band on the cylinder tube and set it at the auto switch mounting position. Put the mounting section of auto switch between the interval of mounting band, then adjust the position of mounting holes of switch to those of mounting band.
③Lightly thread the auto switch mounting screw through the mounting hole into the thread part of band fitting.

(4)After reconfirming the detecting position, tighten the mounting screw to secure the auto switch. (The tightening torque of M5 screw should be about 2 to 3Nm.) (5)Modification of the detecting position should be made in the condition of (3).

Part No. of auto switch mounting bracket (including band and screw)

Outlington against	Bore size (mm)									
Cylinder series	20	25	32	40	Techn Data					
CDM2, CDBM2 CDLM2	BM3-020	BM3-025	BM3-032	BM3-040	Data					



2**U-**Technical

Information **2**


How to Mount and Move the Auto Switch

Mounting Bracket Rail mounting

<Applicable auto switch>

Reed switch D-A72, D-A73, D-A80, D-A72H, D-A73H, D-A76H, D-A80H D-A73C, D-A80C, D-A79W Solid state switch D-F79, D-F7P, D-J79, D-F7NV, D-F7PV, D-F7BV, D-J79C D-F79W, D-F7PW, D-J79W, D-F7NWV, D-F7BVV D-F79F, D-F7LF, D-F7BAL, D-F7NTL

How to mount and move the auto switch



]Slide the auto switch mounting nut inserted into the mounting rail and set it at the auto switch mounting position.

⁽²⁾Fit the convex part of auto switch mounting arm into the concave part of auto switch mounting rail. Then slide the switch over the nut.

(CDQ2 series: Fit the convex part of auto switch mounting arm through the auto switch spacer into the concave part of auto switch mounting rail.)

3 Push the auto switch mounting screw lightly into the mounting nut through the hole of auto switch mounting arm.

④After reconfirming detection position, tighten the mounting screw to secure the auto switch. (Tightening torque of M3 screw should be 0.5 to 0.7Nm.)
 ⑤Modification of the detecting position should be made in the condition of ③.

|--|

						Bo	ore size (m	m)					
Cylinder series	12	16	20	25	32	40	50	63	80	100	125	140	160
CDQ2	BQ-1	BQ-1	BQ-1	BQ-1	BQ-2	BQ-2	BQ-2	BQ-2	BQ-2	BQ-2	BQ-2	BQ-2	BQ-2
MDU	-	-	-	BMU1-025	BMU1-025	BMU1-025	BMU1-025	BMU1-025	-	-	-	-	-
RSDQ	-	-		BQ-1				-	-	-	-	-	-
MK, MK2	-	-	BQ-1	BQ-1	BQ-1 BQ-2	DO 0	BQ-2	DO 0	-	-	—	-	-
CE1	BQ-1	_		_		BQ-2		BQ-2	-	_	_	-	_
CXT	_	_	_	_			_	-	_	-	—	-	

Mounting screw set (Stainless steel specification)

Use the following mounting screw set (Nut included.) according to the required oper-

ating conditions. (Auto switch spacer is not included.)

BBA2: For D-A7/A8/F7/J7

D-F7BAL is mounted on the cylinder with the above stainless steel screw BBA2 before shipment of BBA2 is enclosed with D-F7BAL when shipped without cylinder.




Mounting Bracket Tie-rod mounting

<Applicable auto switch>

Reed switch	D-A53, D-A54, D-A56, D-A64, D-A67
	D-A59W
Solid state switch	D-F59, D-F5P
	D-J59, D-J51, D-F5BAL
	D-F59W, D-F5PW, D-J59W
	D-F59F, D-F5LF
	D-F5NTL

How to mount and move the auto switch



TFix the auto switch on the auto switch mounting bracket with the mounting screw (M4) and install the set screw.

②Fit the mounting bracket into the cylinder tie-rod and then fix the auto switch at the detecting position with the hexagonal wrench. (Be sure to put the auto switch on the surface of cylinder tube.)

③When changing the detecting position, loosen the set screw to move the auto switch and then re-fix the auto switch on the cylinder tube. (Tightening torque of M4 screw should be 1 to 1.2 Nm.)

Part No. of auto switch mounting bracket (including bracket, mounting screw and set screw)

Cylinder		Bore size (mm)									
series	32	40	50	63	80	100	125	140	160	180	200
CDA1, CDBA1, CDV3 CDVS, CDLA, CE2, CNA	-	BT	BT	BT	BT	BT	_	_	_	_	_
CDL1	-	-04	-04	-06	-08	-08	вт	вт	вт	-	-
CDS1	-	_	_	_	_	_	-12	-12	-16	BT -18A	BT -20
MDB/MDBB	BT-03	BT-03	BT-05	BT-05	BT-06	BT-06	-	-	-	—	-


Mounting screw set (Stainless steel specification)

Use the following mounting screw set (Set screw included.) according to the required operating conditions. (Mounting bracket is not included.) BBA1: For D-A5/A6/F5/J5

D-F5BAL is mounted on the cylinder with the above stainless steel screw BBA1 before shipment or BBA1 is enclosed with D-F5BAL when shipped without cylinder.

<Applicable auto switch> Reed switch D-A33C, D-A34C, D-A44C Solid state switch D-G39C, D-K39C

How to mount and move the auto switch



The mounting bracket $\mbox{\sc A}$ on the auto switch with the set screw.

②Fit the convex part of mounting bracket into tie-rod and set the auto switch at the mounting position.

③Insert the mounting bracket B from the underneath and put lightly in the tierod with the mounting screw.

④Set the whole body to the detecting position by sliding, tighten the mounting screw to secure the auto switch. (Tightening torque of M5 screw should be 2 to 3Nm.)

 $\textcircled{5}\mbox{Modification}$ of the detecting position should be made in the condition of 3.

Part No. of auto switch mounting bracket (including bracket and screw)

Culindar carios	Bore size (mm)					
Cylinder series	40	50	63	80	100	
CDA1, CDBA1	BA3	BA3	BA3	BA3	BA3	
CDV3, CDVS, CDL1, CE2, CNA	-040	-050	-063	-080	-100	



RB

J

D

-Х

20-

Technical


Data

Mounting Bracket Direct mounting

<Applicable auto switch>

Reed switch D-90/97, D-90A/93A

How to mount and move the auto switch




Part No. of auto switch mounting bracket (including bracket and screw)

Cylinder		Bore size (mm)						
series	6	10	15	16	20	25	32	
CDJP-□D	BP-1	BP-1	BP-1	-	-	-	-	
CDU	BU-1	BU-1	—	BU-1	BU-1	BU-1	BU-1	

<Applicable auto switch>


Reed switch	D-A90(V)/A93(V)/A96(V)
	D-F9N(V)/F9P(V)/F9B(V)/F9NW(V)/
	F9PW(V)/F9BW(V)/F9BAL

How to mount and move the auto switch



<Applicable auto switch> Reed switch D-E73A/E76A/E80A Solid state switch D-M5N/M5P/M5B D-M5NW/M5PW/M5BW D-M5NTL/M5PTL

How to mount and move the auto switch



①Insert the auto switch mounting nut into the auto switch mounting groove and then set the switch at the mounting position by sliding. ②Put the convex part of auto switch into the mounting groove and slide it over the nut.

③Push the auto switch mounting screw lightly into the mounting nut through the mounting hole.

(4)After reconfirming detecting position, tighten the mounting screw to secure the auto switch. (Tightening torque of M2.5 screw should be 0.1 to 0.2Nm.)

Part No. of auto switch mounting bracket (including nut and screw)

Cylinder	-	Bore size (mm)	
series	25	32	40
ML1 M2.5 X 12 ℓ	BMY2-025	BMY2-025	BMY2-025

<Applicable auto switch>

Reed switch D-Z73/Z76/Z80 Solid state switch D-Y59[&]/Y69[&]/D-Y7P(V) D-Y7NW(V)/Y7PW(V)/Y7BW(V) D-Y7BAL

How to mount and move the auto switch

①Insert the auto switch into the mounting groove and set it at the auto switch mounting position.


②After confirming the detecting position, tighten the mounting screw to secure the auto switch.
③Modification of the detecting position should be made in step ①.



Mounting Bracket Direct mounting

<Applicable auto switch> Solid state switch D-P5DWL

How to mount and move the auto switch



①Mount the mounting bracket onto the mounting nut by tightening bracket fixing screw lightly through the mounting hole on the top of bracket.

②Insert the mounting bracket assembly (bracket+nut) into the mounting groove and set it at the auto switch mounting position.

③Push the auto switch mounting screw lightly into the auto switch through the mounting hole to secure.

(4)After reconfirming detection position, tighten the mounting screw to secure the auto switch. (Tightening torque should be 0.5 to 0.7Nm.)

Part No. of auto switch mounting bracket (including bracket and screw)

Culinder cories	Bore size (mm)					
Cylinder series	40	50	63			
MK, MK2	BQP1-050	BQP1-050	BQP1-050			

RB
J
D
-X
20-

Technical Data

Auto Switch Weight (Single Unit)

Band mounting

Band mounting (g)							
Applicable auto	Model		Lea	ad wire len	gth		
switch	Model	0.5m	3m	None			
	D-C7	2 wire	9	46			
	D-C8	3 wire	10	50			
	D-C73C D-C80C		14	53	_		
Reed switch	D-B5 D-B6		22	78	_		
	D-B59W	20	76	_			
	D-A3	-	_	116			
	D-A4	_		114			
	D-A3⊡A D-A44A		_	_	110		
		2 wire	11	50	_		
	D-H7	3 wire	13	57	_		
		4 wire	13	56	_		
	D-K5	2 wire	18	68	_		
Solid state switch	D-G5	3 wire	20	78	_		
	2.00	4 wire	20	74	—		
	D-□39	-	_	116			
	D-□39A		_	—	110		
	D-H7C		15	54			

Tie-rod	mounting				(g		
Applicable auto	Model	Model		Lead wire length			
switch		0.5m	3m	None			
	D-A5	2 wire	24	80	_		
	D-A6	3 wire	24	80			
	D-A59W		25	80	-		
		ø40	_	—	162		
	D-A3□C	ø50	_	—	166		
		ø63	_	_	184		
Reed switch		ø80	_	—	210		
		ø100	_	_	232		
	D-A44C	ø40	_	—	160		
		ø50	_	_	164		
		ø63	_	_	182		
		ø80	_	—	208		
		ø100	_	—	230		
	D-J5	2 wire	21	71	_		
Solid state switch		3 wire	23	81	-		
3001011	D-F5	4 wire	22	77	_		

(g)

Rail mounting Applicable Lead wire length auto Model switch 0.5m 2 wire 10 D-A7/A7□H D-A8/A80H 3 wire 11 Reed switch D-A73C 12 D-A80C

	D-A79W		11	53
Solid state switch	D-J7	2 wire	11	50
	D F 7	3 wire	13	57
	D-F7	4 wire	13	56
	D-J79C		13	52

Direct mounting Applicable Lead wire length auto Model switch 0.5m 3m 2 wire 7 35 D-A9/A9 V 3 wire 8 41 D-9 5 23 D-9□A 9 47 Reed switch 2 wire 10 47 D-E7□A D-E8□A 3 wire 11 55 2 wire 9 49 **D-Z7 D-Z8** 3 wire 10 55 2 wire 1 9 50 3 wire 10 53 colour D-Y□ 2 wire 2 11 54 colour 3 wire 11 54 2 wire 14 53 D-M5 Solid state 3 wire 16 60 switch D-Y7BA _ 54

1

2

D-F9□

D-F9BA

2 wire

2 wire

colour 3 wire

colour 3 wire

6

7

7

7

_

31

37

32

34

37

5.3-75

(g)

3m

47

52

54