



Our commitment. Your advantage.

- [Products](#) [Documentation](#) [Resources](#) [My Account](#) [Customer Support](#)

[Home](#) > [Products](#) > [By Type](#) > [Resistors](#) > [Product Feature Selector](#) > Product Details

5350500106 Product Details

[Live Product Chat](#)



5350500106
(1624192-6)

TE Internal Number: 1624192-6

[Active](#)

Variable Resistors

[Always EU RoHS/ELV Compliant \(Statement of Compliance\)](#)

Product Highlights:

- Variable Resistor
- Resistor Type = Potentiometer
- Resistance Selection = K ?
- Resistance = 4.7K ?
- Power Rating = .20 W

[View all Features](#)

Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

- [Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- None Available

Catalog Pages/Data Sheets:

- [Spindle Operated Potentiometers - Type 51 Series - T...](#) (PDF, English)

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files:

- None Available

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Variable Resistor
- [Resistor Type](#) = Potentiometer
- [Resistance \(?\)](#) = 4.7K
- [Element](#) = Carbon
- [Sealed](#) = No
- [Mount Angle](#) = Vertical
- [Termination Type](#) = PCB Terminations
- Comment = Suited for Plugin Accessory

Electrical Characteristics:

- Resistance Selection (?) = K
- [Power Rating \(W\)](#) = 0.20
- [Tolerance \(%\)](#) = 20

Termination Related Features:

- [Termination Post Orientation](#) = In Line

Body Related Features:

- [Series](#) = 51
- [Package, Component Size](#) = 12.5 x 15.8

Configuration Related Features:

- [Sections](#) = Single
- [Adjustment Location](#) = Side
- [Adjustment Style](#) = Spindle (Sold Separately)
- [Operating Function](#) = Single Turn

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C
- RoHS/ELV Compliance History = Always was RoHS compliant

Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) = 500

Other:

- Brand = Citec

[Provide Website Feedback](#) | [Need Help?](#)