



# HSC250150RJ Product Details



## HSC250150RJ (2-1630024-9)

TE Internal Number: 2-1630024-9

Active

View 3D PDF

### Fixed Resistors

Always EU RoHS/ELV Compliant (Statement of Compliance)

#### Product Highlights:

- Fixed Resistor
- Resistor Type = Power Resistor
- Resistance Selection = <1K  $\Omega$
- Resistance = 150  $\Omega$
- Power Rating = 250.00 W

[View all Features](#)

### Quick Links

- ▶ Pricing & Availability
- ▶ Search for Tooling
- ▶ Product Feature Selector
- ▶ Contact Us About This Product

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

## Documentation & Additional Information

### Product Drawings:

- [HSC250 ALUMINIUM HOUSED POWER RESISTOR](#) (PDF, English)

### Catalog Pages/Data Sheets:

- [1309350\\_PASSIVE\\_COMPONENT](#) (PDF, English)
- [Aluminium Housed Power Resistors - Type HS Series](#) (PDF, English)
- [4-1773460-6\\_RESISTIVE\\_SOLUTIONS\\_RAIL](#) (PDF, English)
- [8-1773459-4\\_POWER\\_FILTERING\\_AND\\_RESISTIVE\\_SOLUTIONS...](#) (PDF, English)

### Product Specifications:

- None Available

### Application Specifications:

- None Available

### Instruction Sheets:

- None Available

### CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version U)
- [3D Model](#) (IGES, Version U)
- [3D Model](#) (STEP, Version U)

### Additional Information:

- [Product Line Information](#)

### Related Products:

- [Tooling](#)

[List all Documents](#)

## Product Features (Please use the Product Drawing for all design activity)

### Product Type Features:

- Product Type = Fixed Resistor
- Resistor Type = Power Resistor
- Element = Wirewound

### Electrical Characteristics:

- Resistance Selection ( $\Omega$ ) = <1K
- Resistance ( $\Omega$ ) = 150
- Power Rating (W) = 250.00
- Tolerance (%) = 5

### Termination Features:

- Termination Type = M6 Threaded Stud

### Body Features:

- Mount Style = Chassis Mount
- Package, Component Size = 163 x 73

### Configuration Features:

- Number of Terminations = 2
- Number of Resistors = 1

### Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Hand solderable with lead free solder
- RoHS/ELV Compliance History = Always was RoHS compliant

### Conditions for Usage:

- [Temperature Coefficient \(ppm/°C\)](#) =  $\pm 30$

### Operation/Application:

- [Application](#) = High Power

### Packaging Features:

- [Package Type](#) = Loose Piece - Tray

### Other:

- Series = HS
- Brand = CGS

## Corporate Information

[About TE](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)  
[Terms & Conditions](#)  
[Privacy Policy](#)  
[AODA Accessibility Policy](#)  
[AODA Multi-Year Accessibility Plan](#)

## Quick Links

[Distributor Inventory](#)  
[Product Cross Reference](#)  
[Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

## Customer Support

[Email or Chat With Us](#)  
[Find a Phone Number](#)  
[Knowledge Base](#)  
[Manage Your Account](#)

## Keep Me Informed

