
DSM is the commercial industry's smallest D-type connector for shielded I/O wire-to-board applications. Requiring less than 1/3 the area of a traditional D Subminiature connector, MDSM is designed for situations where space and EMI shielding are the primary design drivers.

Unlike other micro connectors, MDSM's rugged construction and unique contact design combined with a PdNi contact finish provide durability of 10,000 mating cycles. All of this comes in a sleek package that includes a snap together shield can and a slide over boot producing a cable assembly with an overmolded look and a low assembled cost. MDSM is an ideal solution for applications where size, shielding, durability and aesthetics are key design criteria.

Applications:

Electronic Notepads VME Cards Multiplexors Serial Storage Devices Computer Workstations Hand Held Devices Bar Code Scanners



Product Features

1,27 (.050) Pitch / Saves Space Fully Shielded / Reduces EMI Crimp Contacts / Applied Cost Savings Accessories Included / Fewer Part Numbers PdNi Plating / 10,000 Mating Cycles Stacked Versions / Saves Horizontal Space Slide Over Boot / Results in Overmolded Appearance Choice of Two Different Latching Options (Thumbscrew / Push-Pull) Approvals & Certifications SSA (Serial Storage Architecture) U.L. File Number E8572 ISO 9001

Specifications

Temperature Rating <u>– 55°C to 125°C</u>

Current Rating 1 A — temp dependent

Contact Resistance 20 m Ω Max.

Insulation Resistance $5000 \text{ M}\Omega \text{ Min.}$

Dielectric Withstanding Voltage 350 V at Sea Level

Durability 10,000 Mating Cycles

Shock / Vibration 50 G's / 50 G's

Wire Size 26 to 30 AWG

Materials and Finishes


Description	Material	Finish
Shell	Steel	Nickel
Shield Can	Steel	Tin
Cover	Steel	Tin
Insulator	Thermoplastic, UL94 V-0	None
Contacts	Copper Alloy	Gold flash over 30 microinches PdNi in mating area, Tin on balance

Contact Arrangements

(Face View of Pin Insert — Use Mirror Image for Socket Side)










Locking/Latching Options

Jackscrew




The jackscrew locking system is designed for applications which require a secure connection. Utilize thumbscrews when the connectors are infrequently unmated.

Push/Pull




The push/pull latching system is designed for applications which require a quick connect and disconnect. A spring retention mechanism latches to a post on the board side to prevent unintentional unmatings.

Z10 Jackpost



Z42 Jackpost




Note: Two Jackposts supplied with boardside connectors.

Note: Two Jackposts supplied with boardside connectors.

Cable Assemblies






Layout	Jackscrew Part Numbers	Push/Pull Part Numbers	A max.	B 0,10±(.004)	C 0,10±(.004)	Ø D Cable Max.
9	CA111972-22	CA111972-43	19,90 (.783)	14,35 (.565)	9,45 (.372)	5,70 (.224)
15	CA111972-11	CA111972-44	23,70 (.993)	18,16 (.715)	13,17 (.519)	6,70 (.264)
25	CA111972-12	CA111972-45	30,05 (1.183)	24,51 (.965)	19,52 (.758)	7,90 (.311)

PCB Connector 90° - Single






Note: Standard jackpost offering recommended for use with .060 panel.


No. of	Part Numbe	ers - Single	Α		С	D		F
Contacts	Thumbscrew	Push/Pull	max.	В	max.	max.	E	±0,05 (.002)
9	MDSM-9PE-Z10-VR25*	MDSM-9E-Z42-VR25*	19,90 (.783)	14,35 (.565)	8,60 (.339)	9,00 (.354)	5,08 (.200)	10,24 (.403)
15	MDSM-15PE-Z10-VR22	MDSM-15PE-Z42-VR22	23,60 (.929)	18,16 (.715)	12,30 (.484)	12,90 (.508)	8,89 (.350)	14,01 (.551)
25	MDSM-25PE-Z10-VR17	MDSM-25PE-Z42-VR17	29,95 (1.179)	24,51 (.965)	18,65 (.734)	19,25 (.758)	15,24 (.600)	20,35 (.801)

^{*}For use with SSA applications

PCB Connector 90° - Stacked







No. of	Part Numbers	s - Stacked	A		С	D		
Contacts	Thumbscrew	Push/Pull	max.	В	max.	max.	E	F
18	MDSM-18PE-Z10-VR25*	MDSM-18PE-Z42-VR25*	19,90 (.783)	14,35 (.565)	8,60 (.339)	9,00 (.354)	5,08 (.200)	10,24 (.403)
30	MDSM-30PE-Z10-VR22	MDSM-30PE-Z42-VR22	23,50 (.925)	18,16 (.715)	12,30 (.484)	12,71 (.500)	8,89 (.350)	14,00 (.551)


^{*}For use with SSA applications


Cable Connectors (Unassembled Components)

Jackscrew



Cable connectors are supplied as complete kits with insulator, hood, locking hardware, shell/shield assembly, and cover, bulk packaged.






Push/Pull



Cable connectors are supplied as complete kits with insulator, hood, shell/shield assembly, and cover, bulk packaged.





Jackscrew	Push/Pull	Α	В	С	D	Max.
Part Numbers	Part Numbers	max.	0,10 (.004)	0,10 (.004)	max.	Cable Entry
MDSM-9SC-Z11-VS1	MDSM-9SC-Z24-VS1	19,90 (.783)	14,35 (.565)	9,45 (.372)	35,50 (1.40)	5,70 (.224)
MDSM-15SC-Z11-VS1	MDSM-15SC-Z24-VS1	23,70 (.993)	18,16 (.715)	13,17 (.519)	35,50 (1.40)	6,70 (.264)
MDSM-25SC-Z11-VS1	MDSM-25SC-Z24-VS1	30,05 (1.183)	24,51 (.965)	19,52 (.769)	42,50 (1.67)	7,90 (.311)
	Part Numbers MDSM-9SC-Z11-VS1 MDSM-15SC-Z11-VS1	Part Numbers Part Numbers	Part Numbers Part Numbers max. MDSM-9SC-Z11-VS1 MDSM-9SC-Z24-VS1 19,90 (.783) MDSM-15SC-Z11-VS1 MDSM-15SC-Z24-VS1 23,70 (.993)	Part Numbers Part Numbers max. 0,10 (.004) MDSM-9SC-Z11-VS1 MDSM-9SC-Z24-VS1 19,90 (.783) 14,35 (.565) MDSM-15SC-Z11-VS1 MDSM-15SC-Z24-VS1 23,70 (.993) 18,16 (.715)	Part Numbers Part Numbers max. 0,10 (.004) 0,10 (.004) MDSM-9SC-Z11-VS1 MDSM-9SC-Z24-VS1 19,90 (.783) 14,35 (.565) 9,45 (.372) MDSM-15SC-Z11-VS1 MDSM-15SC-Z24-VS1 23,70 (.993) 18,16 (.715) 13,17 (.519)	Part Numbers Part Numbers max. 0,10 (.004) 0,10 (.004) max. MDSM-9SC-Z11-VS1 MDSM-9SC-Z24-VS1 19,90 (.783) 14,35 (.565) 9,45 (.372) 35,50 (1.40) MDSM-15SC-Z11-VS1 MDSM-15SC-Z24-VS1 23,70 (.993) 18,16 (.715) 13,17 (.519) 35,50 (1.40)

Note: VS1 refers to packaging multiples of 100. Contacts are sold separately, see this page.

Crimp Contacts







	Part N	Numbers
	1,000 Piece Reel	10,000 Piece Reel
Socket	MDS-S-TS	MDS-S-RL

For crimp tooling, see page 101.



Contact Crimping Tools

Parallel Action Low Volume Hand Tool



Part Number: CCTP-MDS

Note: For use with individual contacts (break off reel MDS-S-TS or MDS-S-RL.

Hand Tool



Part Number: CCTR-MDS

Note: For use with reeled contacts - Part Number MDS-S-TS.

Semi-Automatic Crimper/Stripper



Part Number: ABT-620-MDS (Lease Only)

Note: For use with reeled contacts - Part Number MDS-S-RL. For additional information, see page 275. Crimp dies for SSA Cable will be offered by ITT Cannon. Consult factory for details.

Contact Insertion/Extraction Tools

Jackpost Tool



Part Number: CIET-MDSM

Note: For use with Z10 Jackpost.

Insertion Tool



Part Number: 120090-0102

Note: Contacts cannot be removed from MDSM connectors.

Shield Crimp Tooling

Shield crimping requires four items; one press, one locator, and one each of the two dies listed below.

Locator and Dies for Shield Termination Ordered Separately

_						
		Part Numbers				
	Layout	Locator	Die			
	9	317-8666-013	274-8649-332/274-8649-333			
	15	317-8666-014	274-8649-334/274-8649-335			
	25	317-8666-016	274-8649-338/274-8649-339			

Note: For assembly instructions and crimping information, refer to Manual #MY-1/190.

Hand Press



Part Number: CHP-MDSM-SR

Pneumatic Press



Part Number: CPT-MDSM-SR


MDSM SSA Compatible Cable Assemblies



ITT Cannon's 9 position MDSM connectors have been designed into the ANSI specification called SSA, "Serial Storage Architecture," as the external I/O. SSA is a new serial interface for interconnecting storage devices, storage subsystems, servers and workstations. Storage subsystems are increasing in function, availability, density and performance. With this comes the trend for them to become more complex and ITT Cannon has the interconnect system which meets SSA's high performance requirements.

SSA is an architecture which allows these new subsystems to be implemented more easily and at lower costs than other new high speed parallel interfaces. SSA permits the transfer of data at progressively higher speeds - 20 MB/sec interface currently available with 40 MB/sec becoming available in 1997/98. ITT Cannon's MDSM connector not only functions at these high speeds, but also brings to SSA smaller, less cumbersome and higher reliability cables and connectors than current options.

ITT Cannon is offering SSA compatable external cable assemblies in six different lengths to meet your needs. These assemblies consist of two MDSM 9SC type cable connectors terminated to SSA specified external cable.




Note: Cables shown with Z50 thumbscrews


-	Х	
Part Number	Meter (Feet)	Tolerance
CA112104	0,50 (1.600)	±25,00 (1.000)
CA112104-1	1,00 (2.200)	±25,00 (1.000)
CA112104-2	3,00 (9.800)	±25,00 (1.000)
CA112104-3	5,00 (16.400)	±64,00 (2.500)
CA112104-4	10,00 (32.800)	±64,00 (2.500)
CA112104-5	20,00 (65.600)	±64,00 (2.500)

Note: For push/pull assemblies or other thumbscrews, please consult the factory. Crimp dies for SSA applications will be offered by ITT Cannon. Consult factory for details.

Pinout

SSA External Cable Wiring Table






Note: Shield connected to both shells.

External Cable Pinouts

	P1	P2		
Pin	Signal Name	Pin	Signal Name	
2	LineOut-	4	LineIn -	
6	LineOut+	9	LineIn+	
4	LineIn-	2	LineOut-	
9	LineIn+	6	LineOut+	

Note: Pins 1, 3, 5, 7 and 8 are not connected.

SSA External Cable Wire Cross Section (For Reference Only)



Transfer Impedance Performance Requirements for External SSA Connections

Frequency MHz	Value (dB-0hm)(max.)
30	-25
159	-16
500	-10