




Dead Blow Hammers



These dead blow hammers are a coated die-cast head and handle of aluminium alloy with shock absorbent rubber grip.




The hollow head is partially filled with steel shot which adds to the weight, prevents rebound and delivers 'dead' blows of maximum impact.

Fitted as standard with two screw-in durable nylon faces which when worn can be instantly replaced by hand.

For certain applications tough brown polyurethane faces may be preferred.

THE IDEAL HAMMER FOR SUSTAINED AND EFFECTIVE BLOWS WITHOUT RECOIL.

Used by Engineers, Sheet Metal Workers, Fitters, Tool Makers etc.

Standard	Approx Weight	Face Diameter		Nominal Length	Spare Faces	
					RS Stock No.	
RS Stock No.	g	inch	mm	mm	Hard White (standard)	Brown Tough
732-577	700	1.1/2	38	305	732-599	732-606
600-795	900	1.3/4	44	305	600-802	600-818
732-583	1150	2	50	330	732-628	732-634
382-2083	1850	2.1/2	63	370		



Dead Blow Hammer Replacement Faces



WHITE

Hard Nylon - Shore hardness D 61-65 The best all-purpose face.
For light and heavy assembly work.

BROWN

Tough Polyurethane - Shore hardness D 58-62 Tough and abrasive resistant.
Ideal for striking sharp surfaces including cutting forms, steel rule die
assembly.

Diameter	WHITE Hard Nylon	BROWN Tough	Diameter
			
mm	RS Stock No.	RS Stock No.	inch
38	732-599	732-606	1.1/2
44	600-802	600-818	1.3/4
50	732-628	732-634	2