


# Miniature Flange Mount With Wire Leads 1032 Series

## Applications

- Flanges for rapid mounting
- Convenient surface mounting
- Includes adhesive mounting strips
- Mounting screws



## General Specifications

Enclosure	ABS Plastic
Temperature Range	-40°F to 150°F (-40°C to 65°C)
Environmental	Hermetically Sealed Reed Switch Encapsulated in Polyurethane
NEMA Rating	1, 2, 3, 4, 4x, 5, 6, 12
Protection Class	IP 67
Response Time	1 msec max.
Life Cycles	100,000 Under Full Load, 10,000,000 Under Dry Circuit
Lead Types/O.D.	#22 wire / 0.05" (0.15cm)
Color	Natural
UL/ULC Listed	All Models



Order Information		Electrical Specifications					
Part Number	Contact <sup>1</sup> Configuration	Load Rating (AC/DC)	Switching Voltage (AC/DC)	Switching Current (AC/DC)	Contact Resistance	Sense Range <sup>2</sup> Nominal	Lead Length
1032-N	N.O.	7.5W/VA	100V	0.5A	0.2 Ohms	0.6"(1.6cm)	1'
1032W-N	N.O.	7.5W/VA	100V	0.5A	0.2 Ohms	1.0"(2.5cm)	1'
1937-N	Actuator Only						

**Warning— Each electrical rating is an individual maximum and cannot be exceeded!**

<sup>1</sup> Configuration with actuator away from the switch

<sup>2</sup> Proximity of ferrous materials usually reduces sense range — typically by 50%. The shape and type of material cause a wide diversity of effects. Testing is required to determine actual sense range for specific applications. As measured on a nonferrous surface.

Gap distances are nominal make distance ± 20%. Gap Specifications are for switch to make. Break distance is approximately 1.1 to 1.5 times make.