



# Product Catalog

for professionals

[Products](#) > 97564

## 97564 – F13BX/E/835/ECO

GE Ecolux® Biax® T4 - Facilities; Retail Display; Hospitality; Office; Restaurant; Warehouse

Print this Page

Convert to PDF

**This product is no longer manufactured. Remaining stock will be sold.**

High Color Rendering  
Energy Savings

### GENERAL CHARACTERISTICS

Lamp type	Compact Fluorescent - Plug-In
Bulb	T4
Base	GX23
Primary Application	Facilities; Retail Display; Hospitality; Office; Restaurant; Warehouse
Equivalent Wattage (NOM)	60 W
Rated Life (Vert)	10000 hrs
Rated Life (NOM)	10000 hrs
Starting Temperature (MIN)	-20 °C(-4 °F)
Mercury Content (NOM)	3 mg
Picograms of Mercury (NOM)	423 picograms Hg per mean lumen hour
Additional Info	TCLP compliant

- Contains Mercury, For more on clean up and safe disposal visit [epa.gov/cfl](http://epa.gov/cfl)

### PHOTOMETRIC CHARACTERISTICS


Initial Lumens (Vert)	825
Initial Lumens (NOM)	825
Initial Lumens (Hor)	63
Mean Lumens (NOM)	710
Nominal Initial Lumens per Watt (NOM)	63
Color Temperature (NOM)	3500 K
Color Rendering Index (CRI) (NOM)	82

### ELECTRICAL CHARACTERISTICS


Wattage (NOM)	13.0
Voltage (MIN)	13.0
Voltage (NOM)	120.0
Lamp Current (NOM)	0.285 A
Current Crest Factor (MAX)	1.7



Bulb



Base



[View Larger](#)

### ADDITIONAL RESOURCES

[Disposal Policies & Recycling Information](#)

**DIMENSIONS**

Maximum Overall Length (MOL) (NOM)	7.0000 in (177.8 mm)
Nominal Length (NOM)	7.0000 in (177.8 mm)

**PRODUCT INFORMATION**

Product Code	97564
Description	F13BX/E/835/ECO
ANSI Code	60901-IEC-0013-1
Standard Package	BUNDLE
Standard Package Quantity	100
Sales Unit	Unit
No Of Items Per Sales Unit	1
No Of Items Per Standard Package	100
UPC	043168975643

**▲ CAUTIONS & WARNINGS**

-

[See list of cautions & warnings.](#)**NOTES**

- Based on 60Hz reference circuit.
- Fluorescent lamp lumens decline during life

[Return To Top](#)