

- Low cost crystal for mass market applications
- Surface mount version of 49S crystal
- Comprehensive stock of standard frequencies
- Customized parts readily available
- Industry-standard package
- Low-profile version available

### **DESCRIPTION**

M49 crystals are low profile surface mount crystals having a similar footprint to standard HC49 or 49S crystals. M49 crystals are ideal for use in low cost, mass-market applications. ML49 is a lower profile version.

## **SPECIFICATION**

**RoHS Status:** 

0. 20					
Package Designation					
	M49:	12.4 x 4.5 x 4.0mm			
	ML49:	12.4 x 4.5 x 3.0mm			
Frequency Range					
3.20MHz to 48.0MHz:		AT-Cut Fundamental			
27.0MHz to 70.0MHz:		AT-Cut 3rd Overtone			
24.0MHz to 48.0M	۸Hz:	BT-Cut Fundamental			
Calibration Tolerance:		±30ppm at 25°C standard			
		from ±5ppm available			
Frequency Stability over Temp:		See table			
Operating Temperature Range:		See table			
Shunt Capacitance (C0):		4pf typical, 7pF maximum			
Load Capacitance (CL):		Series or from 8pF to 32pF			
		(Customer specified)			
Ageing:		±3ppm/year maximum			
		(Ta = 25°C, drive 100μW)			
Drive Level:		100μW typical, 500μW maximum			
Reflow Soldering:		260°C, 10s maximum			
Holder:		Hermetic seal, resistance weld			
Packaging:		EIA 24mm tape and reel			
		1000 pieces per reel			

## FREQUENCY STABILITY vs. OPERATING TEMPERATURE RANGE

RoHS Compliant and Pb free

Stability	Temperature	Stability ppm				
Code	Range	±10	±15	±20	±25	±30
Χ	-10 to +60°C	✓	✓	✓	✓	✓
Υ	-20 to +70°C	-	✓	✓	✓	✓
1	-40 to +85°C		✓	✓	✓	✓

√ = available, ■ = contact Mercury

## **EQUIVALENT SERIES RESISTANCE**


Crystal Cut Mode	ESR Ω Max.
AT-Fund	300
AT-Fund	120
AT-Fund	60
AT-Fund	40
BT-Fund	40
AT-3rd OT	150
AT-3rd OT	100
AT-3rd OT	80
	Mode  AT-Fund AT-Fund AT-Fund AT-Fund BT-Fund AT-3rd OT AT-3rd OT

# 49SMD Standard and Low Profile





### **OUTLINE & DIMENSIONS**



## PART NUMBER FORMAT

