

FEATURES

- Miniature size: 7.0mm x 5mm x 1.2mm height
- Gold-plated ceramic base with metal seam-welded lid
- To minimize EMI the whole crystal may be grounded
- Tight tolerance of ± 10 ppm for telecommunications use
- High shock and vibration resistance
- Ideal for PDAs, GPS, PCMCIA and hand-held equipment

DESCRIPTION

Miniature surface-mount MQ crystals are produced using a ceramic substrate and fitted with a hermetically-sealed metal lid. The crystals are competitively priced, well-suited to mass-market electronic applications and may also be produced to close tolerances making this crystal a good choice for applications requiring low mass and tight tolerances.

SPECIFICATION

Frequency Range AT-Cut Fundamental: 6.0MHz to 45.0MHz AT-Cut 3rd Overtone: 30.0MHz to 125.0MHz Calibration Tolerance at 25°C*: from ± 5 ppm ± 10 , ± 20 ppm (±30ppm standard) Frequency stability -10° to +60°C from ±5ppm -20 $^{\circ}$ to +70 $^{\circ}$ C from ±10ppm -40° to +90°C from ±15ppm -55 to +125°C from ±20ppm Storage Temperature: -55°~+105°C **Effective Series Resistance:** See table Shunt Capacitance (C0): 2pF to 4pF typical, 7pF maximum Series or from 10pF to 32pF Load Capacitance (CL): (Customer specified CL) < ±3ppm per year at +25°C Ageing: Drive level: 100 μW maximum Reflow Soldering: 10s maximum, 260°C twice or 180s at 230°C, once. Package: Ceramic base, metal lid, Hermetic seal Packaging: 16mm EIA tape and reel 1000 pieces per reel

RoHS compliant and lead free

EQUIVALENT SERIES RESISTANCE

RoHS Status:


| Frequency Range MHz | Crystal Cut/ Mode | ESR Ohms Max. |
|------------------------|----------------------|------------------|
| 6.0 ~ 11.0 | AT Fund. | 60 |
| 11.1 ~ 14.0 | AT Fund. | 50 |
| 14.1 ~ 45.0 | AT Fund. | 40 |
| 30.0 ~ 40.0 | AT 3rd OT | 100 |
| 40.1 ~ 50.0 | AT 3rd OT | 80 |
| 50.1 ~ 125 | AT 3rd OT | 90 |

7 x 5mm SMD, 4 pad





OUTLINE & DIMENSIONS



PART NUMBER FORMAT

