


## **Series** FLOTECT. Liquid Level Switch L6







# Easy In-wall or External Installation, Up to 2000 psig (138 bar)



Surprisingly compact, the Series L6 Flotect® Level switch is designed and built for years of trouble-free service in a wide variety of process liquid level applications. Operation is simple and dependable with no mechanical linkage as the level switch is magnetically actuated. The float lever pivoted within the body moves when the process liquid displaces the float. A magnet on the opposite end of the float lever controls a second magnet on the switch actuating lever located in the switch housing.

#### **FEATURES**

- Leak proof lower body machined from bar stock
- · Choice of models for direct side wall mounting or mounted in a tee to act as an external
- · Explosion-proof (listings included in specifications)
- · Electrical assembly can be easily replaced without removing the unit from the installation so that the process does not have to be shut down
- Sensitive to level changes of less than 1/2" (12 mm)

				Max.	
			Floor	Pressure	Min.
Model	Body	Installation	Float Material	psig (box)	Sp. Gr.
				(bar)	
L6EPB-B-S-3-O	Brass	Side Wall Mounting	Polypropylene Spherical	1000 (69)	0.9
L6EPB-B-S-3-A	Brass	Side Wall Mounting	304 SS	200 (13.8)	0.5
l	_		Cylindrical		
L6EPB-B-S-3-C	Brass	Side Wall Mounting	304 SS Spherical	350 (24.1)	0.7
L6EPB-B-S-3-B	Brass	Brass External Float	Polypropylene	250 (17.2)	0.9
		Chamber (Tee)	Spherical	, ,	
L6EPB-B-S-3-H	Brass	Brass External Float	304 SS	250 (17.2)	0.7
		Chamber (Tee)	Spherical	, ,	
L6EPS-S-S-3-O	303 SS	Side Wall Mounting	Polypropylene	2000 (138)	0.9
			Spherical		
L6EPS-S-S-3-A	303 SS	Side Wall Mounting	304 SS	200 (13.8)	0.5
		_	Cylindrical		
L6EPS-S-S-3-C	303 SS	Side Wall Mounting	304 SS	350 (24.1)	0.7
		ŭ	Spherical	, ,	
L6EPS-S-S-3-S	303 SS	304 SS External Float	Polypropylene	2000 (138)	0.9
		Chamber (Tee)	Spherical	, ,	
L6EPS-S-S-3-L	303 SS	304 SS External Float	304 SS	350 (24.1)	0.7
		Chamber (Tee)	Spherical	,	

## **OPTIONS**

Gold Plated Contacts option for dry circuits, add suffix -MV (see electrical rating in

High Temperature option rated 400°F (204°C), add suffix -MT (see electrical rating in specifications, no listings or approvals, only available on models with stainless steel floats) CSA and UL approved construction, includes weatherproof and explosion-proof junction box. add suffix -CSA

ATEX compliant construction includes, weatherproof and explosion-proof, junction box, add suffix -AT

IECEx certified construction, add suffix -IEC

DPDT contacts, change seventh character in model number to "D".

Example: L6EPB-B-D-3-O

Options Not Shown: 1-1/2" and 2" male NPT process connection, 2" female NPT connection tee, and top mount.

### **SPECIFICATIONS**

Service: Liquids compatible with wetted materials.

Wetted Materials:

Float: Solid polypropylene or 304 SS.

Lower Body: Brass or 303 SS.

Magnet: Ceramic.

External Float Chamber (Tee): Matches lower body choice of brass or

303 SS

Other: Lever Arm, Spring, Pin, etc.: 301 SS.

Temperature Limit: -4 to 220°F (-20 to 105°C) Standard, MT high temperature option 400°F (205°C)(MT not UL, CSA, ATEX, IECEx and KC). ATEX compliant AT, IECEx IEC and KC option ambient temperature -4 to 167°F (-20 to 75°C) process temperature: -4 to 220°F (-20 to 105°C).

Pressure Limits: See model chart.

Enclosure Rating: Weatherproof and Explosion-proof. Listed with UL and CSA for Class I, Groups A, B, C and D; Class II, Groups E, F, and G.

(Group A on stainless steel body models only).

ATEX (€0344 W II 2 G Ex d IIC T6 Gb Process Temp≤75°C.

EC-Type Certificate No.: KEMA 04ATEX2128.

ATEX Standards: EN 60079-0: 2009: EN60079-1: 2007. IECEx Certified: For Ex d IIC T6 Gb Process Temp≤ 75°C.

IECEx Certificate of Conformity: IECEx DEK II.0039.

IECEx Standards: IEC 60079-00: 2007; IEC 60079-1: 2007.

Korean Certified (KC) for Ex d IIC T6 Gb Process Temp≤75°C.

KTL Certificate Number: 2012-2454-75.

Switch Type: SPDT snap switch standard, DPDT snap switch optional. Electrical Rating: UL models: 5A @ 125/250 VAC (V~). CSA, ATEX and IECEx models: 5A @ 125/250 VAC (V~); 5A res., 3A ind. @ 30 VDC (V=). MV option: .1A @ 125 VAC (V~). MT option: 5A @125/250 VAC (V~). [MT option not UL, CSA, ATEX or IECEx].

Electrical Connections: UL models: 18 AWG, 18" (460 mm) long.

ATEX/CSA/IECEx models: terminal block.

Upper Body: Brass or 303 SS

Conduit Connection: 3/4" male NPT standard, 3/4" female NPT on

junction box models

Process Connection: 1" male NPT on models without external float chamber, 1" female NPT on models with external float chamber. Mounting Orientation: Horizontal with index arrow pointing down. Weight: Approximately 1 lb (.5 kg) without external float chamber, 1.75 lb

(.8 kg) with external float chamber. Specific Gravity: See chart.

Agency Approvals: ATEX, CE, CSA, IECEx, KTL, UL.