

M12 Rugged Distribution Boxes, Two Signals Per Socket, On-Board M23 Connection, with or without LED

ASBSV-R 4 5-4 | ASBSV-R 8 5-4


ASBSV-R 4/LED 5-4 | ASBSV-R 8/LED 5-4




4- and 8-Ports

ASBSV-R pluggable actuator/sensor distributor, 4 and 8 x M12 ports, 4-poles, with or without LED operating and function display, two signals per socket, ground connection, M23 connection for the control cable, 12-poles

4-Ports




8-Ports




Pin Assignments

M12 Wiring Diagrams

4-Ports



8-Ports





M12 Rugged Distribution Boxes, Two Signals Per Socket, On-Board M23 Connection, with or without LED

Technical Data

Environmental Conditions

Degree of protection	IP65 / IP67
Pollution severity	3
Operating temperature range	-40°C / +80°C (dragchain and UL max. 60°C)

Materials

Contact	CuZn, pre-nickel and gold-plated
Contact bearer	TPU-GF
Housing	Zinc die casting
O-ring	FKM

Electrical Data

Rated voltage	30 V
Rated current*	4 A per outlet / 12 A max. total; at 40°C
Rated impulse voltage	32 V
Contact resistance	≤5mΩ
Insulation resistance	> 10 ⁹ Ω

* only in locked position with its proper counterparts or dust covers

Additional Technical Data

operation display: LED Green
 Function display / channel status:
 LED Channel A: Yellow
 LED Channel B: White

Part Number	Ports	Characteristics
ASBSV-R 4 5-4	ASBSV-R 4/LED 5-4 4	
ASBSV-R 8 5-4	ASBSV-R 8/LED 5-4 8	