

COAXIAL ATTENUATORS

SMA

1 - 2 WATTS

Part number	Frequency range (GHz)	ATTENUATION (dB)				V.S.W.R.				Power (W)		Weight (g)	
		Nom.	DEVIATION				CC - 2	2 - 3	3 - 4	4 - 8	avg.		peak
			DC - 2	2 - 3	3 - 4	4 - 8							
R411800124	DC - 3	0	+ 0.3	+ 0.5			≤ 1.20	≤ 1.30			1	100	5
R411801124		1	± 0.3	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411802124		2	± 0.3	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411803124		3	± 0.3	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411804124		4	± 0.3	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411805124		5	± 0.3	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411806124		6	± 0.3	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411807124		7	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411808124		8	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411809124		9	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411810124		10	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411811124		11	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411812124		12	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411813124		13	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411814124		14	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411815124		15	± 0.5	± 0.5			≤ 1.20	≤ 1.30			1	100	5
R411816124		16	± 0.7	± 0.7			≤ 1.20	≤ 1.30			1	100	5
R411817124		17	± 0.7	± 0.7			≤ 1.20	≤ 1.30			1	100	5
R411818124		18	± 0.7	± 1.0			≤ 1.20	≤ 1.30			1	100	5
R411819124		19	± 0.7	± 1.0			≤ 1.20	≤ 1.30			1	100	5
R411820124	20	± 0.7	± 1.0			≤ 1.20	≤ 1.30			1	100	5	
R411800119	DC - 8	0		+ 0.2			≤ 1.20		≤ 1.25	2	100	5	
R411801119		1		± 0.3	± 0.4		≤ 1.20		≤ 1.25	2	100	5	
R411802119		2		± 0.3	± 0.4		≤ 1.20		≤ 1.25	2	100	5	
R411803119		3		± 0.3	± 0.4		≤ 1.20		≤ 1.25	2	100	5	
R411804119		4		± 0.3	± 0.4		≤ 1.20		≤ 1.25	2	100	5	
R411805119		5		± 0.4	± 0.5		≤ 1.20		≤ 1.25	2	100	5	
R411806119		6		± 0.4	± 0.5		≤ 1.20		≤ 1.25	2	100	5	
R411807119		7		± 0.4	± 0.5		≤ 1.20		≤ 1.25	2	100	5	
R411808119		8		± 0.4	± 0.5		≤ 1.20		≤ 1.25	2	100	5	
R411809119		9		± 0.4	± 0.5		≤ 1.20		≤ 1.25	2	100	5	
R411810119		10		± 0.4	± 0.5		≤ 1.20		≤ 1.25	2	100	5	
R411811119		11		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411812119		12		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411813119		13		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411814119		14		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411815119		15		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411816119		16		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411817119		17		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411818119		18		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411819119		19		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5	
R411820119	20		± 0.5	± 0.6		≤ 1.20		≤ 1.25	2	100	5		

