

COAXIAL ATTENUATORS

N

1 - 2 WATTS

Part Number	Frequency range (GHz)	ATTENUATION (dB)			V.S.W.R.		Power (W)		Figure
		Nominal	DEVIATION		DC - 2	2 - 3	avg.	peak	
			CC - 2	2 - 3					
R412700000	DC - 2	0	+ 0.35		≤ 1.20		2	100	1
R412701000		1	± 0.35		≤ 1.15		2	100	1
R412702000		2	± 0.35		≤ 1.15		2	100	1
R412703000		3	± 0.35		≤ 1.15		2	100	1
R412704000		4	± 0.35		≤ 1.15		2	100	1
R412705000		5	± 0.35		≤ 1.15		2	100	1
R412706000		6	± 0.35		≤ 1.15		2	100	1
R412707000		7	± 0.35		≤ 1.15		2	100	1
R412708000		8	± 0.35		≤ 1.15		2	100	1
R412709000		9	± 0.35		≤ 1.15		2	100	1
R412710000		10	± 0.35		≤ 1.15		2	100	1
R412711000		11	± 0.35		≤ 1.15		2	100	1
R412712000		12	± 0.35		≤ 1.15		2	100	1
R412713000		13	± 0.35		≤ 1.15		2	100	1
R412714000		14	± 0.35		≤ 1.15		2	100	1
R412715000		15	± 0.35		≤ 1.15		2	100	1
R412720000		20	± 0.45		≤ 1.15		2	100	1
R412730000		30	± 0.80		≤ 1.15		2	100	2
R412740000		40	± 0.80		≤ 1.15		2	100	2
R412750000		50	± 1.00		≤ 1.15		2	100	2
R412700124	DC - 3	0	+ 0.3	+ 0.5	≤ 1.20	≤ 1.30	1	100	3
R412701124		1	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412702124		2	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412703124		3	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412704124		4	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412705124		5	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412706124		6	± 0.3	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412707124		7	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412708124		8	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412709124		9	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412710124		10	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412711124		11	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412712124		12	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412713124		13	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412714124		14	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412715124		15	± 0.5	± 0.5	≤ 1.20	≤ 1.30	1	100	3
R412716124		16	± 0.7	± 0.7	≤ 1.20	≤ 1.30	1	100	3
R412717124		17	± 0.7	± 0.7	≤ 1.20	≤ 1.30	1	100	3
R412718124		18	± 0.7	± 1.0	≤ 1.20	≤ 1.30	1	100	3
R412719124		19	± 0.7	± 1.0	≤ 1.20	≤ 1.30	1	100	3
R412720124		20	± 0.7	± 1.0	≤ 1.20	≤ 1.30	1	100	3





Figure	A inch (mm)	B inch (mm)	Weight (g)
1	1.97" (50)	.62" (15.8)	60
2	2.39" (60.7)		70
3	1.38" (35)		43