




### Model Number

NBB1,5-8GM40-E2-C

### Features

- 1.5 mm flush
- 3-wire DC

### Connection



### Accessories


#### BF 8

Mounting flange, 8 mm

#### EXG-08

Quick mounting bracket with dead stop

## Dimensions



## Technical Data

### General specifications

Switching element function		PNP	NO
Rated operating distance	$s_n$	1.5 mm	
Installation		flush	
Output polarity		DC	
Assured operating distance	$s_a$	0 ... 1.215 mm	
Reduction factor $r_{AI}$		0.3	
Reduction factor $r_{Cu}$		0.25	
Reduction factor $r_{304}$		0.65	

### Nominal ratings

Operating voltage	$U_B$	10 ... 30 V DC
Switching frequency	$f$	0 ... 1800 Hz
Hysteresis	$H$	typ. 5%
Reverse polarity protection		reverse polarity protected
Short-circuit protection		pulsing
Voltage drop	$U_d$	$\leq 3$ V
Operating current	$I_L$	0 ... 100 mA
No-load supply current	$I_0$	$\leq 20$ mA
Alternating magnetic field	$B$	100 mT
Indication of the switching state		LED, yellow

### Functional safety related parameters

MTTF <sub>d</sub>	2240 a
Mission Time ( $T_M$ )	20 a
Diagnostic Coverage (DC)	0 %

### Ambient conditions

Ambient temperature	-25 ... 70 °C (-13 ... 158 °F)
---------------------	--------------------------------

### Mechanical specifications

Connection type	cable PVC, 2 m
Core cross-section	0.14 mm <sup>2</sup>
Housing material	Brass, PTFE coated
Sensing face	PPS; Ryton R4
Protection degree	IP67

### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

### Approvals and certificates

UL approval	cULus Listed, General Purpose
CSA approval	cCSAus Listed, General Purpose
CCC approval	Products with a maximum operating voltage of $\leq 36$ V do not bear a CCC marking because they do not require approval.