



### Model Number

**NBB1,5-8GS30-E2-T**

### Features

- 1.5 mm flush
- Stainless steel housing
- Extended temperature range

### Accessories

#### BF 8

Mounting flange, 8 mm

#### EXG-08

Quick mounting bracket with dead stop

## Technical Data

### General specifications

Switching element function		PNP	NO
Rated operating distance	$s_n$	1.5 mm	
Installation		flush	
Output polarity		DC	
Assured operating distance	$s_a$	0 ... 1.215 mm	
Actuating element		mild steel, e. g. 1.0037, SR235JR (formerly St37-2) 8 mm x 8 mm x 1 mm	
Reduction factor $r_{Al}$		0.38	
Reduction factor $r_{Cu}$		0.2	
Reduction factor $r_{304}$		0.8	
Reduction factor $r_{Brass}$		0.45	

### Nominal ratings

Operating voltage	$U_B$	10 ... 30 V
Switching frequency	$f$	0 ... 1500 Hz
Hysteresis	$H$	0.01 ... 0.33 mm
Reverse polarity protection		yes
Short-circuit protection		yes
Overload resistance		yes
Wire breakage protection		yes
Inductive overvoltage protection		yes
Surge suppression		yes
Ripple		10 %
Voltage drop	$U_d$	$\leq 2.5$ V
Repeat accuracy	$R$	0.04 mm
Operating current	$I_L$	0 ... 200 mA
Off-state current	$I_r$	0.01 mA
No-load supply current	$I_0$	$\leq 7$ mA
Switching state indicator		LED, yellow

### Functional safety related parameters

MTTF <sub>d</sub>	2360 a
Mission Time (T <sub>M</sub> )	20 a
Diagnostic Coverage (DC)	0 %

### Ambient conditions

Ambient temperature	-25 ... 100 °C (-13 ... 212 °F)
Storage temperature	-40 ... 100 °C (-40 ... 212 °F)

### Mechanical specifications

Connection type	cable PUR , 2 m
Core cross-section	0.25 mm <sup>2</sup>
Housing material	Stainless steel 1.4305 / AISI 303
Sensing face	PBT
Degree of protection	IP67
Mass	58 g


### Compliance with standards and directives

Standard conformity	
Standards	EN 60947-5-2:2007 IEC 60947-5-2:2007

### Approvals and certificates

CCC approval	CCC approval / marking not required for products rated $\leq 36$ V
--------------	--

## Dimensions



## Electrical Connection

