





EXAMPLE:

PART NUMBER RJHSE-538X

TYPICAL FOR SINGLE &

MULTI-PORT

+ - (CATHODE)

- LED COLOR CODE

CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)
0	BLOCKED	BLOCKED	9	GREEN	BLOCKED	J	BiC RD/GR	YELLOW
1	YELLOW	GREEN	А	BiC GR/YE	BiC GR/YE	K	YELLOW	BiC GR/OR
2	BLOCKED	GREEN	В	BiC RD/GR	BiC RD/GR	L	BiC GR/YE	RED
3	YELLOW	BLOCKED	С	BiC RD/GR	BiC GR/YE	М	RED	YELLOW
4	GREEN	YELLOW	D	GREEN	BiC GR/YE	N	BiC GR/RD	BiC GR/YE
5	GREEN	GREEN	Е	YELLOW	BiC GR/YE	P	GREEN	BiC RD/GR
6	YELLOW	YELLOW	F	BiC GR/YE	YELLOW	R	BiC GR/OR	GREEN
7	RED	GREEN	G	BiC GR/OR	BiC GR/OR	T	RED	RED
8	GREEN	RED	Н	BiC GR/YE	GREEN	V	BiC RD/GR	GREEN
						W	ADDITIONAL	OPTIONS

EXAMPLE OF ADDITIONAL LED OPTIONS:

PART NUMBER RJHSE-538W-01Y

ADDITIONAL LED COLOR CODE

DENOTES ADDITIONAL LED OPTIONS TO BE USED

С

D

CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT)	LED 1 (RIGHT)	CODE	LED 2 (LEFT) LED 1 (RIGHT)
0	DO NOT USE		5	BLOCKED	YELLOW	Е	BIC GR/YE BIC GR/RD
1	RED	BLOCKED	6	RED	BiC RD/GR	А	LOWC YE LOWC YE
2	BiC GR/OR	YELLOW	7	BLOCKED	BiC RD/GR	В	LOWC YE LOWC GR
3	YELLOW	RED	8	BiC RD/GR	BLOCKED	С	LOWC GR LOWC YE
4	BLOCKED	RED	9	BiC GR/YE	BLOCKED	D	LOWC GR LOWC GR
						М	LOWC RD LOWC YE

REVISIONS

SYM ZONE ECN, ERN NO. DATE APPRD.

A PROPOSAL SEP21/04

B ADD LED CODE N AUG16/12 L.C

LED SPECIFICATIONS:

FORWARD VOLTAGE: 2.1 VOLTS TYP. REVERSE VOLTAGE: 5.0 VOLTS MIN. LUMINOUS INTENSITY: 0.5 mCd MIN.

(AT If=2mA)

STORAGE TEMPERATURE: -20° TO 85° C LEAD SOLDERING TEMPERATURE: 260° C

(5 SEC, 1/16" FROM CASE)

PLATING ON TAILS: TIN OR TIN/COPPER ALLOY OVER SILVER

PRIMARY COLOR FOR BI-COLOR LEDS IN STANDARD ANODE/ CATHODE CONFIGURATION IS: RED-GREEN= RED RED-YELLOW= RED GREEN-YELLOW= GREEN GREEN-ORANGE= GREEN

LEGEND
BIC=BI-COLOR LED
LOWC=LOW CURRENT LED
YE=YELLOW
GR=GREEN
RD=RED
OR=ORANGE

NOTE:

THE TWO DIGITS PRECEDING THE ADDITIONAL LED CODE MUST BE USED IN THE PART NUMBER, WHEN ORDERING ANY OF THE ADDITIONAL LED OPTIONS.

DRAWN K. LAMBIE	DATE SEP21/04	۸.			- I		<u> </u>		ها ۵۰		\bigcirc		_
DESIGNED		_ /\r	mp h	en) I	(∪ a r	7 a	aa	,	\cup C	r	ο.
CHECKED		TITLE											
I. E. APPRD.			D 0	PTIO	NS	F	OR	RJH	HSE	- - •	SII	NGL	E.
Q. A. APPRD.) Of	R ML	JLTI-	-P0	R	T C	NC	1EC	TC	DRS	5	
DWG. APPRD.			_	Rot	1S	C(PMC	LIAI	VΤ				
ENG. REL. NO.	DWG	DRAWIN										REV.	
REF.			P-RJHSE-LEDS ,						B				
DIMENSIONS ARE IN												1	

THIS DOCUMENT CONTAINS PROPRIETARY INFORMATION AND SUCH INFORMATION MAY NOT BE DISCLOSED TO OTHERS FOR ANY PURPOSE OR USED FOR MANUFACTURING PURPOSES WITHOUT WRITTEN PERMISSION FROM AMPHENOL CANADA CORP.