Features

- 1-channel isolated barrier
- 24 V DC supply (loop powered)
- Current limit 65 mA at 9.8 V DC
- Up to SIL3 acc. to IEC 61508


Function

This isolated barrier is used for intrinsic safety applications. It supplies power to solenoids, LEDs, and audible alarms located in a hazardous area.

It is loop powered, so the available energy at the output is received from the input signal. The output signal has a resistive characteristic. As a result the output voltage and current are dependent on the load and the input voltage.

At full load, 9.8 V at 65 mA is available for the hazardous area application.

Assembly








SIL3


Connection



General specifications		
Signal type		Digital Output
Supply		
Rated voltage	Un	loop powered
Power dissipation		<1 W (≤30 V)
Input		
Connection		terminals 7, 8
Rated voltage	Un	20 35 V DC
Current	o _{II}	72 mA at 20 V input voltage, load = 150 Ω 50 mA at 35 V input voltage, load = 150 Ω
Output		oo hiir tat oo v iiipat vonago, load – 100 12
Connection		terminals 1+, 2-
Internal resistor	D.	≤ 90 Ω
	R _i	≤ 65 mA
Current	l _e	
Voltage	U _e	≥ 9.8 V
Open loop voltage	U _s	≥15.4 V
Output rated operating curren	nt	65 mA
Output signal		These values are valid for the rated operating voltage 20 35 V DC.
Energized/De-energized dela	ıy	single operation: 300 μ s/50 μ s; periodical: 5 μ s / 50 μ s
Directive conformity		
Electromagnetic compatibility	′	
Directive 2004/108/EC		EN 61326-1:2013 (industrial locations)
Conformity		
Electromagnetic compatibility		NE 21:2006
Degree of protection		IEC 60529:2001
Protection against electrical shock		UL 61010-1:2004
Ambient conditions		
Ambient temperature		-20 60 °C (-4 140 °F)
Mechanical specifications		
Degree of protection		IP20
Mass		approx. 100 g
Dimensions		20 x 107 x 115 mm (0.8 x 4.2 x 4.5 in) , housing type B1
Mounting		on 35 mm DIN mounting rail acc. to EN 60715:2001
Data for application in connection		Off 35 Hill DIN Houriting rail acc. to EN 607 15.2001
with Ex-areas		
EC-Type Examination Certificate		BASEFA 06 ATEX 0252, for additional certificates see www.pepperl-fuchs.com
Group, category, type of protection		\textcircled{x} II (1)G [Ex ia Ga] IIC, II (1)D [Ex ia Da] IIIC, I (M1) [Ex ia Ma] I (-20 °C ≤ T_{amb} ≤ 60 °C)
Voltage	U_{o}	17.22 V
Current	l _o	220 mA
Power	P_{o}	947 mW
Input		
Maximum safe voltage	U_{m}	250 V (Attention! The rated voltage can be lower.)
Statement of conformity		TÜV 99 ATEX 1499 X , observe statement of conformity
Group, category, type of protection, temperature class		(x) II 3G Ex nA II T4 [device in zone 2]
Electrical isolation		
Input/Output		safe electrical isolation acc. to IEC/EN 60079-11, voltage peak value 375 V
Directive conformity		
Directive 94/9/EC		EN 60079-0:2012+A11:2013 , EN 60079-11:2012 , EN 60079-15:2010
International approvals		
FM approval		
Control drawing		266-031FM-12 (cFMus)
UL approval		
Control drawing		116-0316 (cULus)
· ·		
IECEx approval		IECEx BAS 06.0058
General information		FO Time Francisco Continues Continues Continues of Conference Devices in Conference Attacks of Conference Atta
Supplementary information		EC-Type Examination Certificate, Statement of Conformity, Declaration of Conformity, Attestation of Conformity and instructions have to be observed where applicable. For information see www.pepperl-fuchs.com.

Output characteristics

Output circuit diagram



Output characteristic

