SBE®80 / SBO® 60 Connectors - up to 80 Amps



SBE® and SBO® connectors build on the capability of the two pole SB® connectors by offering up to 8 auxiliary power / signal contacts along with an IEC 60950 touch safe housing. The center of the main connector features a connector holder for either: two PP15-45, two PPMX, or APP's innovative 1x4 auxiliary connector.

- Touch Safe Interface

 Minimizes potential contact with live circuits per IEC 60950
- Up to 8 Last Mate / First Break Auxiliary's


 Enables intelligent power switching, CAN and interlock loop
 circuitry, as well as power up to 20 amps per pole
- Silver Plated Wire Contacts up to #4 (25 mm²)
 Allows UL rated currents up to 80 amps per pole

| SBE®80 / SBO®60 ORDERING INFORMATION |

SBE®80 / SBO®60 Housings

The smallest size of SBE®, X, O style housing. SBE®80 and SBO®60 housings of the same Voltage Color Code can be mated but is not recommended as it invalidates UL approvals for SBO®60. SBO®60 housings do not meet EN1175-1 requirements for industrial trucks.

	Voltage				
	Color				
Description	Code	SBE®80 Part	Numbers	SBO®60 Part	Numbers
Minimum Qu	uantity	400	25	400	25
Yellow	12V	SBE80YEL-BK	SBE80YEL	SBO60YEL-BK	SBO60YEL
Orange	18V	SBE80ORN-BK	SBE80ORN	SBO60ORN-BK	SBO60ORN
Red	24V	SBE80RED-BK	SBE80RED	SBO60RED-BK	SBO60RED
Gray	36V	SBE80GRA-BK	SBE80GRA	N/A	N/A
White	144V	N/A	N/A	SBO60WHT-BK	SBO60WHT



[69.6]

Mated Length

[112.2]


4.42

SBE®80 / SBO®60 Silver Plated Primary Power Wire Contacts

Use two silver plated contacts per housing for the best electrical performance and durability up to 10,000 mating cycles. See reducing bushings in accessory section for smaller wire size

						Dimer	nsions	
		Mating			- A		- E	3 -
AWG	mm²	Force	- Loose Piece F	Part Numbers -	inches	mm	inches	mm
Minim	um Quai	ntity	1,000	100				
4	25	Low	1339G4-BK	1339G4 *	0.28	7.11	0.35	9.0
6	16	High	1339G1-BK	1339G1 *	0.22	5.59	0.29	7.3

^{*} Sold as pairs. 2 parts shipped for every 1 part ordered.





www.andersonpower.com

□ □ φ

[49.5]

1.95

0.58

[5.1] 0.20 **Materials**

| SBE®80 / SBO®60 CONNECTOR SPECIFICATIONS |

Electrical		
Current Rating Amperes ¹	SBO60	SBE80
Primary Power (6 AWG)	70	80
Powerpole® Auxiliary (12 AWG)	20	20
1x4 Auxiliary (12 AWG)	20	20
PPMX Auxiliary (20 AWG)	7 UL	5 CSA
Voltage Rating AC/DC	UL 1977	EN1175-1
Primary Power	600	150 ⁴
Powerpole® Auxiliary	600	150 ⁴
1x4 Auxiliary	200	
PPMX Auxiliary	300	
Dielectric Withstanding Voltage Primary Power		
Volts AC	2,200	
Avg. Mated Contact Resistance Milliohms¹		
1 1/4" of #6 AWG wire	0.200	
Hot Plug Current Rating Amperes - 250 cycles at	120V DC	
Power	60A	
Powerpole® Auxiliary	30A	
1x4 Auxiliary	5A	

Materials	
Housing SBE® / SBO® & 1x4 Auxiliary Housing Powerpole® Plastic Resin Contact Retention Spring	Polycarbonate / PBT blend Polycarbonate Stainless Steel
Housing Flommobility Boting	
Housing Flammability Rating UL94	V-0
Power & Powerpole® Contact	Silver Plated Copper Alloy
1x4 Auxiliary Contacts	
Pin	Copper alloy, Au over Ni
Socket	BeCu, Au over Ni
Socket Body	Copper alloy, Sn bright over Ni
Retention Clip	Stainless Steel
PPMX Contacts	Gold Plated Copper Alloy
Contact Termination Methods	
Crimp ³	
Hand Solder	
Hallu Soluel	

Mechanical		
Wire Size Range	AWG	mm²
Power Contacts	16 to 6	1.3 to 13.3
Auxiliary Contacts	24 to 10	0.25 to 5.3
Max. Wire Insulation Diameter	in.	mm
Power Contacts	0.440	11.200
Powerpole® Auxiliary	0.175	4.450
1x4 Auxiliary	0.140	3.600
Operating Temperature ²	°F	°C
SBO® and SBE® Housings	-4° to 221°	-20° to 105°
Mating Cycles No Load by Plating	Silver (Ag)	Gold (Au)
Power Contacts	10,000	
Powerpole® Auxiliary	10,000	
1x4 Auxiliary		10,000
PPMX Auxiliary		5,000
Ave Metine / Hometine Force	Lbf.	N
Avg. Mating / Unmating Force	16	N 70
Main Connnector Housing Per Powerpole®	5	70 22
Per Contact in 1x4 Auxiliary	0.7	3.0
Per PPMX Housing	4.50	20.00
Fei FFIMA Housing	4.50	20.00
Min. Contact / Spring Retention Force	Lbf.	N
Power Standard Housing	50	222
Powerpole® Housing	25	111
1x4 Auxiliary Housing	10	44.5
, ,		

Protection

Touch Safety Main Connector Housing
IEC 60950 Pass
IEC 60529 IP20

- ¹ Based on: 105°C rated or better cable of the largest size, Properly calibrated APP® recommended tooling, and a 25°C ambient temperature. UL rating not to exceed the maximum operating temperature. CSA rating below a 30°C temperature rise. Only SBO®60 has UL recognition.
- ² Limited by the thermal properties of the connector plastic housing.
- ³ Use APP® recommended tooling only. Alternate tools may adversely affect the performance of our connectors along with UL and CSA recognition.
- 4 Voltage capability of SBE® housings is identical to SBO®, but derated to meet EN1175-1 requirements.











| SBE®80 / SBO®60 CONNECTOR TEMPERATURE CHARTS|






NOTE: Temperature rise charts are based on a 25°C ambient temperature.

| SBE®80 / SBO®60 Accessories |

Cable Clamps

Clamps are made out the same chemical resistant PBT material that is used in the SBE® housings. Clamp holds the cable between the clamp piece and the connector housing. Screws must be ordered separately for part numbers starting with "113".


Description		Part Numbers
Minimum Quantity	100	25
Red Clamp and Hardware Kit	-	SBE80CLPRED or SBO60CLPRED
Red Clamp Only	113953P1	-
Screws (2 per clamp)	H1120P42 (Individual)	-



"T" Handle

Handles are made out the same chemical resistant PBT material that is used in the SBE® housings. (2) screws and (2) nuts are required to attach each handle.


Description		Part Numbers				
Minimum Quantity	500	100	25			
Red Handle and Hardware Kit	-	- S	BE80HDLRED or SBO60HDLRED			
Red Handle Only	113952P1	-	-			
Hardware Bag	-	-	105G13			
M5 x 35mm Screws	-	113715P4	-			
M5 Nut	-	113716P3	-			



Powerpole® Auxiliary

Powerpole® auxiliary connectors are rated up to 30 amps 600 volts and can be used for auxiliary power, control or sensing. The auxiliary kit includes (1) each black and red Standard Powerpole® housing, (2) contacts, (2) zip cable straps, and (2) retaining pins.

Description	Part N	lumbers
Minimum Quantity	200	25
Powerpole® Auxiliary Kit	-	6344
Black Powerpole® Housing	1327G6	-
Red Powerpole® Housing	1327	-
#16 to #12 Contact	1331	-
Retaining Pin	-	-




1x4 Auxiliary Connector

APP®'s unique 1x4 auxiliary connector allows up to 4 auxiliary circuits up to 20 amps 200 volts each in SBE®, SBO®, & SBX® housings. The genderless design holds two each of the gold plated pin & socket contacts. This innovation allows the very durable and cost effective design of SBE®,O,X connectors to substitute for DIN 43589-1 applications where 4 auxiliary contacts are required. Multiple pin lengths allow the further benefit of sequencing between circuits.

- (2) Retaining pins are required to hold the auxiliary housing in place. Auxiliary Kits include
- (1) Auxiliary Housing, (2) Standard Length Pin Contacts, and (2) Socket Contacts,
- (2) Retaining Pins and (1) Retaining Clip.


Description	AWG	mm²	P	art Numbers	
Minimum Quantity			1,000	250	25
1x4 Auxiliary Kit	12	4	-	-	441G3
1x4 Auxiliary Kit	16 to 14	1.5 to 2.5	-	-	441G1
1x4 Auxiliary Kit	20 to 16	0.75 to 1.5	-	-	441G2
1x4 Auxiliary Housing	Contacts	Sold Separately	3-5956P1	444G1	-



Pin Contacts for 1x4 Auxiliary Connector

Gold plated contacts are available in 4 lengths to allow sequencing of circuits.

Description	AWG	mm²	Part	Numbers
Minimum Quantity			500	50
Standard Length 7.7mm	12	2.5	PM16P12S30	PM16P12S30-50
	16 to 14	1.0 to 1.5	PM16P1416S30	PM16P1416S30-50
	20 to 16	0.75 to 1.0	PM16P1620S30	PM16P1620S30-50
	24 to 20	0.50 to 0.75	PM16P2024S30	PM16P2024S30-50
Pre-Mate 9.3mm	12	2.5	PM16P12A30	PM16P12A30-50
	16 to 14	1.0 to 1.5	PM16P1416A30	PM16P1416A30-50
	20 to 16	0.75 to 1.0	PM16P1620A30	PM16P1620A30-50
	24 to 20	0.50 to 0.75	PM16P2024A30	PM16P2024A30-50
Post-Mate 6.4mm	12	2.5	PM16P12C30	PM16P12C30-50
	16 to 14	1.0 to 1.5	PM16P1416C30	PM16P1416C30-50
	20 to 16	0.75 to 1.0	PM16P1620C30	PM16P1620C30-50
	24 to 20	0.50 to 0.75	PM16P2024C30	PM16P2024C30-50
İ				




Auxiliary Pin	- L		- L	1 -
Contact Lengths	in.	mm	in.	mm
Standard Length 7.7mm	0.77	19.6	0.30	7.7
Pre-Mate 9.3mm	0.83	21.2	0.37	9.3
Post-Mate 6.4mm	0.72	18.3	0.25	6.4

Socket Contacts for 1x4 Auxiliary Connector

Selectively gold plated contacts offer low resistance and durability up to 10,000 mating cycles.

Description	AWG	mm²	Pa	art Numbers
Minimum Quanti	ty		500	50
Socket Contact	12	2.5	PM16S12S32	PM16S12S32-50
	16 to 14	1.0 to 1.5	PM16S1416S32	PM16S1416S32-50
	20 to 16	0.75 to 1.0	PM16S1620S32	PM16S1620S32-50
	24 to 20	0.50 to 0.75	PM16S2024S32	PM16S2024S32-50



Auxiliary Socket Contacts Crimp Barrel ID						
Wire Gauge	in.	mm.				
#24 / 20	0.04	1.1				
#20 / 16	0.07	1.7				
#16 / 14	0.08	2.1				
#12	0.10	2.6				




PPMX Auxiliary Connector

The PPMX auxiliary connector allows up to 8 auxiliary circuits to be used in the SBE®, SBO®, & SBX® housings. There are 4 auxiliary circuits per PPMX connector and two PPMX housings fit into the auxiliary port in the main connector housing. Rated up to 7 amps 300 volts per contact, the genderless design holds two each gold plated pin & socket contacts. This innovation allows the very durable and cost effective equipment design of SBE®, O, X connectors to be used for applications requiring up to 8 battery monitoring or vehicle communication circuits. (2) Retaining pins or (1) Retaining clip is required to hold the auxiliary housing in place.

Auxiliary Kits include (1) Auxiliary Housing, (2) Pin Contacts, and (2) Socket Contacts.

Description	AWG	mm²	Part Numbers		
Minimum Quantity			1,000	100	25
PPMX Auxiliary Kit	24 to 20	0.50 to 0.25	-	4850G6	-
1x4 Auxiliary Housing	Contacts	Sold Separately	4827G6-BK	-	4827G6






Pin & Socket Contacts for PPMX Auxiliary Connector

Gold plated contacts are ideal for signal or low power use with durability up to 5,000 mating cycles.

Description	AWG	mm²	Part Num	bers
Minimum Quantity .			2,000	50
Pin Contacts	24 to 20	0.50 to 0.25	4803G3-BK	4803G3
Socket Contacts	24 to 20	0.50 to 0.25	4802G3-BK	4802G3




NOTE: Contacts sold individually, not sold as a set of two.

SBE® Air Tubes

Air tubes fit into SBE® housings to allow electrolyte circulation while charging the battery. Genderless tube design allows the same part to be used on both sides. (2) Retaining pins are required to hold the air tube in place. Retaining pins are included in Air Tube Kit.


Description	Part Numbers				
Minimum Quantity	500	25			
Air Tube Kit, Black	-	6396G1			
Air Tube Only	3-5798P1	-			



Retaining Pins

Retaining pins are used to hold accessories in the auxiliary port in SBE $^{\circ}$, SBO $^{\circ}$, & SBX $^{\circ}$ housings. Dimension "B" is +/- 0.015 in or 0.38 mm.


				Dimensio	ns		
			- A -		-	В-	
Description	Part Nur	mbers	inches	mm	inches	mm	
Minimum Quantity	1,000	100					
For SBE®80 & SB0®60	110G9-BK	110G9	0.093 / 0.103	2.36 / 2.62	1.000	38.100	



Zip Cable Straps

Zip cable straps are used to secure auxiliary wires to the side of the main power cables.


Description	Part Number
Minimum Quantity	1,000
White	H1835P3



Reducing Bushings

Use with contact part number 1339G1 to allow a smaller wire to be used with the connector. Electrical capability is derated with smaller wire.

				Dimensions			
				- ID -		- Length	-
Contact Barrel Size Wire Size	Par	t Numbers -		inches	mm	Inches	mm
Minimum Quantity	3,000	1,000	100				
#6 AWG [13.3 mm²] #8 AWG [8.4 mm²]	-	5912-BK					11.43
#6 AWG [13.3 mm ²] #12- 10 AWG [3.3- 5.3 mm ²]	5910-BK	-	5910	0.14	3.56	0.47	11.94
#6 AWG [13.3 mm²] #16- 14 AWG [1.3- 2.1 mm²]	5913-BK	-	5913	0.09	2.29	0.47	11.94



15221, DS-SBEO80-60 REV C4.0 www.andersonpower.com

SBO® / SBE® / SBX® - Tooling Information

Wire	e Size	Loose Piece Part Numbers	Lo	ose Piec	e Contact	t Crimp To	ool		
AWG	mm²	Contacts	Pneumatic Bench Tool	+ Die	+ Locator	Number of Crimps o	r Hand Tool		
		SI	BE 320 / SBX	350					
300 MCM	152	6358	N/A	N/A	N/A	N/A			
4/0 AWG	107.2	6356							
3/0 AWG	85	6355	1387G2	1303G12	1304G28	Double			
2/0 AWG	67.4	6354					1368		
#2	N/A	6394		1303G2	1304G28		Series		
N/A	95 mm²	1341G3		1303G17	1304G35				
N/A	70 mm²	1341G2	1387G2	1303G12	1304G34	Double			
N/A	50 mm²	1341G1		1303G8	1304G36				
		SI	BE 160 / SBX	175					
1/0 AWG	53.5	6384G1	1387G2	1303G2	1304G13				
1/0 AWG	55.5	0304G1	1387G1	1388G3	1389G3	Single	1368 Series		
#2	35 mm²	6384G2	1387G2	1303G2	1304G13				
		5	BO 60 / SBE	80					
#4	25	1339G4	1387G1	1388G7	1389G9	Single	N/A		
#6	16	1339G1	100701	1388G6	100000	Omigio	1309G4		
		Powerpol	le 15/45 Auxil	iary Conta	cts **				
#16 / 20	1.3 / .52	1332	1367G1	N/A	N/A	Single	1309G2 or		
#12 / 16	3.3 / 1.3	1331	100701	1071	1471	Omigio	1309G8		
		PowerM	od 1x4 Auxili	ary Contac	ets				
#12 / 24	2.5 / .25	All Crimp Pins	TP0001* N/A		TD0001* N/A		TL0001	Single	TM0001*
#12/24	2.07.20	All Crimp Sockets			TL0002	Single	PM1000G1		
		PPMX	Auxiliary Co	ntacts					
#20 / 24	0.50 / 0.25	4803G3	TP0001*	N/A	TL0005	Single	TM0001* or		
#20 / 24	0.007 0.20	4802G3	11 0001	IFUUUI IN/A		Sirigio	PM1000G1		

^{*} TP0001 and TM0001 tools require locators to properly position contacts.

SBE®160 / SBX®175 Power Contact Extraction Tool: 969P1 SBE®320 / SBX®350 Power Contact Extraction Tool: 970P1 1 x 4 Auxiliary contact Insertion Tool: PM10023G1 1 x 4 Auxiliary Contact Extraction Tool: PM1003G1

The auxiliary contacts used with wire sizes #16 - #24 AWG cannot be properly inserted without the insertion tool. Properly installed auxiliary contact of all wire gauges cannot be removed from the hosing without the extraction tool.

^{**} See Powerpole® family tooling chart for other Powerpole® contacts