





### N-CHANNEL ENHANCEMENT MODE MOSFET

### **Product Summary**

V <sub>(BR)DSS</sub>	R <sub>DS(ON)</sub>	I <sub>D</sub> T <sub>A</sub> = 25°C
60V	7.5Ω @ V <sub>GS</sub> = 5V	115mA

## **Description and Applications**

This new generation MOSFET has been designed to minimize the onstate resistance (R<sub>DS(on)</sub>) and yet maintain superior switching performance, making it ideal for high efficiency power management applications.

- DC-DC Converters
- Power management functions
- Battery Operated Systems and Solid-State Relays
- Drivers: Relays, Solenoids, Lamps, Hammers, Displays, Memories, Transistors, etc

### **Features**


- Low On-Resistance
- Low Gate Threshold Voltage
- Low Input Capacitance
- Fast Switching Speed
- Low Input/Output Leakage
- Ultra-Small Surface Mount Package
- Totally Lead Free, Full RoHS Compliant (Note 1)
- Halogen and Antimony Free. "Green" Device (Notes 2 and 3)
- Qualified to AEC-Q101 Standards for High Reliability

### **Mechanical Data**


- Case: SOT523
- Case Material: Molded Plastic. "Green" Molding Compound. UL Flammability Classification Rating 94V-0
- Moisture Sensitivity: Level 1 per J-STD-020
- Terminals: Matte Tin Finish annealed over Alloy 42 leadframe (Lead Free Plating). Solderable per MIL-STD-202, Method 208
- Terminal Connections: See Diagram
- Weight: 0.002 grams (approximate)












### Ordering Information (Note 4)

Part Number	Qualification	Case	Packaging
2N7002T-7-F	Commercial	SOT523	3,000/Tape & Reel
2N7002T-13-F	Commercial	SOT523	10,000/Tape & Reel
2N7002TQ-7-F	Automotive	SOT523	3,000/Tape & Reel
2N7002TQ-13-F	Automotive	SOT523	10,000/Tape & Reel

Notes:

- 1. EU Directive 2002/95/EC (RoHS) & 2011/65/EU (RoHS 2) compliant. No purposely added lead. Halogen and Antimony free
- 2. Halogen and Antimony free "Green" products are defined as those which contain <900ppm bromine, <900ppm chlorine (<1500ppm total Br + Cl) and <1000ppm antimony compounds.
- 3. Product manufactured with Date Code UO (week 40, 2007) and newer are built with Green Molding Compound. Product manufactured prior to Date Code UO are built with Non-Green Molding Compound and may contain Halogens or Sb₂O₃ Fire Retardants
- 4. For packaging details, go to our website at http://www.diodes.com.

# **Marking Information**



72 = Product Type Marking Code YM = Date Code Marking Y = Year (ex: T = 2006)M = Month (ex: 9 = September)

Date Code Key

Year	2005		2006	2007		2008	2009		2010	2011		2012
Code	S		Т	U		V	W		Χ	Υ		Z
Month	Jan	Feb	Mar	Apr	May	/ Jun	Jul	Aug	Sep	Oct	Nov	Dec
Code	1	2	3	4	5	6	7	8	9	0	N	D

April 2012



# **Maximum Ratings** @T<sub>A</sub> = 25°C unless otherwise specified

Charact	eristic	Symbol	Value	Units
Drain-Source Voltage		V <sub>DSS</sub>	60	V
Drain-Gate Voltage $R_{GS} \le 1.0 M\Omega$		$V_{DGR}$	60	V
Gate-Source Voltage	Continuous Pulsed	V <sub>GSS</sub>	±20 ±40	V
Drain Current (Note 5)	Continuous Continuous @ 100°C Pulsed	I <sub>D</sub>	115 73 800	mA

# Thermal Characteristics @T<sub>A</sub> = 25°C unless otherwise specified

Characteristic	Symbol	Value	Units
Total Power Dissipation (Note 5)	$P_d$	150	mW
Thermal Resistance, Junction to Ambient	$R_{ hetaJA}$	833	°C/W
Operating and Storage Temperature Range	$T_{j,}T_{STG}$	-55 to +150	°C


# Electrical Characteristics @TA = 25°C unless otherwise specified


Chamastanistic		Compleal	N4:	T	Marr	I I m it	Toot Condition
Characteristic	;	Symbol	Min	Тур	Max	Unit	Test Condition
OFF CHARACTERISTICS (Note 6)							
Drain-Source Breakdown Voltage		BV <sub>DSS</sub>	60	_	_	V	$V_{GS} = 0V, I_{D} = 10\mu A$
Zero Gate Voltage Drain Current	@ $T_C = 25^{\circ}C$				1.0	μA	V 60V V 0V
	$@ T_C = 125^{\circ}C$	I <sub>DSS</sub>			500	μΑ	$V_{DS} = 60V, V_{GS} = 0V$
Gate-Body Leakage		I <sub>GSS</sub>	_	_	±10	nA	$V_{GS} = \pm 20V, V_{DS} = 0V$
ON CHARACTERISTICS (Note 6)							
Gate Threshold Voltage		V <sub>GS(th)</sub>	1.0		2.0	V	$V_{DS} = V_{GS}, I_D = 250 \mu A$
Static Drain-Source On-Resistance	@ $T_j = 25^{\circ}C$	D		2.0	7.5	Ω	$V_{GS} = 5.0V, I_D = 0.05A$
	@ T <sub>j</sub> = 125°C	R <sub>DS</sub> (ON)	_	4.4	13.5	52	$V_{GS} = 10V, I_D = 0.5A$
On-State Drain Current		I <sub>D(ON)</sub>	0.5	1.0	_	Α	$V_{GS} = 10V, V_{DS} = 7.5V$
Forward Transconductance		g <sub>FS</sub>	80	_	_	mS	$V_{DS} = 10V, I_D = 0.2A$
DYNAMIC CHARACTERISTICS (Note 7	7)						
Input Capacitance		C <sub>iss</sub>		22	50	pF	
Output Capacitance		Coss	_	11	25	pF	$V_{DS} = 25V, V_{GS} = 0V, f = 1.0MHz$
Reverse Transfer Capacitance		C <sub>rss</sub>	_	2.0	5.0	pF	
SWITCHING CHARACTERISTICS (Not	e 7)						
Turn-On Delay Time		t <sub>D(ON)</sub>		7.0	20	ns	$V_{DD} = 30V, I_D = 0.2A,$
Turn-Off Delay Time		t <sub>D(OFF)</sub>		11	20	ns	$R_L = 150\Omega$ , $V_{GEN} = 10V$ , $R_{GEN} = 25\Omega$

Notes:

- 5. Device mounted on FR-4 PC board, with minimum recommended pad layout, single sided. 6 .Short duration pulse test used to minimize self-heating effect.
- 7. Guaranteed by design. Not subject to production testing.










Fig. 2 On-Resistance Variation with Gate Voltage and Drain-Source Current






Fig. 4 On-Resistance Variation with Temperature






# **Package Outline Dimensions**



SOT523							
Dim	Min	Max	Тур				
Α	0.15	0.30	0.22				
В	0.75	0.85	0.80				
С	1.45	1.75	1.60				
D	_		0.50				
G	0.90	1.10	1.00				
Η	1.50	1.70	1.60				
J	0.00	0.10	0.05				
K	0.60	0.80	0.75				
L	0.10	0.30	0.22				
M	0.10	0.20	0.12				
N	0.45	0.65	0.50				
α	0°	8°					
All	All Dimensions in mm						

# **Suggested Pad Layout**



Dimensions	Value (in mm)
Z	1.8
Х	0.4
Υ	0.51
С	1.3
E	0.7

April 2012



#### **IMPORTANT NOTICE**

DIODES INCORPORATED MAKES NO WARRANTY OF ANY KIND, EXPRESS OR IMPLIED, WITH REGARDS TO THIS DOCUMENT, INCLUDING, BUT NOT LIMITED TO. THE IMPLIED WARRANTIES OF MERCHANTABILITY AND FITNESS FOR A PARTICULAR PURPOSE (AND THEIR EQUIVALENTS UNDER THE LAWS OF ANY JURISDICTION).

Diodes Incorporated and its subsidiaries reserve the right to make modifications, enhancements, improvements, corrections or other changes without further notice to this document and any product described herein. Diodes Incorporated does not assume any liability arising out of the application or use of this document or any product described herein; neither does Diodes Incorporated convey any license under its patent or trademark rights, nor the rights of others. Any Customer or user of this document or products described herein in such applications shall assume all risks of such use and will agree to hold Diodes Incorporated and all the companies whose products are represented on Diodes Incorporated website, harmless against all damages.

Diodes Incorporated does not warrant or accept any liability whatsoever in respect of any products purchased through unauthorized sales channel. Should Customers purchase or use Diodes Incorporated products for any unintended or unauthorized application, Customers shall indemnify and hold Diodes Incorporated and its representatives harmless against all claims, damages, expenses, and attorney fees arising out of, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized application.

Products described herein may be covered by one or more United States, international or foreign patents pending. Product names and markings noted herein may also be covered by one or more United States, international or foreign trademarks.

#### LIFE SUPPORT

Diodes Incorporated products are specifically not authorized for use as critical components in life support devices or systems without the express written approval of the Chief Executive Officer of Diodes Incorporated. As used herein:

- A. Life support devices or systems are devices or systems which:
  - 1. are intended to implant into the body, or
  - 2. support or sustain life and whose failure to perform when properly used in accordance with instructions for use provided in the labeling can be reasonably expected to result in significant injury to the user.
- B. A critical component is any component in a life support device or system whose failure to perform can be reasonably expected to cause the failure of the life support device or to affect its safety or effectiveness.

Customers represent that they have all necessary expertise in the safety and regulatory ramifications of their life support devices or systems, and acknowledge and agree that they are solely responsible for all legal, regulatory and safety-related requirements concerning their products and any use of Diodes Incorporated products in such safety-critical, life support devices or systems, notwithstanding any devices- or systems-related information or support that may be provided by Diodes Incorporated. Further, Customers must fully indemnify Diodes Incorporated and its representatives against any damages arising out of the use of Diodes Incorporated products in such safety-critical. life support devices or systems.

Copyright © 2012, Diodes Incorporated

www.diodes.com