

175 Amps 600 Volts AC/DC

marathon™ Special Products

Product Data Sheet

132X474

Replace "x" with 1, 2, or 3 for number of poles

Power Terminal Block

Wire Range

• Line: (1) 2/0 - #14 AWG

Load: M6 X 13

Electrical Ratings

- 175 Amps
- 600V per UL 1059 & CSA 22.2 No.158, class B & C requirements
- SCCR of 10,000 A (default for terminal blocks).
- CU7AL 75°C connector terminal rating with copper or aluminum wire
- Factory & Field Wiring

Agency Compliance

- UR UL Recognized Terminal Block, Evaluated to UL 1059, File No.XCFR2.E62806
- CSA certifed to C22.2 No. 158, File No. LR19766 (wire classes B & C only)
- CE compliant to IEC 60947-7-1

Material Information

- Insulator base:
 - Thermoplastic
 - Flammability rating of insulator base UL94V0
 - Insulator base temperature rating: -40°C to 125°C (UL RTI)
- Connector: copper, tin plated
- Terminal screws: aluminum, tin plated
- Connector mounting screws: steel, zinc plated
- Threaded studs: steel, zinc plated
- Nuts: steel, zinc plated
- RoHS compliant

A Regal Brand





Termination Specifications

Line Side	Wire Size (CU Stranded)	Torque	Wires / Terminal	Wire Class (UL) 1
	2/0 - 1/0	13.6 N·m (120 lbf·in)	1	В, С
	1 - 6	13.6 N·m (120 lbf·in)	1	B, C, G, H, I (DLO)
	8	4.5 N·m (40 lbf·in)	1	B, C, G, H, I (DLO)
	10 - 14	4 N·m (35 lbf·in)	1	B, C, I (DLO)

Aluminum stranded wire range: 2/0 - #6 AWG

Solid copper wire range: 10 - 14 AWG
Wire strip length: 3/4 in. (19mm)
Terminal screw drive: 3/16 in. hex

Load Side	Termination Type	Torque	Stud Length	Maximum Lug/Bar Width
	Listed lugs on	6.9 N·m	1/2"	.63"
	M6 stud	(61 lbf·in)	(13mm)	(16mm)

- For use with conductors prepared with listed connectors such as single hole compression/crimp lugs or listed ring, fork or spade terminals.
- Conductor size, ampacity, temperature rating and type are dictated by the ratings of the listed lugs utilized and applicable code requirements.

¹ For information on copper stranded wire classes please visit: http://www.marathonsp.com/flexible-stranded-wire.php



Installation & Accessories

- Mounting (Panel or Din):
 - For use with #10 fastener.
 - Torque mounting fastener to 25-30 lbf·in (2.8 3.4 N·m).
 - 7.5 X 35 mm din rail mountable
- Covers:
 - Snap on, hinge covers available upon request
 - Catalog Number: CC132x (replace "x" with number of poles)
 - Covers are black thermoplastic
 - Accessory covers are not intended to provide insulation for electrical spacings.
- Insulator base adders and 1 pole product can be snapped together through integral dovetails to create variable pole power blocks
- Marker Strip: white vinyl strip with mounting screws available.
- Printing options available, consult customer service for specifications
- End bracket for din rail mounting: MSK35

Drawing

