



## ATHD Connector Series

The heavy duty ATHD connector series for size 12 and size 8 power contacts are sealed, single pole, in-line connection systems to replace splices and/or provide power wherever needed. These thermoplastic connectors are field installable and repairable and can thus replace expensive and unrepairable splices. The power connectors are ruggedized and designed for high vibration applications in the Heavy Equipment and Mining markets.

Additional styles and custom solutions to mate to the ATHD plugs are available upon request, including higher temperature resin and seals for harsh fluid applications.

### Features:



- Size 8 crimp contacts are rated to 70 amps\*
- Size 12 crimp contacts are rated to 35 amps\*
- Both will meet 100 mating cycles
- Designed for temperatures of -55 °C to 125 °C
- Operating voltage of 1000 VAC
- Dielectric withstanding voltage of 1500 VAC
- RoHS compliant
- Clip slots for a variety of mounting solutions
- IP67 rated

\* Using Amphenol's exclusive RADSOK® technology




## SPECIFICATIONS

	Size 12 System	Size 8 System
<b>Current Rating</b>	35A with RADSOK®, 25A with standard contacts	70A with RADSOK®, and 60A with standard contacts
<b>Contact Quantity</b>	1	1
<b>Contact Size</b>	12 AWG	8 AWG
<b>Operating Temperature</b>	-55 °C to 125 °C with 150°C upon request	-55 °C to 125 °C with 150°C upon request
<b>Contact Retention</b>	133N	156N
<b>Mating Cycles</b>	100	100
<b>Insulation Resistance</b>	1000MΩ Min. (at 25 °C)	1000MΩ Min. (at 25 °C)
<b>Dielectric Withstanding Voltage</b>	1500 AC (RMS)	1500 AC (RMS)
<b>Moisture Resistance</b>	IP67 (mated)	IP67 (mated)
<b>Operating Voltage</b>	500 VAC	500 VAC
<b>Allowable Wire Size</b>	16-12 AWG	10-8 AWG



## PART NUMBERS FOR PLASTIC

Note: Housing Plug must use the Socket terminal (PS) and Housing Receptacle must use Pin terminal (RP).



	Size 12 System for 12 gage cable	Size 12 System for 16 gage cable	Size 8 System
<b>Plug</b>	ATHD-1PS-12	ATHD-1PS-12 (16)	ATHD-1PS-8
<b>Receptacle</b>	ATHD-1RP-12	ATHD-1RP-12 (16)	ATHD-1RP-8

CONTACT SIZE	ATHD PLUG			ATHD RECEPTACLE		
	OVERALL LENGTH A	OVERALL HEIGHT B	OVERALL WIDTH C	OVERALL LENGTH D	OVERALL HEIGHT E	OVERALL WIDTH F
<b>12</b>	1.498(38.05)	.771(19.58)	.570(14.48)	2.073(52.65)	.850(21.59)	.710(18.08)
<b>8</b>	1.498(38.05)	.861(21.87)	.660(16.76)	2.073(52.65)	.940(23.88)	.800(20.32)

## PART NUMBERS FOR TERMINALS

Amphenol PN	Terminal Description
10-729936-121	Male pin size 12 machined w/ silver plating
10-729936-122	Male pin size 12 machined w/ nickel plating
10-729936-123	Male pin size 12 machined w/ tin plating
10-729936-161	Male pin size 12 machined w/ silver plating to crimp to 16 gage cable
10-729936-162	Male pin size 12 machined w/ nickel plating to crimp to 16 gage cable
10-729936-163	Male pin size 12 machined w/ tin plating to crimp to 16 gage cable
10-730402-121	Female socket size 12 machined w/ silver plating
10-730402-122	Female socket size 12 machined w/ nickel plating
10-730402-123	Female socket size 12 machined w/ tin plating
10-730402-161	Female socket size 12 machined w/ silver plating to crimp to 16 gage cable
10-730402-162	Female socket size 12 machined w/ nickel plating to crimp to 16 gage cable
10-730402-163	Female socket size 12 machined w/ tin plating to crimp to 16 gage cable
10-730742-121	Size 12 Radsok machined socket, silver plating
10-730526-081	Size 8 Radsok machined socket, silver plating
10-729867-081	Male pin size 8 machined w/ silver plating
10-729867-082	Male pin size 8 machined w/ nickel plating
10-729867-083	Male pin size 8 machined w/ tin plating
10-730401-081	Female socket size 8 machined w/ silver plating
10-730401-082	Female socket size 8 machined w/ nickel plating
10-730401-083	Female socket size 8 machined w/ tin plating

Notice: Specifications are subject to change without notice. Contact your nearest Amphenol Corporation Sales Office for the latest specifications. All statements, information and data given herein are believed to be accurate and reliable but are presented without guarantee, warranty, or responsibility of any kind, expressed or implied. Statements of suggestions concerning possible use of our products are made without representation or warranty that any such use is free of patent infringement and are not recommendations to infringe any patent. The user should assume that all safety measures are indicated or that other measures may not be required. Specifications are typical and may not apply to all connectors.

For further information on your individual application requirements, contact: Amphenol Corporation

North America:  
Amphenol Industrial Operations  
180 N. Freeport Drive, Plant 4  
Nogales, AZ 85621  
Tel: (520) 285-5130  
Fax: (520) 285-5134

Europe:  
Amphenol Industrial Operations Europe  
Via Barbaiana 5  
1-20020 Lainate (MI) Italy  
Tel: +39 02 93254.204  
Fax: +39 02 93254.444

Middle East:  
Amphenol Middle East Enterprises FZE  
Office C-37 PO Box 21107  
Ajman Free Zone, UAE  
Tel: +9 716-7422494  
Fax: +9 716-7422941

Asia:  
Amphenol Technology Shenzhen Ltd  
Block 5 Fuan 2nd Industrial Park  
Dayang Rd, Fuyong Baoan  
Baoan, Shenzhen, China 518103  
Tel: +86 755 2881 8389  
Fax: +86 755 2991 8310  
Email: enquiry@amphenol-aio.com

Email: tech@amphenol-aio.com

Email: info@amphenol-aio.com

Email: jhussain@amphenol-industrial.com