



SPECIFICATION SHEET

07-KA730



KUT-GARD® KNIT ACP/KEVLAR®/ GLASS GLOVE WITH POLYESTER LINER - MEDIUM WEIGHT 7 GAUGE

- Seamless knit construction provides comfort without sacrificing dexterity
- Proprietary ACP Technology, Kevlar® & Glass shell provides excellent protection against heat, cuts, lacerations and abrasions
- Heat resistance protects the hand from minor heat and burn injuries up to 350°F. DO NOT use near open flame
- Polyester lining is ultra soft and very lightweight
- Knit wrist helps prevent dirt and debris from entering the glove
- 100% Silicone Free
- Cotton color binding denotes sizing

APPLICATIONS

- Sheet metal fabrication
- Canning and recycling
- Pulp and paper processing
- Plastic molding
- Assembly
- Painting

CARE INSTRUCTIONS

Machine wash in warm water with Detergent. Rinse well and spin extract using high speed. Tumble dry on Low heat setting. Can be Dry-Cleaned. Do Not Bleach.

TECHNICAL DATA

MATERIAL	Kevlar®/Polyester with Silica core			
COLOR	Green			
CUFF STYLE	Elastic knit			
SIZES	S - XL			
PACKAGING	12 pairs per dozen, 12 dozen per case			
CASE	20" x 13" x 16" / 50.8cm x 33cm x 40.6cm			
CASE WEIGHT (S-XL)	S	M	L	XL
	22 lbs 10 kg	23 lbs 10.4 kg	24 lbs 10.9 kg	25 lbs 11.3 kg
COO	USA			

PERFORMANCE PROPERTIES

- Method ASTM F1790-05
- 2565 ± 150 Grams
- ANSI/ISEA 105-2000 Level 4 Cut Resistance


BARCODES

ITEM	BAG	DOZEN	CASE
07-KA730/XL	---	01616314125880	02616314125889
07-KA730/L	---	01616314125859	02616314125858
07-KA730/M	---	01616314125866	02616314125865
07-KA730/S	---	01616314125873	02616314125872



DIMENSIONS (in/cm)

	S	M	L	XL
A	9.0 / 22.9	10.0 / 25.4	10.4 / 26.7	10.9 / 27.9
B	3.6 / 9.1	4.0 / 10.2	4.1 / 10.4	4.3 / 10.9
H	White	Red	Yellow	Green





SPECIFICATION SHEET

09-K1350



MICROFINISH® LATEX GLOVE WITH KEVLAR®

- Crinkle finish provides excellent wet and dry grip
- Available in 10 gauge Kevlar® with acrylic liner

• APPLICATIONS

- Material handling
- Glass handling
- Operations
- Fishing Industries
- Sanitation
- General maintenance
- Woodworking
- Waste handling and recycling
- Cold weather

CARE INSTRUCTIONS

Machine wash in warm water with detergent. Rinse well and spin extract using high speed. Tumble dry on low to medium heat setting. Can be dry cleaned. DO NOT BLEACH.

TECHNICAL DATA

MATERIAL	Kevlar® / Acrylic / Latex				
COLOR	Black and yellow				
CUFF STYLE	Knit wrist				
SIZES	S - XXL				
PACKAGING	1 pair per bag, 12 pairs per dozen, 6 dozen per case				
CASE	26.8" x 10.8" x 9.6" / 68cm x 27.5cm x 24.5cm				
CASE WEIGHT (S-XXL)	S	M	L	XL	XXL
	17.6 lbs 8 kg	18.7 lbs 8.5 kg	19.8 lbs 9 kg	22 lbs 10 kg	23.1 lbs 10.5 kg
COO	China				
HARM CODE	6116.10.6500				



DIMENSIONS (in/cm)

	S	M	L	XL	XXL
A	10.2 / 25.8	10.5 / 26.6	10.6 / 27	10.9 / 27.6	11.3 / 28.6
B	3.9 / 10	4.1 / 10.5	4.3 / 11	4.5 / 11.5	4.6 / 11.8

PERFORMANCE PROPERTIES

EN388: 2342						
ABRASION	0	1	2	3	4	5
CUT	0	1	2	3	4	5
TEAR	0	1	2	3	4	5
PUNCTURE	0	1	2	3	4	5

BARCODES

ITEM	BAG	DOZEN	CASE
09-K1350/S	---	01616314124951	01616314124950
09-K1350/M	---	01616314124968	01616314124967
09-K1350/L	---	01616314124975	01616314124974
09-K1350/XL	---	01616314124982	01616314124981
09-K1350/XXL	---	01616314124999	01616314124998

